

APF3236SEEZGKQBKC

3.2 mm x 3.6 mm Full-Color Surface Mount LED Lamp



DESCRIPTIONS

- The Hyper Red source color devices are made with AIGaInP on GaAs substrate Light Emitting Diode
- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- The Blue source color devices are made with InGaN Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 3.2 mm x 3.6 mm SMD LED, 1.1 mm thickness
- Low power consumption
- . One red, one green and one blue chips in one package
- Package: 1000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- · RoHS compliant

APPLICATIONS


- Backlight
- Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes

 All dimensions are in millimeters (inches).
Tolerance is ±0.2(0.008") unless otherwise noted.
The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	lv (mcd) @ 20mA ^[2]		Viewing Angle ^[1]
			Min.	Тур.	201/2
APF3236SEEZGKQBKC	Hyper Red (AlGaInP)	Water Clear	80	140	
	Green (InGaN)		200	330	150°
	Blue (InGaN)		40	70	

Notes

1. 81/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
2. Luminous intensity / luminous flux: +/-15%.

3. Luminous intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Cumph al		Value		Unit
Parameter	Symbol	Emitting Color	Тур.	Max.	
Wavelength at Peak Emission I_F = 20mA	λ_{peak}	Hyper Red Green Blue	630 515 460	-	nm
Dominant Wavelength I _F = 20mA	λ_{dom} ^[1]	Hyper Red Green Blue	621 525 465	-	nm
Spectral Bandwidth at 50% Φ REL MAX I_{F} = 20mA	Δλ	Hyper Red Green Blue	20 35 25	-	nm
Capacitance	С	Hyper Red Green Blue	25 45 100	-	pF
Forward Voltage I _F = 20mA	V _F ^[2]	Hyper Red Green Blue	2.0 3.3 3.3	2.5 4.1 4.0	V
Reverse Current (V _R = 5V)	I _R	Hyper Red Green Blue	-	10 50 50	μA
Temperature Coefficient of λ_{peak} I_F = 20mA, -10°C $\leq T \leq 85^\circ C$	TC _{λpeak}	Hyper Red Green Blue	0.13 0.05 0.04	-	nm/°C
Temperature Coefficient of λ_{dom} I_F = 20mA, -10°C $\leq T \leq 85^\circ C$	TC _{λdom}	Hyper Red Green Blue	0.06 0.03 0.03	-	nm/°C
$\label{eq:lambda} \begin{array}{c} \mbox{Temperature Coefficient of } V_F & \\ I_F = 20mA, \ -10^\circ C \leq T \leq 85^\circ C & \\ \end{array} \qquad \qquad TC_V \\ \end{array}$		Hyper Red Green Blue	Green -3		mV/°C

Notes:

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd: ±1nm.)
Forward voltage: ±0.1V.
Wavelength value is traceable to CIE127-2007 standards.
Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C


Damastan	Symbol	Value			
Parameter		Hyper Red	Green	Blue	Unit
Power Dissipation	P _D	75	102.5	120	mW
Reverse Voltage	V _R	5	5	5	V
Junction Temperature	Tj	115	115	115	°C
Operating Temperature	T _{op}	-40 to +85			°C
Storage Temperature	T _{stg}	-40 to +85			°C
DC Forward Current	I _F	30	25	30	mA
Peak Forward Current	I _{FM} ^[1]	195	150	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	450	250	V
Thermal Resistance (Junction / Ambient)	R _{th JA} ^[2]	650	630	550	°C/W
Thermal Resistance (Junction / Solder point)	R _{th JS} ^[2]	500	540	450	°C/W

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. R_{th.JA}, R_{th.JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.


Kingbright

APF3236SEEZGKQBKC

TECHNICAL DATA




SPATIAL DISTRIBUTION





HYPER RED

GREEN


BLUE








Luminous Intensity vs. Ambient Temperature







T_a = 25 °C

2.5

2.0

1.5

1.0

0.5

0.0

2.5


Luminous intensity normalised at 20 mA 0.0 22 0.1 0.1 0.2 0.2

0 10 20 30 40 50


0 10

20 mA






Luminous Intensity vs. Ambient Temperature



Forward Current vs. Forward Voltage



Luminous Intensity vs. Forward Current


Forward current (mA)

T_a = 25 °C

20


Forward current (mA)

30 40 50




Luminous Intensity vs. Ambient Temperature

2.5




2.0 .0 .0 .0.5 .0.0 .40 -20 0 20 40 60 80 100 Ambient temperature (°C)




Kingbright

APF3236SEEZGKQBKC


REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS





REEL DIMENSION (units : mm)


TAPE SPECIFICATIONS (units : mm)



Notes

 Don't cause stress to the LEDs while it is exposed to high temperature.
The maximum number of reflow soldering passes is 2 times.
Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

XXXXXXXXXXX

- The information included in this document reflects representative usage scenarios and is intended for technical reference only
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2
- 3 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- 4. liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. 5
- The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright 6 All design applications should refer to Kingbright application notes available at https://www.Ki Notes