

W-Series
WEW 35/1**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|------------|----------------------------|
| Type | WEW 35/1 |
| Order No. | 1059000000 |
| Version | W-Series, End bracket |
| GTIN (EAN) | 4008190172282 |
| Qty. | 50 pc(s). |

W-Series
WEW 35/1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 12 mm | Width (inches) | 0.472 inch |
| Height | 56 mm | Height (inches) | 2.205 inch |
| Depth | 62.5 mm | Depth (inches) | 2.461 inch |
| Net weight | 36.3 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-2 | | |

System specifications

| | | | |
|---------|-------------------|------|-------|
| Version | For the terminals | Rail | TS 35 |
|---------|-------------------|------|-------|

Additional technical data

| | | | |
|---------------------|-----------------|-----------|------------------|
| Installation advice | Direct mounting | Interlock | for screw fixing |
| Type of mounting | when screwed in | | |

Conductors for clamping (rated connection)

| | | | |
|-------------------------|--------|-------------------------|--------|
| Tightening torque, max. | 2.4 Nm | Tightening torque, min. | 1.2 Nm |
|-------------------------|--------|-------------------------|--------|

Dimensions

| | |
|--------------|-------|
| TS 35 offset | 28 mm |
|--------------|-------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001041 | ETIM 4.0 | EC001041 |
| ETIM 5.0 | EC001041 | ETIM 6.0 | EC001041 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-08-10-03 |
| eClass 6.2 | 27-08-10-03 | eClass 7.1 | 27-08-10-03 |
| eClass 8.1 | 27-14-11-35 | eClass 9.0 | 27-14-11-35 |
| eClass 9.1 | 27-14-11-35 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| User Documentation | StorageConditionsTerminalBlocks |