

VEGAVIB S 61

Vibrating level switch for granulates

- Easy setup without adjustment
- Product-independent switching point
- Optimum rod design avoids buildup and jamming
- Easy cleaning
- Wear and maintenance free

Function

The vibrating rod of VEGAVIB is energized by a piezo crystal and it vibrates at a fixed amplitude. If the vibrating rod is covered by product, the amplitude change is detected by the integral electronics and converted into a switch signal. The switching condition is visible from outside via a two colour LED. No special adjustments are required to set up VEGAVIB S 61.

Area of application

VEGAVIB S 61 is used as a level switch in free flowing powders, granulates and coarse grained solids and detects reliably and accurately when a point level is reached. The optimum rod design avoids jamming and buildup of bulk solid material. It is ideal as a high or low level switch in a vessel detecting foodstuffs, perishable or granulate materials, which could be retained in a fork solids level probe.

Technical data

Process pressure	-1 ... 16 bar
Process temperature	-50 ... +150 °C
Density	≥ 100 g/l
Material housing	plastic PBT
Protection	IP 66/IP 67
Materials, wetted parts	316L
Approval	option: ATEX II 1/3 D IP6X T

Electronics transistor (NPN/PNP)

Load current	max. 400 mA
Turn-on voltage	max. 55 V DC
Supply voltage	10 ... 55 V DC
Power consumption	max. 0.5 W

Electronics double relay (DPDT)

Supply voltage	20 ... 253 V AC, 50/60 Hz, 20 ... 72 V DC
Power consumption	1 ... 8 VA (AC), approx. 1.3 W (DC)
Turn-on voltage	min. 10 mV / max. 253 V AC/DC
Switching current	min. 10 µA / max. 3 A AC, 1 A DC
Breaking capacity	max. 750 VA, 54 W

Accessories: Sliding lock fitting (extended versions) pressurised or unpressurised for adjustable switch point