

● ● ● Price index



**IPA Qualification Certificate:**  
Air Cleanless Class ISO Class 2  
(at v = 1 m/s) upon request



**UL94-V2**  
classifications



**Torsional**  
motion possible



**Special equipment:**  
Electrically conductive ESD/ATEX  
version upon request



Just push the cables into the e-chain®  
with your thumb - and it's ready



**When to use the Series E26/Z26:**

- If filling is required without opening and closing lids
- If price is an issue
- If quiet operation is required



**When not to use it:**

- For applications with very high loads and long unsupported travel lengths
  - ▶ Series 2600/2650/2680/2700 E2/000, page 5.182
- If an e-chain® is needed with a high locking crossbar
  - ▶ Series 2600/2650/2680/2700 E2/000, page 5.182

- ❶ Limited torsion tolerance
- ❷ Large pins for long service life
- ❸ Cable-friendly interior
- ❹ Integrated strain relief option
- ❺ "E" Series features split crossbar along the outer radius
- ❻ "Z" Series features split crossbar along the inner radius
- ❼ Dirt-repellent exterior
- ❽ Very easy to fill
- ❾ 1-, 2- or 3-chamber system available
- ❿ The patented push-button principle holds the links together



**Order example complete e-chain®**

Please indicate chain-lengths or number of links **Example: 1 m or 18 links**

1 m **E26.07.150.0**



**e-chain®**

1 set **2607.34PZB**



**Mounting bracket**





### Unsupported length

$FL_G$  = with straight upper run

$FL_B$  = with permitted sag



Further information ► Design, page 1.12



- $S$  = Length of travel
- $R$  = Bending radius
- $H$  = Nominal clearance height
- $H_F$  = Required clearance height
- $D$  = Overlength e-chain® radius in final position
- $K = \pi \cdot R + \text{"safety"}$

#### Other installation methods

- Vertical, hanging  $\leq 10$  m
- Vertical, standing  $\leq 1,5$  m
- Side mounted, un supp.  $\leq 0,5$  m
- Rotary requires further calculation
- Unsupported length of upper run = upon request



### Short travels - unsupported

Unsupported e-chains® feature positive camber over short travels. This must be accounted for when specifying the clearance height  $H_F$ . Please consult igus® if space is particularly restricted.

Pitch = 56 mm/link    Links/m = 18 (1.008 mm)    Chain length =  $S/2 + K$

R	063	075	100	125	150	175	200	250
$H^{+5}$	176	200	250	300	350	400	450	550
D	172	184	209	234	259	284	309	359
K	310	350	430	505	585	665	745	900

The required clearance height:  
 $H_F = H + 35$  mm  
(with 2,0 kg/m fill weight)

Speed / acceleration $FL_G$	max. 20 [m/s] / max. 200 [m/s <sup>2</sup> ]
Speed / acceleration $FL_B$	max. 3 [m/s] / max. 6 [m/s <sup>2</sup> ]
Gliding speed / acceleration (maximum)	max. 3 [m/s] / max. 10 [m/s <sup>2</sup> ]
Material (e-chain®)- permitted temperature °C	igumid NB / -40° up to +80° C
Material (mounting brackets)* - permitted temperature °C	igumid G / -40° up to +120° C
Flammability class (e-chain®), igumid NB	VDE 0304 IIC UL94 V2
Flammability class (mounting brackets), igumid G*	VDE 0304 IIC UL94 HB

\*Available in igumid NB upon request, please consult igus® for delivery time

### Technical Data




Details of material properties

► page 1.38

36,5

easy chain®  
Inner height: 36,5 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222



► page 3.5




Series Z26 - split crossbar along the inner radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
Z26.07.□.0	75	92	063	075 100 125 150 175 200 250	≈ 0,96

$B_a$ : pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.07.150.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18




Series Z26 - split crossbar along the inner radius with 2-chamber system

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
Z26.2/45.□.0	48/48	117	063	075 100 125 150 175 200 250	≈ 1,14

$B_a$ : pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.2/45.150.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18





Series Z26 - split crossbar along the inner radius with 3-chamber system

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii	Weight [kg/m]
Z26.3/45.□.0	47/48/47	167	063	075 100 125 150 175 200 250	≈ 1,30


$B_a$ : pin dimension approx. 0,3 - 0,5 mm wider!

Supplement Part No. with required radius. Example: Z26.3/45.150.0

0 = standard color, other colors ▶ page 1.39 · Pitch = 56 mm/link - Links/m = 18




Part No. structure




easy chain®  
Inner height: 36,5 mm

Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222




▶ page 3.5




**The Standard - option polymer - pivoting**

- Recommended for unsupported and gliding applications
- Well suited for tight installation conditions
- Strain relief with detachable tiwrap plates
- Variable traverse angle for flexible assembly
- The twistability of the e-chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options




Possible installation conditions for assembled mounting brackets ► Order example "preassembled" below

Moving end with bore  
(outer link) 26...3PZ(B)




26...4PZ(B) Fixed end  
with pin (inner link)




**Option polymer - locking**

- Recommended for unsupported and gliding applications
- Furthermore:**
  - At very high speed and/or acceleration
  - If space is limited for height (the  $H_F$  measurement)
  - The twistability of the e-chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options



Possible installation conditions for assembled mounting brackets ► Order example "preassembled" below

Moving end with bore  
(outer link) 26...1PZ(B)




26...2PZ(B) Fixed end  
with pin (inner link)

**Dimensions and order configurations**

Strain relief is possible on the moving end and/or the fixed end.

Part No. structure (pivoting)



Full set, for both ends:

2607. 34 PZB +tiwrap plate

Single-part order:


2607. 3 PZB +tiwrap plate

Mounting bracket with bore

2607. 4 PZB +tiwrap plate

Mounting bracket with pin

Part No. structure (locking)



Full set, for both ends:

2607. 12 PZB +tiwrap plate

Single-part order:

2607. 1 PZB +tiwrap plate

Mounting bracket with bore

2607. 2 PZB +tiwrap plate

Mounting bracket with pin

26...3PZ(B) Standard! (pivoting)


26...1PZ(B) (locking)

Moving end

Standard! (pivoting) 26...4PZ(B)

(locking) 26...2PZ(B)

Fixed end



For e-chain®	Part No. full set with tiwrap plate	Part No. tiwrap plate + 10 cable tiwraps	Part No. full set without tiwrap plate	Number of teeth	Dim. A [mm]
E26-Z26.07	2607. 34 PZB	2607. 34 PZBK1	2607. 34 PZ	7	55
E26-Z26.2/45	2610. 12 PZB	2610. 12 PZBK1	2610. 12 PZ	10	80
E26-Z26.3/45	2615. 15 PZB	2615. 15 PZBK1	2615. 15 PZ	15	130

Please add the Part No. with the requested index - 34 for the pivoting configuration

e.g. 2607. 34 PZB or 12 for the locking configuration e.g. 2607. 12 PZB

For the preassembled mode please add the index A1...A4 e.g. 2607. 34 PZB A1

igus GmbH  
51147 Cologne

Internet: www.igus.eu  
E-mail: info@igus.de

### Strain relief for polymer mounting brackets (pivoting or locking)

The strain relief tiwrap plates can be directly snapped onto the mounting bracket. After bolting the mounting brackets to the machine, the strain relief tiwrap plates are also firmly connected to the base. They do not need to be bolted on separately. Cable tiwraps secure the tiwrap plate "teeth" and the cable to provide proper strain relief and save time. **Details ▶ chapter 10**





Tiewrap plate	No. of teeth <i>n</i>	Dim. C [mm]	Dim. B [mm]	Center bore
3050.ZB	5	50	30	-
3075.ZB	7	75	55	-
3100.ZB	10	100	80	-
3115.ZB	11	115	95	-
3125.ZB	12	125	105	-
3150.ZB	15	150	130	-
3175.ZB	17	175	155	-
3200.ZB	20	200	180	+
3225.ZB	22	225	205	+
3250.ZB	25	250	230	+


(- = no / + = yes)

### Tiewrap plate as individual part

As individual component screwed on or can be plugged in the mounting brackets. **Details ▶ chapter 10**



Single tiewrap plate





Shown assembled

### Cable tiwraps as individual part

Cable tiwraps 100 pieces/bag	Width x length	Max. Ø	Tensile strength
CFB.001	4,8 x 150 mm	36 mm	222 N



Other strain relief elements - optional ▶ chapter 10



▶ chapter 10



▶ page 3.5