

Feature

1. Built-in controller Samsung-(KS0107 · KS0108 or equivalent)

- 2. +5V power supply
- 3. 1/64 duty cycle
- 4.N.V. Built-in

(and)

		And and a second se
Pin NO.	Symbol	Function
1	Vss	GND
2	Vdd	Power supply (+5V)
3	Vo	Contrast Adjustment
4	D/I	Data/instruction
5	R/W	Data read/write
6	Ę	H→L Enable signal
7	DB0	Data bus line
8	DB1	Data bus line
9	DB2	Data bus line
10	DB3	Data bus line
11	DB4	Data bus line
12	DB5	Data bus line
13	DB6	Data bus line
14	DB7	Data bus line
15	CS1	Chip select for IC1
16	CS2	Chip select for IC2
17 RST		Reset
18	Vee	Negative voltage output
19	А	Power supply for LED+(4.2V)RA=O Ω
20	к	Power supply for LED (0V)

Mechanical Data

			-
5	Item	Standard Value	Unit
	Module Dimension	93.0x70.0	mm
	Viewing Area	72.0x40.0	mm
	Mounting hole	88.0x65.0	mm
	Dot Pitch	0.52x0.52	mm

Absolute Maximum Rating

ltom	Cumhal	Stan	11			
ltem	Symbol	min.	typ.	max.	Unit	
Power Supply	VDD-VSS	4.75	5.0	5.25	V	
Input Voltage	VI	-0.3		VDD	V	

Note : VSS=0 Volt, VDD=5.0 Volt.

Electronical Characteristics

ltem	Symbol	Condition	Standard Value			
item	Symbol	Condition	min.	typ.	max.	Unit
Innut Valtage	VDD	L level	0.7VDD		V _{DD}	V
Input Voltage	vio	H level	0		$0.3V_{DD}$	V
Supply Current	IDD	VDD=5V		2.5	7.5	m
	VDD-V0	-20°C	9.9	10.4	10.9	V
Recommended LC Driving		0°C	9.7	10.2	10.7	
Voltage for Normal Temp.		25°C	8.9	9.4	9.9	
Venter medule		50°C	8.6	9.1	9.6	
Version module		70°C	8.4	8.9	9.4	
LED Forward Voltage	VF	25°C		4.2	4.6	V
	IF	25°C Array		330	660	
LED Forward Current		25 C Edge		120	240	mΑ
EL Power Supply Current	IEL	Vel=110VAC;400Hz			5.0	m



