

MULTILAYER CERAMIC CAPACITORS/AXIAL & RADIAL LEADED

Multilayer ceramic capacitors are available in a variety of physical sizes and configurations, including leaded devices and surface mounted chips. Leaded styles include molded and conformally coated parts with axial and radial leads. However, the basic capacitor element is similar for all styles. It is called a chip and consists of formulated dielectric materials which have been cast into thin layers, interspersed with metal electrodes alternately exposed on opposite

edges of the laminated structure. The entire structure is fired at high temperature to produce a monolithic block which provides high capacitance values in a small physical volume. After firing, conductive terminations are applied to opposite ends of the chip to make contact with the exposed electrodes. Termination materials and methods vary depending on the intended use.

TEMPERATURE CHARACTERISTICS

Ceramic dielectric materials can be formulated with a wide range of characteristics. The EIA standard for ceramic dielectric capacitors (RS-198) divides ceramic dielectrics into the following classes:

Class I: Temperature compensating capacitors, suitable for resonant circuit application or other applications where high Q and stability of capacitance characteristics are required. Class I capacitors have predictable temperature coefficients and are not affected by voltage, frequency or time. They are made from materials which are not ferro-electric, yielding superior stability but low volumetric efficiency. Class I capacitors are the most stable type available, but have the lowest volumetric efficiency.

Class II: Stable capacitors, suitable for bypass or coupling applications or frequency discriminating circuits where Q and stability of capacitance characteristics are not of major importance. Class II capacitors have temperature characteristics of \pm 15% or less. They are made from materials which are ferro-electric, yielding higher volumetric efficiency but less stability. Class II capacitors are affected by temperature, voltage, frequency and time.

Class III: General purpose capacitors, suitable for by-pass coupling or other applications in which dielectric losses, high insulation resistance and stability of capacitance characteristics are of little or no importance. Class III capacitors are similar to Class II capacitors except for temperature characteristics, which are greater than \pm 15%. Class III capacitors have the highest volumetric efficiency and poorest stability of any type.

KEMET leaded ceramic capacitors are offered in the three most popular temperature characteristics:

COG: Class I, with a temperature coefficient of 0 ± 30 ppm per degree C over an operating temperature range of - 55°C to + 125°C (Also known as "NP0").

X7R: Class II, with a maximum capacitance change of \pm 15% over an operating temperature range of - 55°C to + 125°C.

Z5U: Class III, with a maximum capacitance change of + 22% - 56% over an operating temperature range of + 10°C to + 85°C.

Specified electrical limits for these three temperature characteristics are shown in Table 1.

SPECIFIED ELECTRICAL LIMITS

Parameter	Temp	Temperature Characteristics		
r at afficter	C0G	X7R	Z5U	
Dissipation Factor: Measured at following conditions. COG – 1 kHz and 1 vrms if capacitance >1000pF 1 MHz and 1 vrms if capacitance ≤ 1000 pF X7R – 1 kHz and 1 vrms* or if extended cap range 0.5 vrms Z5U – 1 kHz and 0.5 vrms	0.10%	2.5% (3.5% @ 25V)	4.0%	
Dielectric Stength: 2.5 times rated DC voltage.	Р	Pass Subsequent IR Test		
Insulation Resistance (IR): At rated DC voltage, whichever of the two is smaller	1,000 MΩ–μF or 100 GΩ	1,000 MΩ–μF or 100 GΩ	1,000 MΩ–μF or 10 GΩ	
Temperature Characteristics: Range, °C Capacitance Change without DC voltage	-55 to +125 0 ± 30 ppm/°C	-55 to +125 ± 15%	+ 10 to +85 +22%,-56%	

^{*} MHz and 1 vrms if capacitance ≤ 100 pF on military product.

APPLICATION NOTES FOR MULTILAYER CERAMIC CAPACITORS

ELECTRICAL CHARACTERISTICS

The fundamental electrical properties of multilayer ceramic capacitors are as follows:

Polarity: Multilayer ceramic capacitors are not polar, and may be used with DC voltage applied in either direction.

Rated Voltage: This term refers to the maximum continuous DC working voltage permissible across the entire operating temperature range. Multilayer ceramic capacitors are not extremely sensitive to voltage, and brief applications of voltage above rated will not result in immediate failure. However, reliability will be reduced by exposure to sustained voltages above rated.

Capacitance: The standard unit of capacitance is the farad. For practical capacitors, it is usually expressed in microfarads (10-6 farad), nanofarads (10-9 farad), or picofarads (10⁻¹² farad). Standard measurement conditions are as follows:

Class I (up to 1,000 pF): 1MHz and 1.2 VRMS


maximum.

Class I (over 1,000 pF): 1kHz and 1.2 VRMS

maximum.

Class II: 1 kHz and 1.0 \pm 0.2 VRMS. Class III: 1 kHz and 0.5 \pm 0.1 VRMS.

Like all other practical capacitors, multilayer ceramic capacitors also have resistance and inductance. A simplified schematic for the equivalent circuit is shown in Figure 1. Other significant electrical characteristics resulting from these additional properties are as follows:



C = Capacitance

R_S = Equivalent Series Resistance (ESR)

L = Inductance

R_D = Insulation Resistance (IR)

Impedance: Since the parallel resistance (Rp) is normally very high, the total impedance of the capacitor is:

$$Z = \sqrt{R_S^2 + (X_C - X_L)^2}$$

Where Z = Total Impedance


RS = Equivalent Series Resistance

 X_{C} = Capacitive Reactance = $\frac{1}{2\pi fC}$

 X_1 = Inductive Reactance = $2\pi fL$

The variation of a capacitor's impedance with frequency determines its effectiveness in many applications.

Dissipation Factor: Dissipation Factor (DF) is a measure of the losses in a capacitor under AC application. It is the ratio of the equivalent series resistance to the capacitive reactance, and is usually expressed in percent. It is usually measured simultaneously with capacitance, and under the same conditions. The vector diagram in Figure 2 illustrates the relationship between DF, ESR, and impedance. The reciprocal of the dissipation factor is called the "Q", or quality factor. For convenience, the "Q" factor is often used for very low values of dissipation factor. DF is sometimes called the "loss tangent" or "tangent δ ", as derived from this diagram.



Insulation Resistance: Insulation Resistance (IR) is the DC resistance measured across the terminals of a capacitor, represented by the parallel resistance (Rp) shown in Figure 1. For a given dielectric type, electrode area increases with capacitance, resulting in a decrease in the insulation resistance. Consequently, insulation resistance is usually specified as the "RC" (IR x C) product, in terms of ohm-farads or megohm-microfarads. The insulation resistance for a specific capacitance value is determined by dividing this product by the capacitance. However, as the nominal capacitance values become small, the insulation resistance calculated from the RC product reaches values which are impractical. Consequently, IR specifications usually include both a minimum RC product and a maximum limit on the IR calculated from that value. For example, a typical IR specification might read "1,000 megohm-microfarads or 100 gigohms, whichever is less."

Insulation Resistance is the measure of a capacitor to resist the flow of DC leakage current. It is sometimes referred to as "leakage resistance." The DC leakage current may be calculated by dividing the applied voltage by the insulation resistance (Ohm's Law).

Dielectric Withstanding Voltage: Dielectric withstanding voltage (DWV) is the peak voltage which a capacitor is designed to withstand for short periods of time without damage. All KEMET multilayer ceramic capacitors will withstand a test voltage of 2.5 x the rated voltage for 60 seconds.

KEMET specification limits for these characteristics at standard measurement conditions are shown in Table 1 on page 4. Variations in these properties caused by changing conditions of temperature, voltage, frequency, and time are covered in the following sections.



APPLICATION NOTES FOR MULTILAYER CERAMIC CAPACITORS

TABLE 1 EIA TEMPERATURE CHARACTERISTIC CODES FOR CLASS I DIELECTRICS

Significant Figure of Temperature Coefficient		Multiplier Applied to Temperature Coefficient		Tolerance of Temperature Coefficient *		
	PPM per Degree C	Letter Symbol	Multi- plier	Number Symbol	PPM per Degree C	Letter Symbol
	0.0		-1	0	±30	
	0.3	В	-10	1	±60	Н
	0.9	Α	-100	2	±120	J
	1.0	M	-1000	3	±250	K
	1.5	Р	-100000	4	±500	L
	2.2	R	+1	5	±1000	M
	3.3	S	+10	6	±2500	Ν
	4.7	Τ	+100	7		
	7.5	U	+1000	8		
			+10000	9		
*	Those our	antrinal tala	ranaga annl	. +0 0 +	naint maaa	.vomont

^{*} These symetrical tolerances apply to a two-point measurement of temperature coefficient: one at 25°C and one at 85°C. Some deviation is permitted at lower temperatures. For example, the PPM tolerance for COG at -55°C is +30 / -72 PPM.

TABLE 2 EIA TEMPERATURE CHARACTERISTIC CODES FOR CLASS II & III DIELECTRICS

	w Temperature High Temperature Maximum Capa Rating Rating Shift		•		•
Degree Celcius	Letter Symbol	Degree Celcius	Number Symbol	Percent	Letter Symbol
+10C	Z	+45C	2	±1.0%	Α
-30C	Υ	+65C	4	±1.5%	В
-55C	Χ	+85C	5	±2.2%	С
		+105C	6	±3.3%	D
		+125C	7	±4.7%	Ε
		+150C	8	±7.5%	F
		+200C	9	±10.0%	Р
				±15.0%	R
				±22.0%	S
				+22/-33%	Τ
				+22/-56%	U
				+22/-82%	V

EFFECT OF TEMPERATURE




Figure 3. Temperature °C Capacitance & DF vs Temperature - C0G




Figure 4. Temperature °C Capacitance & DF vs Temperature - X7R




Figure 5. Temperature °C Capacitance & DF vs Temperature - Z5U

APPLICATION NOTES FOR MULTILAYER CERAMIC CAPACITORS

EFFECT OF APPLIED VOLTAGE




Figure 6. AC or DC Volts Applied

Typical Effects of 1000 Hz AC and DC Voltage Level on

Capacitance and Dissipation Factor - X7R

Note: COG Dielectric capacitance and dissipation factor are stable with voltage.




Figure 7. AC or DC Volts Applied

Typical Effects of 1000 Hz AC and DC Voltage Level on

Capacitance and Dissipation Factor - Z5U

Note: COG Dielectric capacitance and dissipation factor are stable with voltage.

Effect of Temperature: Both capacitance and dissipation factor are affected by variations in temperature. The maximum capacitance change with temperature is defined by the temperature characteristic. However, this only defines a "box" bounded by the upper and lower operating temperatures and the minimum and maximum capacitance values. Within this "box", the variation with temperature depends upon the specific dielectric formulation. Typical curves for KEMET capacitors are shown in Figures 3, 4, and 5. These figures also include the typical change in dissipation factor for KEMET capacitors.

Insulation resistance decreases with temperature. Typically, the insulation resistance at maximum rated temperature is 10% of the 25°C value.

Effect of Voltage: Class I ceramic capacitors are not affected by variations in applied AC or DC voltages. For Class II and III ceramic capacitors, variations in voltage affect only the capacitance and dissipation factor. The application of DC voltage higher than 5 vdc reduces both the capacitance and dissipation factor. The application of AC voltages up to 10-20 Vac tends to increase both capacitance and dissipation factor.

At higher AC voltages, both capacitance and dissipation factor begin to decrease.

Typical curves showing the effect of applied AC and DC voltage are shown in Figure 6 for KEMET X7R capacitors and Figure 7 for KEMET Z5U capacitors.

Effect of Frequency: Frequency affects both capacitance and dissipation factor. Typical curves for KEMET multilayer ceramic capacitors are shown in Figures 8 and 9.

The variation of impedance with frequency is an important consideration in the application of multilayer ceramic capacitors. Total impedance of the capacitor is the vector of the capacitive reactance, the inductive reactance, and the ESR, as illustrated in Figure 2. As frequency increases, the capacitive reactance decreases. However, the series inductance (L) shown in Figure 1 produces inductive reactance, which increases with frequency. At some frequency, the impedance ceases to be capacitive and becomes inductive. This point, at the bottom of the V-shaped impedance versus frequency curves, is the self-resonant frequency. At the self-resonant frequency, the reactance is zero, and the impedance consists of the ESR only.

Typical impedance versus frequency curves for KEMET multilayer ceramic capacitors are shown in Figures 10, 11, and 12. These curves apply to KEMET capacitors in chip form, without leads. Lead configuration and lead length have a significant impact on the series inductance. The lead inductance is approximately 10nH/inch, which is large compared to the inductance of the chip. The effect of this additional inductance is a decrease in the self-resonant frequency, and an increase in impedance in the inductive region above the self-resonant frequency.

Effect of Time: The capacitance of Class II and III dielectrics change with time as well as with temperature, voltage and frequency. This change with time is known as "aging." It is caused by gradual realignment of the crystalline structure of the ceramic dielectric material as it is cooled below its Curie temperature, which produces a loss of capacitance with time. The aging process is predictable and follows a logarithmic decay. Typical aging rates for COG, X7R, and Z5U dielectrics are as follows:

COG None
X7R 2.0% per decade of time
Z5U 5.0% per decade of time

Typical aging curves for X7R and Z5U dielectrics are shown in Figure 13.

The aging process is reversible. If the capacitor is heated to a temperature above its Curie point for some period of time, de-aging will occur and the capacitor will regain the capacitance lost during the aging process. The amount of deaging depends on both the elevated temperature and the length of time at that temperature. Exposure to 150°C for one-half hour or 125°C for two hours is usually sufficient to return the capacitor to its initial value.

Because the capacitance changes rapidly immediately after de-aging, capacitance measurements are usually delayed for at least 10 hours after the de-aging process, which is often referred to as the "last heat." In addition, manufacturers utilize the aging rates to set factory test limits which will bring the capacitance within the specified tolerance at some future time, to allow for customer receipt and use. Typically, the test limits are adjusted so that the capacitance will be within the specified tolerance after either 1,000 hours or 100 days, depending on the manufacturer and the product type.



APPLICATION NOTES FOR MULTILAYER CERAMIC CAPACITORS

POWER DISSIPATION

Power dissipation has been empirically determined for two representative KEMET series: C052 and C062. Power dissipation capability for various mounting configurations is shown in Table 3. This table was extracted from Engineering Bulletin F-2013, which provides a more detailed treatment of this subject.

Note that no significant difference was detected between the two sizes in spite of a 2 to 1 surface area ratio. Due to the materials used in the construction of multilayer ceramic capacitors, the power dissipation capability does not depend greatly on the surface area of the capacitor body, but rather on how well heat is conducted out of the capacitor lead wires. Consequently, this power dissipation capability is applicable to other leaded multilayer styles and sizes.

TABLE 3 POWER DISSIPATION CAPABILITY (Rise in Celsius degrees per Watt)

Mounting Configuration	Power Dissipation of C052 & C062
1.00" leadwires attached to binding post of GR-1615 bridge (excellent heat sink)	90 Celsius degrees rise per Watt ±10%
0.25" leadwires attached to binding post of GR-1615 bridge	55 Celsius degrees rise per Watt ±10%
Capacitor mounted flush to 0.062" glass- epoxy circuit board with small copper traces	77 Celsius degrees rise per Watt ±10%
Capacitor mounted flush to 0.062" glass- epoxy circuit board with four square inches of copper land area as a heat sink	53 Celsius degrees rise per Watt ±10%

As shown in Table 3, the power dissipation capability of the capacitor is very sensitive to the details of its use environment. The temperature rise due to power dissipation should not exceed 20°C. Using that constraint, the maximum permissible power dissipation may be calculated from the data provided in Table 3.

It is often convenient to translate power dissipation capability into a permissible AC voltage rating. Assuming a sinusoidal wave form, the RMS "ripple voltage" may be calculated from the following formula:

$$E = Z \times \sqrt{\frac{P_{MAX}}{R}}$$

Where E = RMS Ripple Voltage (volts)

P = Power Dissipation (watts)

Z = Impedance

R = ESR

The data necessary to make this calculation is included in Engineering Bulletin F-2013. However, the following criteria must be observed:

- 1. The temperature rise due to power dissipation should be limited to 20°C.
- The peak AC voltage plus the DC voltage must not exceed the maximum working voltage of the capacitor.

Provided that these criteria are met, multilayer ceramic

capacitors may be operated with AC voltage applied without need for DC bias.

RELIABILITY

A well constructed multilayer ceramic capacitor is extremely reliable and, for all practical purposes, has an infinite life span when used within the maximum voltage and temperature ratings. Capacitor failure may be induced by sustained operation at voltages that exceed the rated DC voltage, voltage spikes or transients that exceed the dielectric withstanding voltage, sustained operation at temperatures above the maximum rated temperature, or the excessive temperature rise due to power dissipation.

Failure rate is usually expressed in terms of percent per 1,000 hours or in FITS (failure per billion hours). Some KEMET series are qualified under U.S. military established reliability specifications MIL-PRF-20, MIL-PRF-123, MIL-PRF-39014, and MIL-PRF-55681. Failure rates as low as 0.001% per 1,000 hours are available for all capacitance / voltage ratings covered by these specifications. These specifications and accompanying Qualified Products List should be consulted for details.

For series not covered by these military specifications, an internal testing program is maintained by KEMET Quality Assurance. Samples from each week's production are subjected to a 2,000 hour accelerated life test at 2 x rated voltage and maximum rated temperature. Based on the results of these tests, the average failure rate for all non-military series covered by this test program is currently 0.06% per 1,000 hours at maximum rated conditions. The failure rate would be much lower at typical use conditions. For example, using MIL-HDBK-217D this failure rate translates to 0.9 FITS at 50% rated voltage and 50°C.

Current failure rate details for specific KEMET multilayer ceramic capacitor series are available on request.

MISAPPLICATION

Ceramic capacitors, like any other capacitors, may fail if they are misapplied. Typical misapplications include exposure to excessive voltage, current or temperature. If the dielectric layer of the capacitor is damaged by misapplication the electrical energy of the circuit can be released as heat, which may damage the circuit board and other components as well.

If potential for misapplication exists, it is recommended that precautions be taken to protect personnel and equipment during initial application of voltage. Commonly used precautions include shielding of personnel and sensing for excessive power drain during board testing.

STORAGE AND HANDLING

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature – reels may soften or warp, and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40° C, and maximum storage humidity not exceed 70% relative humidity. In addition, temperature fluctuations should be minimized to avoid condensation on the parts, and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability, chip stock should be used promptly, preferably within 1.5 years of receipt.

APPLICATION NOTES FOR MULTILAYER CERAMIC CAPACITORS

10M

Figure 8. Frequency - Hertz
Capacitance & DF vs Frequency - C0G




Figure 9. Frequency - Hertz
Capacitance & DF vs Frequency - X7R & Z5U




Figure 13. Typical Aging Rates for X7R & Z5U

IMPEDANCE VS FREQUENCY




Figure 10. Impedance vs Frequency for C0G Dielectric




Figure 11. Impedance vs Frequency for X7R Dielectric




Figure 12. Impedance vs Frequency for Z5U Dielectric

Ceramic Molded xial/Radial - Standard

CERAMIC MOLDED AXIAL & RADIAL

PERFORMANCE CHARACTERISTICS

GENERAL SPECIFICATIONS

Working Voltage:

C0G - 50, 100, 200 X7R - 50, 100, 200

Temperature Characteristics:

C0G 0 \pm 30 PPM / °C from -55°C to +125°C X7R \pm 15% from -55°C to +125°C

Capacitance Tolerance:

COG ±0.5pF, ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF is tightest tolerance available) X7R ±10%, ±20%, -0 +100%, +80% / -20%

Construction:

Monolithic block of ceramic dielectric with Interdigitated internal electrodes, encapsulated in a molded case, and having axial or radial leads. Meets flame test requirements of UL Standard 94V-0.

Lead Material:

Axial: Solder coated copper clad steel Radial: Solder-coated copper standard (100% tin plated optional)

Solderability:

MIL-STD-202, Method 208, Sn62 solder, 245°C for $5 \pm 1/2$ seconds.

Terminal Strength:

EIA-198 Method 303, Condition A (2.2 kg)

ELECTRICAL

Capacitance:

Within specified tolerance and when measured with 1 volt rms at 1kHz (1000 pF or less at 1 MHz for C0G).

Dissipation Factor @25°C:

25°C at 1kHz (1000 pF or less at 1 MHz for C0G). C0G – 0.15% maximum X7R – 2.5% maximum

Insulation Resistance:


After 2 minutes electrification at 25°C and rated voltage C0G – 100K $M\Omega$ or 1000 $M\Omega$ – $\mu F,$ whichever is less. X7R – 100K $M\Omega$ or 1000 $M\Omega$ – $\mu F,$ whichever is less.

Dielectric Withstanding Voltage:

250% of rated voltage for 5 seconds with current limited to 50 mA at 25°C.




CAPACITOR OUTLINE DRAWINGS — (AXIAL LEADS)



DIMENSIONS — INCHES (MILLIMETERS)

Case Size	Military Equivalent Styles	L Length	D Body diameter	C Lead Diameter
C114	CC75, CCR75 CK12, CKR11	.160 ± .010 (4.06 ± .25)	.090 ± .010 (2.29 ± .25)	.020, +.000,003 (.51, +.00,08)
C124	CC76, CCR76 CK13, CKR12	.250 ± .010 (6.35 ± .25)	.090 ± .010 (2.29 ± .25)	.020, +.000,003 (.51, +.00,08)
C192	CC77, CCR77 CK14, CKR14	.390 ± .010 (9.91 ± .25)	.140 ± .010 (3.56 ± .25)	.025, +.004,001 (.64, +.10,025)
C202	CC78, CCR78 CK15, CKR15	.500 ± .020 (12.70 ± .51)	.250 ± .015 (6.35 ± .38)	.025, +.004,001 (.64, +.10,025)
C222	CC79, CCR79 CK16, CKR16	.690 ± .030 (17.53 ± .76)	.350 ± .020 (8.89 ± .51)	.025, +.004,001 (.64, +.10,025)


CAPACITOR OUTLINE DRAWINGS — (RADIAL LEADS)



DIMENSIONS — INCHES (MILLIMETERS)

Case Size	Military Equivalent Styles	H Height	L Length	W Width	S Lead Spacing
C052	CC05, CCR05 CK05, CKR05	.190 ± .010 (4.83 ± .25)	.190 ± .010 (4.83 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)
C062	CC06, CCR06 CK06, CKR06	.290 ± .010 (7.37 ± .25)	.290 ± .010 (7.37 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)
C512	CC07, CCR07	.480 ± .020 (12.19 ± .51)	.480 ± .020 (12.19 ± .51)	.140 ± .010 (3.56 ± .25)	.400 ± .020 (10.16 ± .51)
C522	CC08, CCR08	.480 ± .020 (12.19 ± .51)	.480 ± .020 (12.19 ± .51)	.240 ± .010 (6.10 ± .25)	.400 ± .020 (10.16 ± .51)

For packaging information, see pages 46, 47 and 48.



Standard tolerances for each Series are shown in the repetitive parts lists.

Case Sizes	
Radial	Axial
C052	C114
C062	C124
C512	C192
C522	C202
	C222

Part Number Example: C052C102K2R5TA (14 digits - no spaces)


2 - 200V; 1 - 100V; 5 - 50V

AXIAL CAPACITOR MARKING

STANDARD C114C, C124C, C192C, C202C & C222C

KC0G	KEMET, Temperature Characteristic
101J	Capacitance, Capacitance Tolerance
200V	Voltage
0812	——Date Code

RADIAL CAPACITOR MARKING C052C & C062C STANDARD MARKING



C512 & C522 STANDARD MARKING

KEMET C512X7R	KEMET SIZE and Temperature Characteristic
105K 50V	————Capacitance, Capacitance Tolerance, Voltage
0832	———Date Code



ULTRA-STABLE TEMPERATURE CHARACTERISTIC—COG (NPO)

RATINGS & PART NUMBER REFERENCE

OADAOITANOE	LEMET
CAPACITANCE	KEMET
pF	PART NUMBER
	14 STANDARD COG
1.0	C114C109(<u>1</u>)2G5CA
1.5	C114C159(<u>1</u>)2G5CA
2.2	C114C229(<u>1</u>)2G5CA
2.7	C114C279(<u>1</u>)2G5CA
3.3	C114C339(<u>1</u>)2G5CA
3.9	C114C399(<u>1</u>)2G5CA
4.7	C114C479(<u>1</u>)2G5CA
5.6	C114C569(<u>1</u>)2G5CA
6.8	C114C689(<u>1</u>)2G5CA
8.2	C114C829(<u>1</u>)2G5CA
10.0	C114C100(<u>2</u>)2G5CA
12.0	C114C120(<u>2</u>)2G5CA
15.0	C114C150(<u>2</u>)2G5CA
18.0	C114C180(<u>2</u>)2G5CA
22.0	C114C220(<u>2</u>)2G5CA
27.0	C114C270(<u>3</u>)2G5CA
33.0	C114C330(<u>3</u>)2G5CA
39.0	C114C390(<u>3</u>)2G5CA
47.0	C114C470(<u>3</u>)2G5CA
56.0	C114C560(<u>4</u>)2G5CA
68.0	C114C680(<u>4</u>)2G5CA
82.0	C114C820(<u>4</u>)2G5CA
100.0	C114C101(<u>4</u>)2G5CA
120.0	C114C121(<u>4</u>)2G5CA
150.0	C114C151(<u>4</u>)2G5CA
180.0	C114C181(<u>4</u>)2G5CA
220.0	C114C221(<u>4</u>)2G5CA
270.0	C114C271(<u>4</u>)2G5CA
330.0	C114C331(<u>4</u>)2G5CA
	14 STANDARD COG
82.0	C114C820(<u>4</u>)1G5CA
100.0	C114C101(<u>4</u>)1G5CA
120.0	C114C121(<u>4</u>)1G5CA
150.0	C114C151(<u>4</u>)1G5CA
180.0	C114C181(<u>4</u>)1G5CA
220.0	C114C221(<u>4</u>)1G5CA
270.0	C114C271(<u>4</u>)1G5CA
330.0	C114C331(<u>4</u>)1G5CA
390.0	C114C391(<u>4</u>)1G5CA
470.0	C114C471(<u>4</u>)1G5CA
560.0	C114C561(<u>4</u>)1G5CA
680.0	C114C681(<u>4</u>)1G5CA

NOTE 1:	Insert proper symbol for capacitance tolerance as
	follows:

- (1) 1.0 pF to 8.2 pF: D— ±.5 pF (2) 10.0 pF to 22 pF: J— ±5%, K— ±10% (3) 27.0 pF to 47 pF: G— ±2%, J— ±5%, K— ±10% (4) 56.0 pF and up: F— ±1%,G— ±2%, J— ±5%, K— ±10%

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT – C	124 STANDARD COG
390.0	C124C391(4)2G5CA
470.0	C124C471(<u>4</u>)2G5CA
560.0	C124C561(<u>4</u>)2G5CA
100 VOLT – C	124 STANDARD COG
820.0	C124C821(<u>4</u>)1G5CA
1,000.0	C124C102(<u>4</u>)1G5CA
200 VOLT - C	192 STANDARD COG
680.0	C192C681(4)2G5CA
820.0	C192C821(<u>4</u>)2G5CA
1,000.0	C192C102(<u>4</u>)2G5CA
1,200.0	C192C122(<u>4</u>)2G5CA
1,500.0	C192C152(<u>4</u>)2G5CA
1,800.0	C192C182(<u>4</u>)2G5CA
2,200.0	C192C222(<u>4</u>)2G5CA
2,700.0	C192C272(<u>4</u>)2G5CA
3,300.0	C114C332(<u>4</u>)2G5CA
3,900.0	C114C392(<u>4</u>)2G5CA
4,700.0	C114C472(<u>4</u>)2G5CA
100 VOLT – C	192 STANDARD COG
1,200.0	C192C122(4)1G5CA
1,500.0	C192C152(<u>4</u>)1G5CA
1,800.0	C192C182(4)1G5CA
2,200.0	C192C222(<u>4</u>)1G5CA
2,700.0	C192C272(4)1G5CA
3,300.0	C192C332(<u>4</u>)1G5CA
3,900.0	C192C392(4)1G5CA
4,700.0	C192C472(<u>4</u>)1G5CA
5,600.0	C192C562(4)1G5CA
6,800.0	C192C682(<u>4</u>)1G5CA
8,200.0	C192C822(<u>4</u>)1G5CA
NOTE 1: Insert proper syn	nbol for capacitance tolerance as

NOTE 1: Insert proper symbol for capacitance tolerance as follows:

- (1) 1.0 pF to 8.2 pF: D— ±.5 pF

- (2) 10.0 pF to 22 pF: $y = \pm 5\%$, $y = \pm 10\%$ (3) 27.0 pF to 47 pF: $y = \pm 2\%$, $y = \pm 5\%$, $y = \pm 10\%$ (4) 56.0 pF and up: $y = \pm 1\%$, $y = \pm 1\%$, $y = \pm 10\%$

CAPACITANCE pF	KEMET PART NUMBER		
200 VOLT – C2	202 STANDARD COG		
5,600.0	C202C562(4)2G5CA		
6,800.0	C202C682(4)2G5CA		
8,200.0	C202C822(4)2G5CA		
10,000.0	C202C103(<u>4</u>)2G5CA		
12,000.0	C202C123(<u>4</u>)2G5CA		
15,000.0	C202C153(<u>4</u>)2G5CA		
18,000.0	C202C183(<u>4</u>)2G5CA		
22000.0	C202C223(<u>4</u>)2G5CA		
100 VOLT - C2	202 STANDARD COG		
10,000.0	C202C103(<u>4</u>)1G5CA		
12,000.0	C202C123(<u>4</u>)1G5CA		
15,000.0	C202C153(<u>4</u>)1G5CA		
18,000.0	C202C183(<u>4</u>)1G5CA		
22,000.0	C202C223(<u>4</u>)1G5CA		
27,000.0	C202C273(<u>4</u>)1G5CA		
33,000.0	C202C333(<u>4</u>)1G5CA		
200 VOLT - C222 STANDARD C0G			
27,000.0	C222C273(<u>4</u>)2G5CA		
33,000.0	C222C333(<u>4</u>)2G5CA		
39,000.0	C222C393(<u>4</u>)2G5CA		
47,000.0	C222C473(<u>4</u>)2G5CA		
100 VOLT – C2	222 STANDARD COG		
39,000.0	C222C393(<u>4</u>)1G5CA		
47,000.0	C222C473(<u>4</u>)1G5CA		
56,000.0	C222C563(<u>4</u>)1G5CA		
68,000.0	C222C683(<u>4</u>)1G5CA		
82,000.0	C222C823(<u>4</u>)1G5CA		
100,000.0	C222C104(<u>4</u>)1G5CA		
NOTE 1: Insert proper sym	nbol for capacitance tolerance as		

follows:

- (1) 1.0 pF to 8.2 pF: D— ±.5 pF

- (2) 10.0 pF to 22 pF: $J = \pm 5\%$, $K = \pm 10\%$ (3) 27.0 pF to 47 pF: $G = \pm 2\%$, $J = \pm 5\%$, $K = \pm 10\%$ (4) 56.0 pF and up: $F = \pm 1\%$, $G = \pm 2\%$, $J = \pm 5\%$, $K = \pm 10\%$

ULTRA-STABLE TEMPERATURE CHARACTERISTIC—COG (NPO)

RATINGS & PART NUMBER REFERENCE

CAPACITANCE	KEMET
pF	PART NUMBER
	- C052 SIZE C0G
1.0	C052C109(1)2G5CA
1.5	C052C159(<u>1</u>)2G5CA
2.2	C052C229(<u>1</u>)2G5CA
2.7	C052C279(<u>1</u>)2G5CA
3.3	C052C339(<u>1</u>)2G5CA
3.9	C052C399(1)2G5CA
4.7	C052C479(<u>1</u>)2G5CA
5.6	C052C569(<u>1</u>)2G5CA
6.8	C052C689(<u>1</u>)2G5CA
8.2	C052C829(<u>1</u>)2G5CA
10.0	C052C029(1)2C3CA C052C100(2)2G5CA
12.0	C052C120(2)2G5CA
15.0	C052C120(<u>2</u>)2G5CA C052C150(<u>2</u>)2G5CA
	·—·
18.0	C052C180(<u>2</u>)2G5CA
22.0	C052C220(<u>2</u>)2G5CA
27.0	C052C270(<u>3</u>)2G5CA
33.0	C052C330(<u>3</u>)2G5CA
39.0	C052C390(<u>3</u>)2G5CA
47.0	C052C470(<u>3</u>)2G5CA
56.0	C052C560(<u>4</u>)2G5CA
68.0	C052C680(<u>4</u>)2G5CA
82.0	C052C820(<u>4</u>)2G5CA
100.0	C052C101(<u>4</u>)2G5CA
120.0	C052C121(<u>4</u>)2G5CA
150.0	C052C151(4)2G5CA
180.0	C052C181(<u>4</u>)2G5CA
220.0	C052C221(<u>4</u>)2G5CA
270.0	C052C271(<u>4</u>)2G5CA
330.0	C052C331(<u>4</u>)2G5CA
390.0	C052C391(4)2G5CA
470.0	C052C471(4)2G5CA
560.0	C052C561(<u>4</u>)2G5CA
680.0	C052C681(<u>4</u>)2G5CA
820.0	C052C821(<u>4</u>)2G5CA
1,000.0	C052C102(<u>4</u>)2G5CA
1,200.0	C052C122(<u>4</u>)2G5CA
1,500.0	C052C152(<u>4</u>)2G5CA
1,800.0	C052C182(<u>4</u>)2G5CA
2,200.0	C052C222(<u>4</u>)2G5CA
2,700.0	C052C272(<u>4</u>)2G5CA
	- C052 SIZE C0G
390.0	C052C391(<u>4</u>)1G5CA
470.0	C052C471(<u>4</u>)1G5CA
560.0	C052C561(<u>4</u>)1G5CA
680.0	C052C681(<u>4</u>)1G5CA
820.0	C052C821(<u>4</u>)1G5CA
1,000.0	C052C102(<u>4</u>)1G5CA
1,200.0	C052C122(<u>4</u>)1G5CA
1,500.0	C052C152(<u>4</u>)1G5CA
1,800.0	C052C182(<u>4</u>)1G5CA
2,200.0	C052C222(4)1G5CA
2,700.0	C052C272(<u>4</u>)1G5CA
3,300.0	C052C332(<u>4</u>)1G5CA
3,900.0	C052C332(<u>4</u>)1G5CA C052C392(<u>4</u>)1G5CA
4,700.0	C052C392(<u>4</u>)1G5CA C052C472(<u>4</u>)1G5CA
	bol for capacitance tolerance as

NOTE 1: Insert proper symbol for capacitance tolerance as follows:

- (1) 1.0 pF to 8.2 pF: D— ±.5 pF (2) 10.0 pF to 22 pF: J— ±5%, K— ±10% (3) 27.0 pF to 47 pF: G— ±2%, J— ±5%, K— ±10% (4) 56.0 pF and up: F— ±1%,G— ±2%, J— ±5%, K— ±10%

CAPACITANCE	KEMET
pF	PART NUMBER
200 VOLT -	- C062 SIZE C0G
3,300.0	C062C332(<u>4</u>)2G5CA
3,900.0	C062C392(4)2G5CA
4,700.0	C062C472(<u>4</u>)2G5CA
5,600.0	C062C562(<u>4</u>)2G5CA
6,800.0	C062C682(<u>4</u>)2G5CA
8,200.0	C062C822(<u>4</u>)2G5CA
10,000.0	C062C103(<u>4</u>)2G5CA
	- C062 SIZE C0G
5,600.0	C062C562(<u>4</u>)1G5CA
6,800.0	C062C682(<u>4</u>)1G5CA
8,200.0	C062C822(<u>4</u>)1G5CA
10,000.0	C062C103(<u>4</u>)1G5CA
12,000.0	C062C123(<u>4</u>)1G5CA
15,000.0	C062C153(<u>4</u>)1G5CA
18,000.0	C062C183(<u>4</u>)1G5CA
22,000.0	C062C223(<u>4</u>)1G5CA
200 VOLT -	- C512 SIZE C0G
12,000.0	C512C123(<u>4</u>)2G5CA
15,000.0	C512C153(<u>4</u>)2G5CA
18,000.0	C512C183(<u>4</u>)2G5CA
22,000.0	C512C223(<u>4</u>)2G5CA
27,000.0	C512C273(<u>4</u>)2G5CA
33,000.0	C512C333(<u>4</u>)2G5CA
39,000.0	C512C393(<u>4</u>)2G5CA
47,000.0	C512C473(<u>4</u>)2G5CA
56,000.0	C512C563(<u>4</u>)2G5CA
68,000.0	C512C683(<u>4</u>)2G5CA
	- C512 SIZE C0G
27,000.0	C512C273(<u>4</u>)1G5CA
33,000.0	C512C333(<u>4</u>)1G5CA
39,000.0	C512C393(<u>4</u>)1G5CA
47,000.0	C512C473(<u>4</u>)1G5CA
56,000.0	C512C563(<u>4</u>)1G5CA
68,000.0	C512C683(<u>4</u>)1G5CA
82,000.0	C512C823(<u>4</u>)1G5CA
100,000.0	C512C104(<u>4</u>)1G5CA
	- C522 SIZE C0G
82,000.0	C522C823(<u>4</u>)2G5CA
100,000.0	C522C104(<u>4</u>)2G5CA
	- C522 SIZE C0G
120,000.0	C522C124(<u>4</u>)1G5CA
150,000.0	C522C154(<u>4</u>)1G5CA
180,000.0	C522C184(<u>4</u>)1G5CA

NOTE 1: Insert proper symbol for capacitance tolerance as follows:

- (1) 1.0 pF to 8.2 pF: D— ±.5 pF (2) 10.0 pF to 22 pF: J— ±5%, K— ±10% (3) 27.0 pF to 47 pF: G— ±2%, J— ±5%, K— ±10% (4) 56.0 pF and up: F— ±1%,G— ±2%, J— ±5%, K— ±10%



STABLE TEMPERATURE CHARACTERISTIC—X7R

RATINGS & PART NUMBER REFERENCE

CAPACI- TANCE pF	TOL. %	KEMET PART NUMBER
pF 100	%	DADT NIIMBED
100		CART NUMBER
	VOLT -	- C114 SIZE
10	10	C114C100K1R5CA
10	20	C114C100M1R5CA
12	10	C114C120K1R5CA
15	10	C114C150K1R5CA
15	20	C114C150M1R5CA
18	10	C114C180K1R5CA
22 22	10 20	C114C220K1R5CA C114C220M1R5CA
27	10	C114C270K1R5CA
33	10	C114C330K1R5CA
33	20	C114C330M1R5CA
39	10	C114C390K1R5CA
47	10	C114C470K1R5CA
47	20	C114C470M1R5CA
56	10	C114C560K1R5CA
68	10	C114C680K1R5CA
68	20	C114C680M1R5CA
82	10	C114C820K1R5CA
100 100	10 20	C114C101K1R5CA C114C101M1R5CA
120	10	C114C121K1R5CA
150	10	C114C121K1R5CA C114C151K1R5CA
150	20	C114C151K1R5CA C114C151M1R5CA
180	10	C114C181K1R5CA
220	10	C114C221K1R5CA
220	20	C114C221M1R5CA
270	10	C114C271K1R5CA
330	10	C114C331K1R5CA
330	20	C114C331M1R5CA
390	10	C114C391K1R5CA
470	10	C114C471K1R5CA
470	20	C114C471M1R5CA
560	10	C114C561K1R5CA
680	10	C114C681K1R5CA
680 820	20 10	C114C681M1R5CA C114C821K1R5CA
1,000	10	C114C621K1R5CA C114C102K1R5CA
1,000	20	C114C102M1R5CA
1,200	10	C114C122K1R5CA
1,500	10	C114C152K1R5CA
1,500	20	C114C152M1R5CA
1,800	10	C114C182K1R5CA
2,200	10	C114C222K1R5CA
2,200	20	C114C222M1R5CA
2,700	10	C114C272K1R5CA
2,700	20	C114C332K1R5CA
3,300	10	C114C332M1R5CA
3,300	20	C114C392K1R5CA
3,900 4,700	10	C114C392K1R5CA
4,700	10 20	C114C472K1R5CA C114C472M1R5CA
,		- C114 SIZE
5,600	10	C114C562K5R5CA
6.800	10	C114C682K5R5CA
6,800	20	C114C682M5R5CA
8,200	10	C114C822K5R5CA
10,000	10	C114C103K5R5CA
10,000	20	C114C103M5R5CA

CAPACI-	TOL.	KEMET
TANCE pF	%	PART NUMBER
•	VOLT	– C124 SIZE
5,600	10	C124C562K1R5CA
6,800	10	C124C682K1R5CA
6,800	20	C124C682M1R5CA
8,200	10	C124C822K1R5CA
10,000	10	C124C103K1R5CA
10,000	20	C124C103M1R5CA
		- C124 SIZE
12,000	10	C124C123K5R5CA
15,000	10	C124C153K5R5CA
15,000	20	C124C153M5R5CA C124C183K5R5CA
18,000 22,000	10	C124C163K5R5CA C124C223K5R5CA
22,000	20	C124C223M5R5CA
27,000	10	C124C273K5R5CA
33,000	10	C124C333K5R5CA
33,000	20	C124C333M5R5CA
39,000	10	C124C393K5R5CA
47,000	10	C124C473K5R5CA
47,000	20	C124C473M5R5CA
10	VOLT	– C192 SIZE
12,000	10	C192C123K1R5CA
15,000	10	C192C153K1R5CA
15,000	20	C192C153M1R5CA
18,000	10	C192C183K1R5CA
22,000 22,000	10 20	C192C223K1R5CA C192C223M1R5CA
27,000	10	C192C223W1R5CA C192C273K1R5CA
33,000	10	C192C333K1R5CA
33,000	20	C192C333M1R5CA
39,000	10	C192C393K1R5CA
47,000	10	C192C473K1R5CA
47,000	20	C192C473M1R5CA
56,000	10	C192C563K1R5CA
68,000	10	C192C683K1R5CA
68,000	20	C192C683M1R5CA
82,000	10	C192C823K1R5CA
100,000	10	C192C104K1R5CA
100,000	20	C192C104M1R5CA
	_	- C192 SIZE
56,000	10	C192C563K5R5CA C192C683K5R5CA
68 000		CIBZCOOSKSKSCA
68,000 68,000		C192C683M5R5CA
68,000	20	C192C683M5R5CA
68,000 82,000	20 10	C192C823K5R5CA
68,000 82,000 100,000	20 10 10	C192C823K5R5CA C192C104K5R5CA
68,000 82,000 100,000 100,000	20 10 10 20	C192C823K5R5CA C192C104K5R5CA C192C104M5R5CA
68,000 82,000 100,000	20 10 10 20 10	C192C823K5R5CA C192C104K5R5CA
68,000 82,000 100,000 100,000 120,000	20 10 10 20	C192C823K5R5CA C192C104K5R5CA C192C104M5R5CA C192C124K5R5CA
68,000 82,000 100,000 100,000 120,000 150,000	20 10 10 20 10	C192C823K5R5CA C192C104K5R5CA C192C104M5R5CA C192C124K5R5CA C192C154K5R5CA
68,000 82,000 100,000 100,000 120,000 150,000 150,000	20 10 10 20 10 10 20	C192C823K5R5CA C192C104K5R5CA C192C104M5R5CA C192C124K5R5CA C192C154K5R5CA C192C154M5R5CA
68,000 82,000 100,000 100,000 120,000 150,000 150,000 180,000	20 10 10 20 10 10 20 10	C192C823K5R5CA C192C104K5R5CA C192C104M5R5CA C192C124K5R5CA C192C154K5R5CA C192C154M5R5CA C192C184K5R5CA

CARACI						
CAPACI- TANCE	TOL.	KEMET				
	%	PART NUMBER				
pF						
	VOLT	- C202 SIZE				
56,000	10	C202C563K1R5CA				
68,000	10	C202C683K1R5CA				
68,000	20	C202C683M1R5CA				
82,000	10	C202C823K1R5CA				
100,000	10	C202C104K1R5CA				
100,000	20	C202C104M1R5CA				
120,000	10	C202C124K1R5CA				
150,000	10	C202C154K1R5CA				
150,000	20	C202C154M1R5CA				
180,000	10	C202C184K1R5CA				
220,000	10	C202C224K1R5CA				
220,000	20	C202C224M1R5CA				
270,000	10	C202C274K1R5CA				
330,000	10	C202C334K1R5CA				
330,000	20	C202C334M1R5CA				
50 VOLT - C202 SIZE						
470,000	10	C202C474K5R5CA				
470,000	20	C202C474M5R5CA				
680,000	10	C202C684K5R5CA				
680,000	20	C202C684M5R5CA				
1,000,000	10	C202C105K5R5CA				
1,000,000	20	C202C105M5R5CA				
100	VOLT -	- C222 SIZE				
470,000	10	C222C474K1R5CA				
470,000	20	C222C474M1R5CA				
680,000	10	C222C684K1R5CA				
680,000	20	C222C684M1R5CA				
1,000,000	10	C222C105K1R5CA				
1,000,000	20	C222C105M1R5CA				
50	VOLT -	- C222 SIZE				
2,200,000	10	C222C225K5R5CA				
2,200,000	20	C222C225M5R5CA				
3,300,000	10	C222C335K5R5CA				
3,300,000	20	C222C335M5R5CA				
l 						

STABLE TEMPERATURE CHARACTERISTIC—X7R

RATINGS & PART NUMBER REFERENCE

CAPACI- TANCE pF	TOL. %	KEMET PART NUMBER
20	0 VOLT	- C052 SIZE
10	10	C052C100K2R5CA
10	20	C052C100M2R5CA
12	10	C052C120K2R5CA
15	10	C052C150K2R5CA
15	20	C052C150M2R5CA
18	10	C052C180K2R5CA
22	10	C052C220K2R5CA
22	20	C052C220M2R5CA
27	10	C052C270K2R5CA
33	10	C052C330K2R5CA
33	20	C052C330M2R5CA
39	10	C052C390K2R5CA
47	10	C052C470K2R5CA
47	20	C052C470M2R5CA
56	10	C052C560K2R5CA
68	10	C052C680K2R5CA
68	20	C052C680M2R5CA
82	10	C052C820K2R5CA
100	10	C052C101K2R5CA
100	20	C052C101M2R5CA
120	10	C052C121K2R5CA
150	10	C052C151K2R5CA
150	20	C052C151M2R5CA
180	10	C052C181K2R5CA
220	10	C052C221K2R5CA
220	20	C052C221M2R5CA
270	10	C052C271K2R5CA
330	10	C052C331K2R5CA
330	20	C052C331M2R5CA
390	10	C052C391K2R5CA
470	10	C052C471K2R5CA
470	20	C052C471M2R5CA
560	10	C052C561K2R5CA
680	10	C052C681K2R5CA
680	20	C052C681M2R5CA
820	10	C052C821K2R5CA
1,000	10	C052C102K2R5CA
1,000	20	C052C102M2R5CA

CAPACI-		
TANCE pF	TOL. %	KEMET PART NUMBER
100	VOLT	- C052 SIZE
1,200	10	C052C122K1R5CA
1,500	10	C052C152K1R5CA
1,500	20	C052C152M1R5CA
1,800	10	C052C182K1R5CA
2,200	10	C052C222K1R5CA
2,200	20	C052C222M1R5CA
2,700	10	C052C272K1R5CA
3,300 3,300	10 20	C052C332K1R5CA C052C332M1R5CA
3,900	10	C052C332M1R5CA C052C392K1R5CA
4,700	10	C052C392K1R5CA
4,700	20	C052C472M1R5CA
5,600	10	C052C562K1R5CA
6,800	10	C052C682K1R5CA
6,800	20	C052C682M1R5CA
8,200	10	C052C822K1R5CA
10,000	10	C052C103K1R5CA
10,000	20	C052C103M1R5CA
50	VOLT -	- C052 SIZE
12,000	10	C052C123K5R5CA
15,000	10	C052C153K5R5CA
15,000	20	C052C153M5R5CA
18,000	10	C052C183K5R5CA
22,000	10	C052C223K5R5CA
22,000	20	C052C223M5R5CA
27,000	10 10	C052C273K5R5CA C052C333K5R5CA
33,000 33,000	20	C052C333M5R5CA
39,000	10	C052C393K5R5CA
47,000	10	C052C473K5R5CA
47,000	20	C052C473M5R5CA
56,000	10	C052C563K5R5CA
68,000	10	C052C683K5R5CA
68,000	20	C052C683M5R5CA
82,000	10	C052C823K5R5CA
100,000	10	C052C104K5R5CA
100,000	20	C052C104M5R5CA
		- C062 SIZE
1,200	10	C062C122K2R5CA
1,500	10	
		C062C152K2R5CA
1,500	20	C062C152M2R5CA
1,800	20 10	C062C152M2R5CA C062C182K2R5CA
1,800 2,200	20 10 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA
1,800 2,200 2,200	20 10 10 20	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA
1,800 2,200 2,200 2,700	20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA
1,800 2,200 2,200	20 10 10 20	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA
1,800 2,200 2,200 2,700 3,300	20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA
1,800 2,200 2,200 2,700 3,300 3,300	20 10 10 20 10 10 20	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900	20 10 10 20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C372K2R5CA C062C332M2R5CA C062C332M2R5CA C062C332M2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900 4,700 4,700 5,600	20 10 10 20 10 10 20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA C062C332M2R5CA C062C392K2R5CA C062C472K2R5CA C062C472K2R5CA C062C472K2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900 4,700 4,700 5,600 6,800	20 10 10 20 10 10 20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA C062C332M2R5CA C062C392K2R5CA C062C372K2R5CA C062C472K2R5CA C062C472K2R5CA C062C472K2R5CA C062C682K2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900 4,700 4,700 5,600 6,800 6,800	20 10 10 20 10 10 20 10 10 20 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA C062C332M2R5CA C062C392K2R5CA C062C472K2R5CA C062C472M2R5CA C062C562K2R5CA C062C562K2R5CA C062C682K2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900 4,700 4,700 5,600 6,800 6,800 8,200	20 10 10 20 10 10 20 10 10 20 10 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA C062C392K2R5CA C062C472K2R5CA C062C472M2R5CA C062C562K2R5CA C062C682K2R5CA C062C682K2R5CA C062C682K2R5CA C062C682K2R5CA
1,800 2,200 2,200 2,700 3,300 3,300 3,900 4,700 4,700 5,600 6,800 6,800	20 10 10 20 10 10 20 10 10 20 10 20 10	C062C152M2R5CA C062C182K2R5CA C062C222K2R5CA C062C222M2R5CA C062C272K2R5CA C062C332K2R5CA C062C332M2R5CA C062C332M2R5CA C062C392K2R5CA C062C472K2R5CA C062C472M2R5CA C062C562K2R5CA C062C562K2R5CA C062C682K2R5CA

C	E		
	CAPACI- TANCE pF	TOL. %	KEMET PART NUMBER
	10	0 VOLT	- C062 SIZE
	12,000	10	C062C123K1R5CA
	15,000	10	C062C153K1R5CA
	15,000	20	C062C153M1R5CA
	18,000	10	C062C183K1R5CA
	22,000	10	C062C223K1R5CA
	22,000	20	C062C223M1R5CA
	27,000	10	C062C273K1R5CA
	33,000	10 20	C062C333K1R5CA
	33,000 39,000	10	C062C333M1R5CA C062C393K1R5CA
	47,000	10	C062C393K1R5CA
	47,000	20	C062C473M1R5CA
	56,000	10	C062C563K1R5CA
	68,000	10	C062C683K1R5CA
	68,000	20	C062C683M1R5CA
	82,000	10	C062C823K1R5CA
	100,000	10	C062C104K1R5CA
	100,000	20	C062C104M1R5CA
	1,000,000	10	C062C105K1R5CA
	1,000,000	20	C062C105M1R5CA
			- C062 SIZE
	120,000	10	C062C124K5R5CA
	150,000	10	C062C154K5R5CA
	150,000	20 10	C062C154M5R5CA C062C184K5R5CA
	180,000 220,000	10	C062C224K5R5CA
	220,000	20	C062C224M5R5CA
	270,000	10	C062C274K5R5CA
	330,000	10	C062C334K5R5CA
	330,000	20	C062C334M5R5CA
	390,000	10	C062C394K5R5CA
	470,000	10	C062C474K5R5CA
	470,000	20	C062C474M5R5CA
	560,000	10	C062C564K5R5CA
	680,000	10	C062C684K5R5CA
	680,000	20	C062C684M5R5CA
	820,000	10	C062C824K5R5CA
	1,000,000	10	C062C105K5R5CA C062C105M5R5CA
	1,000,000	20	
	1,000,000	10	- C512 SIZE C512C105K5X5CA
	1,000,000	20	C512C105N5X5CA C512C105M5X5CA
	1,500,000	10	C512C155K5X5CA
	1,500,000	20	C512C155M5X5CA
	2,000,000	10	C512C205K5X5CA
	2,000,000	20	C512C205M5X5CA
	2,200,000	10	C512C225K5X5CA
	2,200,000	20	C512C225M5X5CA
		0 VOLT	
	1,000,000	10	C522C105K1X5CA
	1,000,000	20	C522C105M1X5CA
		VOLT	
	2,700,000	10	C522C275K5X5CA
	2,700,000 3,300,000	20	C522C275M5X5CA
	3,300,000	10 20	C522C335K5X5CA C522C335M5X5CA
	0,000,000		JULEGOODINIONOON





Ceramic Axial

Lead Tape and Reel Packaging

KEMET offers standard reeling of Molded and Conformally Coated Axial Leaded Ceramic Capacitors for automatic insertion or lead forming machines per EIA specification RS-296. KEMET's internal specification four-digit suffix, 7200, is placed at the end of the part number to designate tape and reel packaging, ie: C410C104Z5U5CA7200.

Paper (50 lb.) test minimum is inserted between the layers of capacitors wound on reels for component pitch $\leq 0.400^\circ$. Capacitor lead length may extend only a maximum of .0625" (1.59mm) beyond the tapes' edges. Capacitors are centered in a row between the two tapes and will deviate only \pm 0.031 (0.79mm) from the row center. A minimum of 36" (91.5 cm) leader tape is provided at each end of the reel capacitors. Universal splicing clips are used to connect the tape. Standard reel quantities are shown on page 48.





Adhesive Tape

Adhesive Tape

Table 1 Dimensions in Inches (Millimeters)

Component Body Diameter	Component Pitch "A"	Inside Tape Spacing "E ± 1.5mm (0.059")	
	0.020" or (±0.5mm)	I	III*
0" (0mm) to 0.197" (5mm) 0.197" (5.01mm) to 0.394: (10mm)	0.197" or (5mm) 0.394" or (10mm)	2.062" (52.4mm)	2.874" (73mm)

^{*} Not Available for Conformally Coated Parts.

CERAMIC LEADED PACKAGING INFORMATION

Ceramic Radial

Lead Tape and Reel Packaging

KEMET offers standard reeling of Molded and Conformally Coated Radial Leaded Ceramic Capacitors for automatic insertion per EIA specification RS-468. Parts are taped to a tagboard carrier strip, and wound on a reel as shown in Figure 1. Kraft paper interleaving is inserted between the layers of capacitors on the reel. Ammopack is also available, with the same lead tape configuration and package quantities.





Figure 1 **Carrier Strip Adhesive Tape** Kraft Paper Interleaving Carrier Tape

(Note: Non-standard lead lengths available in bulk only.)

Figure 3: Standard Reel



(.20") center-to-center. # See page 22 for exact lead configuration for Series.

Ceramic Radial Tape and Reel Dimensions in Millimeters (Inches)

Dimension	Symbol	Nom mm	inal (inch)	Tolera mm (ir		Dimension	Symbol	Nominal mm (inch)	Tolerance mm (inch)
Sprocket Hole Diameter	Do	4.0 (.157)	± 0.2 (.008)	Height to Seating Plane (formed leads) (2)	H ₀	7301 7303 16.0 (.630) 18.0 (.709	7301 7303 ±0.5 (.020) Minimum
Sprocket Hole Pitch	P0	12.7	(.500)	± 0.3 (.012)	Component Alignment	Δh	4.0 (.157)	±0.2 (.008)
Component Pitch	Р	12.7	(.500)	± 0.3 (.012)	Lead Protrusion	L1	1.0 (.039)	Maximum
Lead Spacing (1)	F	5.08 (.20)	2.54 (.10)	+0.6 (+.024		Composite Tape Thickness	t	0.7 (.051)	±0.2 (.008)
Sprocket Hole Center to Lead Center (1)	P1	3.81 (.150)	5.08 (.200)	± 0.7 (.028)	Overall Tape and Lead Thickness	Т	1.5 (.059)	Maximum
Sprocket Hole Center to Component Center	P2	6.35	(.250)	± 1.3 (.051)	Carrier Tape Width	W	18.0 (.709)	+1.0 - 0.5 (+.039020)
Height to Seating Plane (straight leads) (2)	Н	7301 16.0 (.630)	7303 18.0 (.709)	7301 ±0.5 (.020)	7303 Minimum	Hold-Down Tape Width	W0	5.0 (.197)	Minimum
Component Height Above Tape Center	H1	32.2	(1.27)	Maxir	num	Hold-Down Tape Location	W2	3.0 (.118)	Maximum

Measured at the egress from the carrier tape, on the component side.

Determined by a 4 digit suffix placed at the end of the part number, as follows:
7301 = Recommended for parts with formed leads.
7303 = Recommended for parts with straight leads.
Example: C322C104K5R5CA7303
Example: C320C104K5R5CA7303



CERAMIC LEADED PACKAGING INFORMATION

KEMET Series	Military Style	Military Specification	Standard (1) Bulk Quantity	Ammo Pack Quantity Maximum	Maximum Reel Quantity	Reel Size
C114C-K-G	CK12, CC75	MIL-C-11015/	200/Box		5000	12"
C124C-K-G	CK13, CC76	MIL-PRF-20	200/Box		5000	12"
C192C-K-G	CK14, CC77		100/Box		3000	12"
C202C-K	CK15		25/Box		500	12"
C222C-K	CK16		10/Tray		300	12"
C052C-K-G	CK05, CC05		100/Bag	2000	2000	12"
C062C-K-G	CK06, CC06		100/Bag	1500	1500	12"
C114G	CCR75	MIL-PRF-20	200/Box		5000	12"
C124G	CCR76		200/Box		5000	12"
C192G	CCR77		100/Box		3000	12"
C202G	CC78-CCR78		25/Box		500	12"
C222G	CC79-CCR79		10/Tray		300	12"
C052/56G	CCR05		100/Bag		1700	12"
C062/66G	CCR06		100/Bag		1500	12"
C512G	CC07-CCR07		Footnote (2)		N/A	N/A
C522G	CC08-CCR08		Footnote (2)		N/A	N/A
C114T	CKR11	MIL-PRF-39014	200/Box		5000	12"
C124T	CKR12	WIIL-1 1XI -03014	200/Box		5000	12"
C1241 C192T	CKR12		100/Box		3000	12"
C1921 C202T	CKR14 CKR15		25/Box		500	12"
C2021 C222T	CKR15		10/Tray		300	12"
C052/56T	CKR05		100/Hay		1700	12"
C052/56T	CKR05		100/Bag		1500	12"
C31X	CKNOO		500/Bag	2500	2500	12"
C31X			_	2500	2500	12"
C32X			500/Bag			12"
			250/Bag	1500	1500	12"
C340			100/Bag	1000	1000	
C350			50/Bag	N/A	500	12"
C410			300/Box	4000	5000	12"
C412			200/Box	4000	5000	12"
C420			300/Box	4000	5000	12"
C430			200/Box	2000	2500	12"
C440	> 1/4	11/4	200/Box	2000	2500	12"
C512	N/A	N/A	Footnote (2)		N/A	N/A
C522	N/A	N/A	Footnote (2)		N/A	N/A
C617			250/Bag		1000	12"
C622/C623			100/Bag 100/Bag		500 500	12"
C627/C628 C630/C631			100/Bag 100/Bag		500 500	12"
C630/C631 C637/C638			50/Bag		500	12"
C637/C638 C640/C641			50/Bag 50/Bag		500	12"
C642/C643			50/Bag 50/Bag		500	12" 12"
C647/C648			50/Bag 50/Bag		500	12"
C657/C658			50/Bag 50/Bag		500	12"
C667/C668			50/Bag 50/Bag		500	12"

NOTE: (1) Standard packaging refers to number of pieces per bag, tray or vial.

⁽²⁾ Quantity varies. For further details, please consult the factory.