

Type 3521 Series

Key Features

2 Watts at 70°C

Small size to power ratio

Supplied on tape

Value marked on resistor


500 volt maximum overload

250 volt

maximum working voltage

Terminal finish matte Sn over Ni

AEC-Q200 Qualified




TE Connectivity is pleased to announce that our 3521 series high power Thick Film Chip Resistor is now AEC-Q200 Qualified. This low cost device, suitable for auto placement in volume, and for most applications, including high frequency operations, owing to the short lead structure, is attractively priced and available on 7" reels of 4000 pieces.

Characteristics – Electrical

Power Rating	2W
Resistance Range	0.1Ω ~ 10ΜΩ
Tolerance	±1% ±5%
Max. Working Voltage	250V
Max. Overload Voltage	500V
Dielectric Withstanding Voltage	500V
Temperature Range	-55°C ~ +155°C
Ambient Temperature	70°C

Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70 $^{\circ}$ C . For temperature in excess of 70 $^{\circ}$ C , The load shall be derated as shown below:



9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Voltage Rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial line frequency and waveform corresponding to the power rating , as determined from the following formula:

 $RCWV = VP \times R$

Where:


RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt)

P = Power Rating (watt)

R = Nominal Resistance (ohm)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value.

Construction & Dimensions:




Dimensi	ons: (m	າm)			
L		W	Н	£1	ይ2
6.35±0).10	3.20±0.20	0.55±0.10	0.60±0.25	0.50±0.20

9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Recommended solder pad



4 layers PCB specification:

1) Outside 2 layers (Top and Bottom) with copper foil thickness at 2oz.

2) Inside 2 layers (Middle layers) with copper foil thickness at 4 oz.

Marking:

For E24 series Values three digit marking, the first two digits are significant figures and the third denoting number of zeros.

E.G.

For Ohmic Values below 10Ω

E.G.

For E96 Values four digit marking, the first three showing significant figures and the fourth showing number of zeros. As previously letter R is for decimal point.

4992

E.G.

49K9Ω

9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Performance Specification:

Characteristics	Limits	Test Methods
Operational life	±(1%+0.1Ω)max	125°C, at 35% of operating power, 1000H (1.5 hours "ON", 0.5 hour "OFF"). (MIL-STD-202)
	<100mΩ	Apply to rate current for 0Ω
$\begin{array}{llllllllllllllllllllllllllllllllllll$		Parametrically test per lot and sample size requirements, summary to show Min, Max, Mean and Standard deviation at room as well as Min and Max operating temperatures. (User Spec)
External Visual	No Mechanical Damage	Electrical test not required. Inspect device construction, marking and workmanship (MIL-STD-883 Method 2009)
Physical Dimension	Reference 2.0 Dimension Standards	Verify physical dimensions to the applicable device detail specification. Note: User(s) and Suppliers spec. Electrical test not required. (JESD22 MH Method JB-100)
Resistance to Solvent	Marking Unsmeared	Note: Add Aqueous wash chemical – OKEM Clean or equivalent. Do not use banned solvents. (MIL-STD-202 Method 215)
Terminal Strength	Not broken	Force of 1.8kg for 60 seconds. (JIS-C-6429)
High Temperature Exposure (Storage)	Resistance change rate is ± (0.5%+0.1Ω) Max.	1000hrs. @T=155°C.Unpowered. Measurement at 24±2 hours after test conclusion. (MIL-STD-202 Method 108)
	<50mΩ	Apply to rate current for 0Ω
Temperature cycling	Resistance change rate is $\pm (0.5\%+0.1\Omega)$ Max.	1000 Cycles (-55°C to +155°C). Measurement at 24±2 hours after test conclusion (JESD22 Method JA-104)
	<50mΩ	Apply to rate current for 0Ω
Moisture Resistance	Resistance change rate is ± (0.5%+0.1Ω) Max.	T=24 hours /cycle. Unpowered. Measurement at 24±2 hours after test conclusion. (MIL-STD-202 Method 106)
	<50mΩ	Apply to rate current for 0Ω
Biased Humidity	Resistance change rate is ± (1%+0.1Ω) Max	10% rated power, 85°C/85%RH, 1000H. Measurement at 24 hours after test conclusion. (MIL-STD-202 Method 103)
	<100mΩ	Apply to rate current for 0Ω
Mechanical Shock	±(1%+0.1Ω) max	Wave Form: Tolerance for half sine shock pulse. Peak value is 100g's. Normal duration (D) is 6. (MIL-STD-202 Method 213)
Vibration	±(1%+0.1Ω) max	5g's for 20 min., 12cycle each of 3 orientations. Note: Use 8"*5"PCB. 031" thick 7 secure points (onone) long side and 2 secure points at corners of opposite sides. Parts mounted within 2' from any secure point. Test from 10-2000Hz. (MIL-STD-202 Method 204)

9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Characteristics	Limits	Test Methods			
		-55°C/+155°C Note: Number of cycles required -300,			
	±(1%+0.1Ω) max	Maximum transfer time -20 seconds, Dwell			
Thermal Shock	±(1%+0.122) max	time -15 minutes. Air-Air.			
		(MIL-STD-202 Method 107)			
	<50mΩ				
	<30/1122	Apply to rate current for 0Ω With the electrometer in direct contact with			
		the discharge tip, verify the voltage setting			
		at levels of			
ESD	±(10%+0.1W)max	±500V,±1KV, ±2KV, ±4KV, ±8KV,			
		The electrometer reading shall be within			
		$\pm 10\%$ for voltages from 500V to $\leq 800V$.			
		(AEC-Q200-002)			
		For both leaded & SMD. Electrical test not			
	95% coverage Min.	required			
		Magnification 50X. Conditions:			
Solderability		a) Method B 4hrs at 155°C dry heat, the dip			
Solderability		in bath with 245°C,5s.			
		b) Method B: at 215°C,5s.			
		c) Method D: at 260°C, 60s.			
		(J-STD-002)			
	No ignition of the tissue paper or	V-0 or V-1 are acceptable. Electrical test not			
Flammability		required.			
	scorching of the pinewood board	(UL-94)			
Board Flex	±(1%+0.05W)max	2mm (Min) (JIS-C-6429)			
board riex	<50mW	Apply to rate current for 0 W			
		Temperature sensing at 500 [®] , Voltage			
		power subjected to 32VDC current clamped			
Flame Retardance	No flame	up to 500ADC and decreased in			
		1.0VDC/hour.			
		(AEC-Q200-001)			
		Condition B No per-heat of samples. Note:			
Resistance to soldering Heat	±(1%+0.05Ω)max.	Single Wave Solder-Procedure 2 for SMD			
		and Procedure 1 for Leaded with solder			
	. ,	within 1.5mm of device body.			
		(MIL-STD-202 Method 210)			
	<50mW	Apply to rate current for 0 W			
* Sulfuration test: H2S 3~5PPM 50°C±2°C 91%~93%RH 1000H					

Performance Specification (continued)

Packaging specification

Embossed Taping:

А	В	С	ØD+0.1	ØD1+0.1 -0	Е	F	G	W	Τ±
±0.2	±0.2	±0.05	-0	-0	±0.1	±0.05	±0.1	±0.2	0.1
3.50	6.70	2.0	1.5	1.5	1.75	5.5	4.0	12.0	1.0


9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change




Peeling Strength of Top Cover Tape

Test Condition: 0.1 to 0.7 N at a peel-off speed of 300 mm / min.



Reel Dimensions



Таре	Reel	A ±	B ±	C ±	D ± 1	M ± 2	W ± 1
	Qty	0.5	0.5	0.5			
Embossed	4,000	2	13	21	60	178	13.8

Environment Related Substance

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

9-1773463-5 Rev G 02/2020

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Storage Condition

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of $25^{\circ}C \pm 10^{\circ}C$ and a relative humidity of 60%RH $\pm 10\%$ RH, chemical and dust free atmosphere

Even within the above guarantee periods, do not store these products in the following conditions, otherwise their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NO2

2. In direct sunlight

AEC-Q200

The 3521 series is qualified to AEC-Q200 standard at Grade"4"

How To Order

3521	10K	F	т
Common Part	Resistance Value	Tolerance	Pack Style
3521 – SMD Power Resistor	1Ω - 1R0 100Ω - 100R 1,000Ω (1KΩ) -1K0 10,000Ω (10KΩ) - 10K 1,000,000Ω (1MΩ) - 1M0	F — 1%	T – 4000 Reel

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: 352110RFT