



Elastische Einpresszone / compliant pressfit zone
 Isolierwerkstoff / housing material : PBT GF30
 Bauart 7 / type 7
 Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
 Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
 Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2
 Schichtaufbau im metallisierten Loch siehe Zeichnung 114124
 diameter of drilled hole see drawing 114124

Bestückungsplan / contact layout ■ bestückt / assembled



- $\phi 1,0^{+0,09}_{-0,06}$ Durchmesser des metallisierten Loches
 $\phi 1,0^{+0,09}_{-0,06}$ Diameter of finished plated-through hole
 $\phi 1,15 \pm 0,025$ Bohrungsdurchmesser des Loches
 $\phi 1,15 \pm 0,025$ Diameter of drilled hole

Leiterplatten-Lochbild / PCB drillhole pattern



Steckbare Codierung / Plugable Coding

Bei Änderung Variante 223527 (auf Transportpalette) beachten!

Information:		Tolerances		Scale	2:1
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation	
				Federleiste C 96 EE Fem. Connector C 96 Pressfit	
		www.ERNI.com		204752	
c	14.08.2006			1	
Index	Date	H:00058708.SZA		STVC	

Consider protection memo form DN 34

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[204752](#) [204752-E](#)