



Bestückungsplan / contact layout ■ bestückt / assembled





Leiterplatten-Lochbild / PCB drillhole pattern



Elastische Einpresszone / compliant pressfit
 Isolierwerkstoff / housing material : PBT GF30
 Bauart 7 / type 7
 Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
 Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
 Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2
 Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6
 diameter of drilled hole see drawing 164062/Nr.6

- 1) $\phi 1,0 \pm 0,09$ Durchmesser des metallisierten Loches
 $\phi 1,0 \pm 0,09$ Diameter of finished plated-through hole
 $\phi 1,15 \pm 0,025$ Bohrungsdurchmesser des Loches
 $\phi 1,15 \pm 0,025$ Diameter of drilled hole

Information: All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Tolerances  All Dimensions in mm	Scale 2:1
	Subject to modification without prior notice. Drawing will not be updated.	Designation Federleiste C 64 EE Fem. Connector C 64 Pressfit
 www.ERNI.com	244294	1
Index	Date	H:00057939.SZA STVC

Consider protection memo from DIN 34

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[244294](#) [244294-E](#)