Ratings

Voltage: 60 V Current: 1 A Waterproof: IP 67

Operating Temperature Range -40 \sim 85 $^{\circ}\text{C}$

Materials

- 1 Insulator: Nylon 66 + 30% glass fiber, black
 2 Sleeve: brass, gold-flashing
 3 Shell: brass, nickel plated
 4 O-ring: rubber
 5 Hexagonal nut: brass, nickel plated
 6 O-ring: rubber

Electrical Requirements
Dielectric strength: 1 min @ 500 Vac
Insulation resistance: 10* Ω min Contact resistance: $10 \text{ m}\Omega$ or less

Mechanical Requirements


Insertion force: 0.82 kgf max Withdrawal force: 0.62 kgf max Life cycle: 500 mating cycles

Environmental RequirementsCold test: -25 °C for 2 hours without deformation Heat test: 85 °C for 16 hours while maintaining minimum 10 8 Ω insulation resistance

5

Assembly info

Wire guage: 26 AWG max (Ø0.55 mm) Panel cutout: Ø7.1 mm recommended



Revision:	Date:	Description:	Prepared:	Notes:			
Α	8/7/2018	Initial release		RoHS compliant		ENSILITY	
A1	12/7/2018	Corrected description	Verified:	Function test: no open, no short circuit, no intermittent	tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
			Dimensions are in				
			millimeters.	Description:	Size:	Part number:	
			Tolerances: X: ± 0.3 mm X.X: ± 0.1 mm X.XX: ± 0.05 mm	Connector, 4 pin M5 socket, 5xL13.7mm, gold plated, panel mount, solder cup, IP67	Α	54-00107	
					Scale:	3:1 Sheet 1 of 1	

3 2