**Ratings** Voltage: 60 V Current: 1 A Waterproof: IP 67

# Operating Temperature Range -40 $\sim 85~^{\circ}\text{C}$

1 Insulator: Nylon 66 + 30% glass fiber, black

2 Sleeve: brass, gold-flashing 3 Shell: brass, nickel plated 4 O-ring: rubber

5 Hexagonal nut: brass, nickel plated 6 O-ring: rubber

Electrical Requirements
Dielectric strength: 1 min @ 500 Vac Insulation resistance:  $10^8 \Omega$  min Contact resistance:  $10 \text{ m}\Omega$  or less

Mechanical Requirements Insertion force: 0.82 kgf max Withdrawal force: 0.62 kgf max Life cycle: 500 mating cycles


## **Environmental Requirements**

Cold test: -25 °C for 2 hours without deformation Heat test: 85 °C for 16 hours while maintaining minimum 10<sup>8</sup> Ω insulation resistance

5

## Assembly info

Wire guage: 26 AWG max (Ø0.55 mm) Panel cutout: Ø5.1 mm recommended



Revision:	Date:	Description:	Prepared:	Notes:				
Α	8/7/2018	Initial release		RoHS compliant		$\vdash$	NSII .	ITY
A1	12/10/2018	Updated notes	Verified:	Function test: no open, no short circuit, no intermittent	tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com			
			Dimensions are in millimeters. Tolerances: X: ± 0.3 mm					
				Description:	Size:	Part number:		
				Connector, 3 pin M5 socket, 5xL13.7mm, gold plated, panel mount, solder cup, IP67	Α	54-00102		
			X.X: ± 0.1 mm X.XX: ± 0.05 mm		Scale:	3:1		Sheet 1 of 1

3