


www.vishay.com

Vishay Siliconix

Power MOSFET



P-Channel	MOSFET

PRODUCT SUMMARY				
V _{DS} (V)	-200			
R _{DS(on)} (Ω)	V _{GS} = -10 V 1.5			
Q _g (Max.) (nC)	20			
Q _{gs} (nC)	3.3			
Q _{gd} (nC)	11			
Configuration	Sin	gle		

FEATURES

- Dynamic dV/dt rating
- Repetitive avalanche rated
- Surface-mount (IRFR9220, SiHFR9220)
- Straight lead (IRFUFU9220, SiHFU9220)
- · Available in tape and reel
- P-channel
- Fast switching
- · Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



DESCRIPTION

Third power MOSFETs technology is the key to Vishay advanced line of Power MOSFET transistors. The efficient geometry and unique processing of the Power MOSFETs design achieve very low on-state resistance combined with high transconductance and extreme device ruggedness.

The DPAK is designed for surface mounting using vapor phase, infrared, or wave soldering techniques. The straight lead version (IRFU, SiHFU series) is for through-hole mounting applications. Power dissipation levels up to 1.5 W are possible in typical surface-mount applications.

ORDERING INFORMATION							
Package	DPAK (TO-252)	DPAK (TO-252)	DPAK (TO-252)	DPAK (TO-252)	IPAK (TO-251)		
Lead (Pb)-free and	SiHFR9220-GE3	SiHFR9220TRL-GE3 a	SiHFR9220TRR-GE3 a	SiHFR9220TR-GE3 a	SiHFU9220-GE3		
halogen-free	IRFR9220PbF-BE3	IRFR9220TRPbF-BE3	-	-	-		
Lead (Pb)-free	IRFR9220PbF	IRFR9220TRLPbFa	IRFR9220TRRPbFa	IRFR9220TRPbFa	IRFU9220PbF		

Note

a. See device orientation

ABSOLUTE MAXIMUM RATINGS (TC	= 25 °C, unl	ess otherwis	se noted)		
PARAMETER			SYMBOL	LIMIT	UNIT
Drain-source voltage			V _{DS}	-200	V
Gate-source voltage			V _{GS}	± 20	¬
Continuous drain surrent	V at 10 V	T _C = 25 °C	1	-3.6	
Continuous drain current $V_{GS} \text{ at -10 V} \frac{T_C = 25 \text{ °C}}{T_C = 100 \text{ °C}}$			I _D	-2.3	Α
Pulsed drain current ^a			I _{DM}	-14	
Linear derating factor				0.33	W/°C
Linear derating factor (PCB mount) e				0.020	VV/ C
Single pulse avalanche energy ^b			E _{AS}	310	mJ
Repetitive avalanche current ^a			I _{AR}	-3.6	A
Repetitive avalanche energy a			E _{AR}	4.2	mJ
Maximum power dissipation $T_C = 25 ^{\circ}C$				42	w
Maximum power dissipation (PCB mount) e T _A = 25 °C			P_D	2.5	VV
Peak diode recovery dV/dt ^c			dV/dt	-5.0	V/ns
Operating junction and storage temperature range			T _J , T _{stg}	-55 to +150	- °C
Soldering recommendations (peak temperature) d For 10 s				260	7

Notes

- Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11) $V_{DD} = -50$ V, Starting $T_J = 25$ °C, L = 35 mH, $R_g = 25$ Ω , $I_{AS} = -3.6$ A (see fig. 12) $I_{SD} \le -3.9$ A, $dI/dt \le 95$ A/µs, $V_{DD} \le V_{DS}$, $T_J \le 150$ °C 1.6 mm from case

- When mounted on 1" square PCB (FR-4 or G-10 material)

S21-0373-Rev. F, 19-Apr-2021 Document Number: 91283

IRFR9220, IRFU9220, SiHFR9220, SiHFU9220

Vishay Siliconix

THERMAL RESISTANCE RATINGS						
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Maximum junction-to-ambient	R _{thJA}	-	-	110		
Maximum junction-to-ambient (PCB mount) ^a	R _{thJA}	-	-	50	°C/W	
Maximum junction-to-case (drain)	R _{thJC}	-	-	3.0		

Note

a. When mounted on 1" square PCB (FR-4 or G-10 material)

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V _{DS}	V _{GS} =	0 V, I _D = - 250 μA	- 200	-	-	V
V _{DS} temperature coefficient	$\Delta V_{DS}/T_{J}$	Reference	e to 25 °C, I _D = - 1 mA	-	- 0.22	-	V/°C
Gate-source threshold voltage	V _{GS(th)}	V _{DS} =	V _{GS} , I _D = - 250 μA	- 2.0	-	- 4.0	V
Gate-source leakage	I _{GSS}		V _{GS} = ± 20 V	-	-	± 100	nA
Zero gate voltage drain current	I _{DSS}		- 200 V, V _{GS} = 0 V V, V _{GS} = 0 V, T _J = 125 °C	-	-	- 100 - 500	μA
Drain-source on-state resistance	R _{DS(on)}	-	I _D = - 2.2 A ^b	-	-	1.5	Ω
Forward transconductance	9 _{fs}	V _{DS} =	- 50 V, I _D = - 2.2 A	1.1	-	-	S
Dynamic		1					ı
Input capacitance	C _{iss}		V _{GS} = 0 V,	-	340	-	
Output capacitance	C _{oss}		$V_{DS} = -25 V$,	-	110	-	pF
Reverse transfer capacitance	C _{rss}	f = 1	.0 MHz, see fig. 5	-	33	1	
Total gate charge	Qg			-	-	20	
Gate-source charge	Q _{gs}	$V_{GS} = -10 \text{ V}$ $I_D = -3.9 \text{ A}, V_{DS} = -160 \text{ V}, see fig. 6 and } 13^b$		-	-	3.3	nC
Gate-drain charge	Q _{gd}	1	See fig. 6 dild 16	-	-	11	1
Turn-on delay time	t _{d(on)}	V _{DD} = - 100 V, I _D = - 3.9 A,		=	8.8	-	
Rise time	t _r			=	27	-] _
Turn-off delay time	t _{d(off)}	$R_g = \overline{18} \Omega$,	$R_D = 24 \Omega$, see fig. 10^b	=	7.3	-	ns ns
Fall time	t _f			=	19	-	
Internal drain inductance	L _D	Between 6 mm (0.25	") from	I	4.5	I	nH
Internal source inductance	L _S	package and die cont		-	7.5	ı	'"'
Drain-Source Body Diode Characteristic	cs						
Continuous source-drain diode current	I _S	MOSFET symbol showing the integral reverse p - n junction diode		1	-	- 3.6	A
Pulsed diode forward current ^a	I _{SM}			-	-	- 14	^
Body diode voltage	V_{SD}	$T_J = 25 \circ C$	$I_S = -3.6 \text{ A}, V_{GS} = 0 \text{ V}^b$	-	-	- 6.3	V
Body diode reverse recovery time	t _{rr}	T 25 °C I-	3 0 A dl/dt - 100 A/usb	1	150	300	ns
Body diode reverse recovery charge	Q_{rr}	$T_J = 25 ^{\circ}\text{C}, I_F = -3.9 \text{A}, dI/dt = 100 \text{A/} \mu \text{s}^{\text{b}}$			0.97	2.0	μC
Forward turn-on time	t _{on}	Intrinsic turn-on time is negligible (turn-on is dominated by L _S and L _D)				L _D)	

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11)

b. Pulse width \leq 300 µs; duty cycle \leq 2 %

www.vishay.com

Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics, T_C = 25 °C




Fig. 1 - Typical Output Characteristics, T_C = 150 °C




Fig. 2 - Typical Transfer Characteristics




Fig. 3 - Normalized On-Resistance vs. Temperature




Fig. 4 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 6 - Typical Source-Drain Diode Forward Voltage




Fig. 5 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 7 - Maximum Safe Operating Area

www.vishay.com Vishay Siliconix




Fig. 8 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 9 - Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit

Peak Diode Recovery dV/dt Test Circuit



• Compliment N-Channel of D.U.T. for driver






Fig. 10 - For P-Channel


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg291283.

TO-252AA Case Outline

VERSION 1: FACILITY CODE = Y








	MILLIMETERS			
DIM.	MIN.	MAX.		
Α	2.18	2.38		
A1	-	0.127		
b	0.64	0.88		
b2	0.76	1.14		
b3	4.95	5.46		
С	0.46	0.61		
C2	0.46	0.89		
D	5.97	6.22		
D1	4.10	-		
Е	6.35	6.73		
E1	4.32	-		
Н	9.40	10.41		
е	2.28	BSC		
e1	4.56	BSC		
L	1.40	1.78		
L3	0.89	1.27		
L4	-	1.02		
L5	1.01	1.52		

Note

• Dimension L3 is for reference only



VERSION 2: FACILITY CODE = N



	MILLIMETERS			
DIM.	MIN.	MAX.		
А	2.18	2.39		
A1	-	0.13		
b	0.65	0.89		
b1	0.64	0.79		
b2	0.76	1.13		
b3	4.95	5.46		
С	0.46	0.61		
c1	0.41	0.56		
c2	0.46	0.60		
D	5.97	6.22		
D1	5.21	-		
Е	6.35	6.73		
E1	4.32 -			
е	2.29 BSC			
Н	9.94	10.34		

	MILLIMETERS			
DIM.	MIN.	MAX.		
L	1.50	1.78		
L1	2.74	ref.		
L2	0.51 BSC			
L3	0.89	1.27		
L4	-	1.02		
L5	1.14	1.49		
L6	0.65	0.85		
θ	0°	10°		
θ1	0°	15°		
θ2	25°	35°		

Notes


- Dimensioning and tolerance confirm to ASME Y14.5M-1994
- All dimensions are in millimeters. Angles are in degrees
- Heat sink side flash is max. 0.8 mm
- · Radius on terminal is optional

ECN: E19-0649-Rev. Q, 16-Dec-2019

DWG: 5347

Case Outline for TO-251AA (High Voltage)

OPTION 1:



	MILLIM	IETERS	INC	HES
DIM.	MIN.	MAX.	MIN.	MAX.
Α	2.18	2.39	0.086	0.094
A1	0.89	1.14	0.035	0.045
b	0.64	0.89	0.025	0.035
b1	0.65	0.79	0.026	0.031
b2	0.76	1.14	0.030	0.045
b3	0.76	1.04	0.030	0.041
b4	4.95	5.46	0.195	0.215
С	0.46	0.61	0.018	0.024
c1	0.41	0.56	0.016	0.022
c2	0.46	0.86	0.018	0.034
D	5.97	6.22	0.235	0.245

	MILLIN	IETERS	INC	HES
DIM.	MIN.	MAX.	MIN.	MAX.
D1	5.21	-	0.205	-
E	6.35	6.73	0.250	0.265
E1	4.32	-	0.170	-
е	2.29	BSC	2.29	BSC
L	8.89	9.65	0.350	0.380
L1	1.91	2.29	0.075	0.090
L2	0.89	1.27	0.035	0.050
L3	1.14	1.52	0.045	0.060
θ1	0'	15'	0'	15'
θ2	25'	35'	25'	35'

ECN: E21-0682-Rev. C, 27-Dec-2021


DWG: 5968

Notes

- Dimensioning and tolerancing per ASME Y14.5M-1994
- Dimension are shown in inches and millimeters
- Dimension D and E do not include mold flash. Mold flash shall not exceed 0.13 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- Thermal pad contour optional with dimensions b4, L2, E1 and D1
- Lead dimension uncontrolled in L3
- Dimension b1, b3 and c1 apply to base metal only
- Outline conforms to JEDEC® outline TO-251AA

Revision: 27-Dec-2021 1 Document Number: 91362

OPTION 2: FACILITY CODE = N



DIM.	MIN.	NOM.	MAX.
Α	2.180	2.285	2.390
A1	0.890	1.015	1.140
b	0.640	0.765	0.890
b1	0.640	0.715	0.790
b2	0.760	0.950	1.140
b3	0.760	0.900	1.040
b4	4.950	5.205	5.460
С	0.460	-	0.610
c1	0.410	-	0.560
c2	0.460	-	0.610
D	5.970	6.095	6.220
D1	4.300	-	-

DIM.	MIN.	NOM.	MAX.
D2	5.380	-	-
E	6.350	6.540	6.730
E1	4.32	-	-
е	2.29 BSC		
L	8.890	9.270	9.650
L1	1.910	2.100	2.290
L2	0.890	1.080	1.270
L3	1.140	1.330	1.520
L4	1.300	1.400	1.500
θ1	0°	7.5°	15°
θ2	4°	-	-

ECN: E21-0682-Rev. C, 27-Dec-2021

DWG: 5968


Notes

- Dimensioning and tolerancing per ASME Y14.5M-1994
- All dimension are in millimeters, angles are in degrees
- Heat sink side flash is max. 0.8 mm

Revision: 27-Dec-2021 2 Document Number: 91362



RECOMMENDED MINIMUM PADS FOR DPAK (TO-252)



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.