

PRODUCT DATASHEET

HALOSTAR PRO 60 W 12 V GY6.35

HALOSTAR® PRO | Low-voltage halogen lamps with pin base



Areas of application

- General illumination
- Kitchen lighting
- Lighting for reading
- Entrance lighting
- Shops
- Restaurants, hotels and similar prestigious applications
- Offices, public buildings
- Outdoor applications only in suitable luminaires

Product benefits

- Brilliant accent lighting
- Significantly lower CO₂ emissions compared to standard version
- High luminous efficacy compared with standard lamps
- Incredibly small dimensions for revolutionary new luminaire designs
- Approved for use in open luminaires (to IEC 60598-1)
- UV filter
- Contains no mercury

Product features

- Average life: 4,000 h
- 100 % dimmable



- Color rendering index R_a : 100
- IRC technology


TECHNICAL DATA

Electrical data

Nominal wattage	60 W
Construction wattage	60.00 W
Nominal voltage	12 V
Claimed equiv. conventional lamp power	90 W
Nominal current	5.41 A

Photometrical data

Luminous flux	1560 lm
Luminous efficacy	26 lm/W
Light color (designation)	Warm White
Color temperature	3000 K
Color rendering index Ra	100
Light color	1030
UV protection	Yes



Light technical data

Starting time	0.0 s
---------------	-------

Dimensions & Weight

Overall length	44.00 mm
Light center length (LCL)	30,0 mm
Diameter	12 mm
Product weight	1.98 g

Lifespan

Lifespan	4000 h
----------	--------

Number of switching cycles	50000
----------------------------	-------

Additional product data

Base (standard designation)	GY6.35
Mercury-free	Yes

Capabilities

Dimmable	Yes
Burning position	Any

Certificates & Standards

Energy efficiency class	G
Energy consumption	60.00 kWh/1000h

Country-specific categorizations



ILCOS	HSGST/UB/UI-60-12-GY6.35-12/30
Order reference	64447 ECO

Energy labelling regulation data acc EU 2019/2015

Lighting technology used	OTHER
Non-directional or directional	NDLS
Mains or non-mains	NMLS
Light source cap-type (or other electric interface)	GY6.35
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Claim of equivalent power	No
Length	44.00 mm
Height	12 mm
Width	12 mm
Chromaticity coordinate x	0.437
Chromaticity coordinate y	0.404
Beam angle correspondence	SPHERE_360
EPREL ID	714440

Model number	AC35323,AC35323,AC35323
--------------	-------------------------

DOWNLOAD DATA

DOWNLOAD DATA	
	CAD data 3-dim
	CAD data 3-dim

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4050300785400	Folding box 1	70 mm x 23 mm x 25 mm	5.83 g	0.04 dm ³
4050300785417	Bundle 5			
4050300785424	Shipping box 40	127 mm x 113 mm x 155 mm	268.00 g	2.22 dm ³
4050300951751	Shipping box 40	144 mm x 107 mm x 121 mm	224.29 g	1.86 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.