

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0622018675](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Daughter Card Module Installation Press-In Tool for 3-Pair by 8-Column Assemblies

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**


Product Family	Application Tooling
Series	<a href="#">207123</a>
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	883906297183
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

Engineering Number 62201-8674

**Reference - Drawing Numbers**

Application Tooling Documents [ATS-622018675-001](#), [TM-622018799-001](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207123 Series](#)

**Use With**

Impact Daughtercard Signal Module Assembly, [76170 Series](#)

**Application Tooling**

**FAQ**

**Description**

**Product #**

Impact 85 Ohm Plus 3 Pair, RAM [1705109807](#)

Signal Module, Right Guided, Open Endwalls, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free

Impact 85 Ohm Plus 3 Pair Right- [1705301038](#)

Angle Daughtercard, Unguided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free

Impact 85 Ohm Plus 1705303038  
3 Pair Right-Angle  
Daughtercard, Left  
Guide, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 85 Ohm 1705305038  
Plus 3 Pair Right-  
Angle Daughtercard,  
Right Guide, 8  
Columns, 72 Circuits,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 761701008  
3 Pair Right-Angle  
Daughtercard  
Receptacle,  
Unguided, 8  
Columns, 72 Circuits,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 761701038  
3 Pair Right-Angle  
Daughtercard  
Receptacle,  
Unguided, 8  
Columns, 72 Circuits,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 761703008  
3 Pair Right-Angle  
Daughtercard  
Receptacle, Left  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 761703038  
3 Pair Right-Angle  
Daughtercard  
Receptacle, Left  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 761703078  
3 Pair Right-Angle  
Daughtercard  
Receptacle with ESD  
Clip, Left Guided, 8  
Columns, 72 Circuits,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 761703138  
3 Pair Right-Angle  
Daughtercard  
Receptacle, Left

Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Polarizing Key  
Position A, Lead-  
Free

Impact 100 Ohm 761703538

3 Pair Right-Angle  
Daughtercard  
Receptacle, Left  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Polarizing Key  
Position E, Lead  
Free

Impact 100 Ohm 761705008

3 Pair Right-Angle  
Daughtercard  
Receptacle, Right  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 761705038

3 Pair Right-Angle  
Daughtercard  
Receptacle, Right  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 761705138

3 Pair Right-Angle  
Daughtercard  
Receptacle, Right  
Guided, 8 Columns,  
72 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Polarizing Key  
Position B, Lead-  
Free

Impact 100 Ohm 764101804

3 Pair Right-Angle  
Male Header,  
Unguided, Open  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 764101807

3 Pair Right-Angle  
Male Header,  
Unguided, Open  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole

Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 764101808

3 Pair Right-Angle  
Male Header,  
Unguided, Open  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 764101827

3 Pair Right-Angle  
Male Header,  
Unguided, Dual  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 764103804

3 Pair Right-Angle  
Male Header,  
Left Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 764103807

3 Pair Right-Angle  
Male Header,  
Left Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 764103808

3 Pair Right-Angle  
Male Header, Left  
Guided, Open  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 764103818

3 Pair Right-Angle  
Male Header,  
Left Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin

Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Keying Orientation A,  
Lead-Free

Impact 100 Ohm 764105804

3 Pair Right-Angle

Male Header,  
Right Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free  
Impact 100 Ohm [764105807](#)  
3 Pair Right-Angle  
Male Header,  
Right Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm [764105818](#)  
3 Pair Right-Angle  
Male Header,  
Right Guide, Open  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Keying Orientation A,  
Lead-Free  
Impact 100 Ohm [764107807](#)  
3 Pair Right-Angle  
Male Header,  
Left Guide, Right  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm [764109807](#)  
3 Pair Right-Angle  
Male Header,  
Right Guided, Left  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free  
Impact 100 Ohm [764109808](#)  
3 Pair Right-Angle  
Male Header,  
Right Guided, Left  
Endwall, 8 Columns,  
72 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

This document was generated on 07/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**