

### SYSTEM COMPONENTS

Hydraulic Hoses	High pressure hydraulic hoses	Pages 50 - 51	
Hydraulic Oil	Premium grade hydraulic oil	Page 51	
Pressure Gauges	Pressure gauges and gauge mounting blocks	Page 52	
Manifolds	Distribution blocks, controlled manifolds and manifold stations with pressure gauges	Page 53	
Couplers & Fittings	High pressure couplers, fittings and adaptors	Page 54	E
Control Valves	Directional and flow control valves	Pages 55 - 56	



### HIGH PRESSURE HYDRAULIC HOSES - BLACK



Working pressure 700 Bar

4:1 Factor of safety

Special lengths available on request


Hi-Force high pressure hydraulic hoses provide the vital, high quality, safe connection for your hydraulic equipment. Available in black and red and supplied complete with an ergonomically designed protective strain reliever at both ends, Hi-Force high pressure hoses are suitable for working pressures up to 700 Bar with a 4:1 factor of safety.



Tip for double acting systems ...

By using black hoses for the advance lines and red hoses [see next page] for the retract lines, identification is made easy and the possibility of incorrectly connected hoses is reduced.

Hose bore is 6.6mm and outside diameter is 12.7mm for all models:



### HIGH PRESSURE HYDRAULIC HOSES - RED




Choice of hose end combinations

Hand grip protective strain relievers

Plastic protective end caps included

Hose bore is 6.6mm and outside diameter is 12.7mm for all models:



#### HYDRAULIC OII



Hi-Force premium grade hydraulic oil is specially formulated for use with Hi-Force hydraulic tools, providing optimum performance throughout all working conditions.

Model	Capacity	
number	litres	For use with
HF032-1	1	Manually operated pumps
HF032-5	5	Manually operated pumps
HF032-25	25	Manually operated pumps
HF046-1	1	Powered pumps
HF046-5	5	Powered pumps
HF046-25	25	Powered pumps

### PRESSURE GAUGES & GAUGE MOUNTING BLOCKS



Clear precise dual scale readings

Manufactured to EN837-1

Calibration certificates on request

Hi-Force hydraulic pressure gauges are your "window" to the system and are recommended for use within all hydraulic systems to allow the user to constantly monitor the system pressure. Hi-Force hydraulic pressure gauges are manufactured to EN837-1 and are accurate to +/-1% of full scale. Standard range models up to 109 tonnes are featured in this catalogue, however gauges to suit Hi-Force high tonnage cylinders & digital pressure gauges are available on request. Always specify Hi-Force pressure gauges for use with your Hi-Force hydraulic tools.


#### Gauges:

	Gauge		Reading	Reading			
Model	diameter	Gauge	Inner	Outer	Inlet	Compatible	Weight
number	mm	type	scale	scale	thread	Hi-Force cylinders	kg
HG63G	63	glycerine	0-700 Bar	0-10.000 Psi	1/4"-18NPT	All models	0.2
HG1	100	dry	0-700 Bar	0-10.000 Psi	½"-14NPT	All models	0.9
HG1G	100	glycerine	0-700 Bar	0-10.000 Psi	½"-14NPT	All models	1.0
HG5	100	dry	0-700 Bar	0-4.5 tonnes	½"-14NPT	All 4.5 tonnes models	0.9
HG10	100	dry	0-700 Bar	0-10 tonnes	½"-14NPT	All 10 tonnes models	0.9
HG11	100	dry	0-700 Bar	0-11 tonnes	½"-14NPT	All 11 tonnes models	0.9
HG20	100	dry	0-700 Bar	0-20 tonnes	½"-14NPT	All 20 tonnes models	0.9
HG23	100	dry	0-700 Bar	0-23 tonnes	½"-14NPT	All 23 tonnes models	0.9
HG25	100	dry	0-700 Bar	0-25 tonnes	½"-14NPT	All 25 tonnes models	0.9
HG32	100	dry	0-700 Bar	0-32 tonnes	½"-14NPT	All 32 tonnes models	0.9
HG33	100	dry	0-700 Bar	0-33 tonnes	½"-14NPT	All 33 tonnes models	0.9
HG50	100	dry	0-700 Bar	0-50 tonnes	½"-14NPT	All 50 tonnes models	0.9
HG61	100	dry	0-700 Bar	0-61 tonnes	½"-14NPT	All 61 tonnes models	0.9
HG102	100	dry	0-700 Bar	0-102 tonnes	½"-14NPT	All 102 tonnes models	0.9
HG109	100	dry	0-700 Bar	0-109 tonnes	½"-14NPT	All 109 tonnes models	0.9
HG2	150	dry	0-700 Bar	0-10.000 Psi	½"-14NPT	All models	1.6
HG2G	150	glycerine	0-700 Bar	0-10.000 Psi	½"-14NPT	All models	1.7

#### Gauge mounting blocks:

		Dimensions	6				
Model number	Length mm	Width mm	Height mm	Gauge thread	Inlet thread	Outlet thread	Weight kg
HGA1	75	32	32	½"-14NPT	⅓"-18NPT male	%"-18NPT female	0.25
HGA2	170	32	32	½"-14NPT	%"-18NPT male	¾"-18NPT female	0.85
HGA1-25	75	32	32	1/4"-18NPT	¾"-18NPT male	%"-18NPT female	0.30
HGA2-25	170	32	32	1/4"-18NPT	¾"-18NPT male	¾"-18NPT female	0.90

### **MANIFOLDS**




Working pressure 700 Bar


Choice of open or controlled manifolds


2, 4, 5, 6 or 8 outlet port models available


Hi-Force manifolds are designed specifically to allow easy control of the direction of flow of the hydraulic fluid within the system. Supplied either as open manifold blocks or with individual needle type shut off/throttle valves on each 3/8" NPT outlet, Hi-Force manifolds provide even greater versatility in your hydraulic system. The range offers 9 models with a choice of up to 8 outlets per manifold and all models are suitable for 700 Bar maximum working pressure.

			Number									
Model			of	Female	Threads	Weight		Dime	nsic	ns ir	n mr	n
numbei	r Type	Design	outlets	Inlet	Outlet	kg	Α	В	С	D	Е	F
HM2	manifold	parallel	2	3/6"-18NPT	2 x 3/8"-18NPT	1.0	114	32	32	50	-	-
HM4	manifold	parallel	4	3/8"-18NPT	4 x ¾"-18NPT	1.5	214	32	32	50	-	-
HM5	manifold	hexagon	5	3/8"-18NPT	5 x ¾"-18NPT	0.7	-	41	51	-	M6	38
HM6	manifold	parallel	6	3/8"-18NPT	6 x ¾"-18NPT	2.0	314	32	32	50	-	-
HM8	manifold	parallel	8	3/8"-18NPT	8 x 3/8-18NPT	2.5	414	32	32	50	-	-
HM4L	manifold	extended paralle	1 4	3/8"-18NPT	4 x ¾"-18NPT	2.4	394	32	32	110	-	-
HM6L	manifold	extended paralle	l 6	3/4"-18NPT	6 x ¾"-18NPT	3.7	614	32	32	110	-	-
HM2C	controlled manifold	parallel	2	3/4"-18NPT	2 x 3/8-18NPT	2.0	150	51	38	100	-	-
HM4C	controlled manifold	parallel	4	%"-18NPT	4 x ¾"-18NPT	3.5	350	51	38	100	-	-










#### Model no. Description

HM4C-SU 4-Way controlled manifold unit, suitable for single acting systems.

Supplied complete with four pressure gauges, reading 0-700 bar, female coupler on inlet port and four female couplers on outlet ports. All mounted on a sturdy framework.



#### Model no. Description

HM4C-DU 4-Way controlled manifold unit, suitable for double acting systems.

Supplied complete with four pressure gauges, reading 0-700 bar, female coupler on inlet port and four female couplers on outlet ports. Also included is a 4-way open manifold for return flow, again with female couplers on inlet and outlet ports. All mounted on a sturdy framework.

### HIGH PRESSURE COUPLERS AND FITTINGS

Hi-Force high pressure couplers and fittings are designed for easy system connection and assembly of your Hi-Force hydraulic equipment. All Hi-Force couplers and fittings are suitable for 700 Bar maximum working pressure. Hi-Force recommends the use of threaded dust caps with quick connect couplers to protect the thread of the coupler and at the same time prevent any contaminants entering your hydraulic system. Always specify Hi-Force couplers and fittings for use with your Hi-Force hydraulic tools.







Safety first!

Be sure to use genuine Hi-Force couplers and fittings which are designed to withstand the full 700 bar working pressure.

Large selection of standard adaptors

Working pressure 700 Bar























Model number	See picture	Description	Thread specification
HF7	1	Nipple	1/4" NPT male to 1/4" NPT male
HF8	5	Adaptor	1/4" NPT female to 1/4" NPT female
HF10	2	Elbow	$^{3\!/_{\!8}}$ " NPT female to $^{3\!/_{\!8}}$ " NPT female
HF12	3	Equal tee	³∕8" NPT female
HF13	4	Cross	³/8" NPT female
HF14	5	Adaptor	⅓" NPT female to ⅙" NPT female
HF15	5	Reducer	<sup>3</sup> ∕ <sub>8</sub> " NPT female to ¹⁄₄" NPT female
HF16	6	Elbow	<sup>3</sup> ∕ <sub>8</sub> " NPT female to <sup>3</sup> ∕ <sub>8</sub> " NPT male
HF17	1	Nipple	$^{3}\!\!/_{\!8}$ " NPT male to $^{3}\!\!/_{\!8}$ " NPT male
HF19	1	Long nipple	⅓8" NPT male to ⅔8" NPT male
HF24	7	Adaptor	3/8" NPT male to 3/8" BSP female
HF27	1	Nipple	1⁄4" NPT male to 3⁄8" NPT male
HF30	7	Reducer	3/8" NPT male to 1/4" NPT female
HF31	8	Tee	<sup>3</sup> ∕ <sub>8</sub> " NPT female to <sup>3</sup> ∕ <sub>8</sub> " NPT male
HF33	7	Reducer	3/8" NPT male to 1/4" BSPT female
HF55	7	Reducer	3/8" NPT female to 1/4" NPT male
HF69	7	Adaptor	½" BSP male to ¾" NPT female
CF1	9	Female coupler	³/8" NPT male
CM1	10	Male coupler	³∕8" NPT female
CMF1	9 + 10	Complete coupler	³∕₅" NPT
CF2	9	Female coupler	1⁄4" NPT male
CM2	10	Male coupler	1/4" NPT female
CMF2	9 + 10	Complete coupler	1/ <sub>4</sub> " NPT
CFD1	11	Metal dust cap for CF1	
CMD1	12	Metal dust cap for CM1	
CFD2	11	Metal dust cap for CF2	
CMD2	12	Metal dust cap for CM2	
PPC1	13	Moulded universal dust cap t	o suit CF1 & CM1

### **DIRECTIONAL CONTROL VALVES**





Working pressure 700 Bar


Pump or remote mounted design


Manual or solenoid options available


Hi-Force control valves are designed to provide precise control of the hydraulic system either by accurate pressure or directional flow control. The PMV range of pump mounted valves is identical to the valves fitted to the Hi-Force powered pumps featured on pages 35 - 37, 39 - 40, 43, 44 and can be easily interchanged, making your powered pump even more versatile. The RMV range allows for remote mounting away from the pump. Always specify Hi-Force control valves for use with your Hi-Force hydraulic tools. Flow control values are featured on the next page.











#### Directional control valves:

	Model number					
Description	Manual valve no load holding	Manual valve with load holding	Solenoid valve 24V incl. control	Manual valve closed centre		
Pump mounted, 2-way, 2 position valve	PMV2	-	-	-		
Pump mounted, 3-way, 3 position valve	PMV3	PMV3L	PMV3S	PMV3C		
Pump mounted, 4-way, 3 position valve	PMV4	PMV4L	PMV4S	PMV4C		
Remote mounted, 3-way, 3 position valve	RMV3	RMV3L	RMV3S	RMV3C		
Remote mounted, 4-way, 3 position valve	RMV4	RMV4L	RMV4S	RMV4C		


### FLOW CONTROL VALVES



Working pressure 700 Bar


3/8" 18 NPT connections

Ensures system safety and control




Manual shut off valve with needle type flow control. Used for load holding and throttling functions. Can also be used as a gauge isolator.

	Dimensions in mm						
Model Number	Height	Length	Width				
HM1C	82	64	38				




Manual check valve used for automatic load locking, with precise manual load lowering feature.

	Dimensions in mm
Model Number	Height Length Width
HFV66	86 75 47



Adjustable pressure relief valve, for pressure setting from 55 to 700 Bar. Supplied complete with return line hose.

	Dimensions in mm					
Model Number	Height	Length	Width			
HPV152	102	64	32			



Pilot operated check valve used as a safety valve for double acting cylinders. Pilot port connects to cylinder retract line.

	Dimensions in mm					
Model Number	Height	Length	Width			
HFV42	84	64	32			



#### **UK Head Office**

Hi-Force Limited
Prospect Way, Daventry
Northants, NN11 8QH
United Kingdom

Tel: +44 1327 301 000 Fax: +44 1327 706 555 daventry@hi-force.com

Your authorised distributor:

## www.hi-force.com

Cat. Ref. HF0110E