ELECTRONIC ASSEMBLY

EA DOGL128-6 GRAPHIC

new display design

128x64 DOTS, 3.3V





TECHNICAL DATA

- * HIGH-CONTRAST LCD SUPERTWIST DISPLAY (STN AND FSTN) WITH 15µm DOT GAP
- * OPTIONAL LED BACKLIGHTS IN VARIOUS COLORS
- * 128x64 PIXELS (CORRESPONDS TO 8x21 CHARACTERS OR 4x16 LARGE CHARACTERS)
- * ST7565R CONTROLLER WITH SPI (4-WIRE) INTERFACE
- * POWER SUPPLY: SINGLE SUPPLY 3.0V TO 3.3V (TYPICALLY 320µA)
- * NO ADDITIONAL VOLTAGES REQUIRED
- * OPERATING TEMPERATURE RANGE -20°C TO +70°C (STORAGE -30°C TO +80°C)
- * LED BACKLIGHTING 5mA TO 90mA
- * NO MOUNTING REQUIRED: SIMPLY SOLDER ONTO PCB

ORDERING CODE

GRAPHICS DISPLAY, 128x64, 68x51mm	EA DOGL128x-6
x: W = white background (FSTN pos. transflective)	
$E = yellow/green \ background \ (STN \ pos. \ transmissive)$	
$B = blue \ background \ (STN \ neg. \ transmissive)$	
$S = black\ background\ (FSTN\ neg.\ transmissive)$	
$L = yellow/green\ background\ (STN\ pos.\ reflective,\ cannot\ be\ backlit)$	
LED BACKLIGHT, WHITE	EA LED68X51-W
LED BACKLIGHT, YELLOW/GREEN	EA LED68X51-G
LED BACKLIGHT, BLUE	EA LED68X51-B
LED BACKLIGHT, RED	EA LED68X51-R
LED BACKLIGHT, AMBER	EA LED68X51-A
LED BACKLIGHT, FULL COLOR RGB	EA LED68X51-RGB

ACCESSORIES

USB TEST BOARD FOR PC (WINDOWS 2000, XP, VISTA)	EA 9780-4USB
TOUCH PANEL, 4-WIRE, ANALOG, STICK-ON	EA TOUCH128-2
ZIF CONNECTOR FOR TOUCH PANEL, BOTTOM CONTACT	EA WF100-04S
SOCKET CONNECTOR 4.8 mm HEIGHT (2 PCS. REQUIRED)	EA FL-20P
CHARACTER SETS PLUS FONTEDITOR	EA USBSTICK-FONT



EA DOGL128-6

The EA DOGL128-6, a 128x64-pixel graphics display, is a new addition to ELECTRONIC ASSEMBLY'S EA DOGL series. It, too, has pins that allow it to be mounted quickly and easily. 6 different optional LED backlights are available. These can be combined with 5 different display technologies, making it possible to have up to around 20 different designs.

Designed for compact, handheld devices, this modern LCD series offers a number of benefits with and without backlighting:

- * Extremely compact (68x51 mm) with a large viewing area of 64x36 mm
- * Super-flat: 2.8 mm without backlight module, and only 6.5 mm with a b./l. module mounted
- * Serial SPI interface (4-wire)
- * Single supply +3.0 V or +3.3 V or dual power supply +1.8..3.3V
- * Typical power consumption of only 320µA in full operation (white LED backlight from 5mA)
- * Easily mounted by soldering
- * Wide range of design variants orderable as single units, backlighting color changes possible

CONTRAST ADJUSTMENT

The contrast can be set by means of a command for all the displays in the EA DOGL128-6 series. The contrast setting of the display must be set once by the software, and is then kept constant throughout the entire operating temperature range (-20..+70°C), thanks to the integrated temperature compensation.

LED BACKLIGHT

6 different variants are available for individual backlighting: white, yellow/green, blue, red, amber and a full-color version.

There are 3 separate LED paths available for each monochrome backlight that can be switched in parallel or in series to suit the system voltage. This means that most backlights can be run at either 3.3 V or a higher voltage.

To operate the backlight, we recommend a current source (e.g. CAT4238TD) or an external series resistor to limit the current. This can be calculated from R=U/I; you can find the values in the table on the right. To prolong the life of the backlights, we recommend that you use a current source. The operating life of the yellow/green, red and

LED backlight	Forw	ard voltaç	је (V)	Current max.	Limiting resistor (ohm, each path)		
	min	typ	max	(mA)	@3,3 V	@5 V	
yellow/green EA LED68x51-G		2,1		60	20	47	
white EA LED68x51-W		3,3		45	CAT4238	39	
amber EA LED68x51-A		2,1		60	24	52	
green EA LED68x51-E		3,1		45	CAT4238	33	
blue EA LED68x51-B		3,3		45	CAT4238	39	
red EA LED68x51-R		2		60	24	52	
full color	red	green	blue	60 each			
EA LED68x51-RGB	typ. 4V	typ. 4V	typ. 4V	colour	-	15	

amber backlights is 100,000 hours. The life of the white and blue backlights is considerably shorter. We recommend that you dim these or switch them off whenever possible.

<u>Important:</u> Never connect the backlight LEDs directly to a 5V/3.3V supply as this will immediately destroy the LEDs. Always use a current source. Please note that derating applies at temperatures exceeding +25°C.

ASSEMBLING

First, clip the display and backlight modules together by gently pushing the display pins through the corresponding holes on the backlight module. Then insert the entire module into the socket, or into the soldering holes on the pcb. The backlight pins (the 2 rows with 3 pins at the bottom) must be soldered on the top side as well to ensure good contact between the modules.

Important: The display has 2 protective films on the top and the bottom (except the version EA DOGL128L that does have 1 foil on the top only), and there is also one on the backlight. These must be removed. Make sure that neither display nor backlight will never come into contact with any kind of liquid like Fluxer, Cleaner, Water.


5 DIFFERENT TECHNOLOGIES

See below for an overview of available technologies, combinations with available backlights and their usability:

display type	technology	optional backlight	readability	display color non backlighted	display color with backlighted	recommended backlight color
ELECTRONIC ASSEMBLY EA DOGL 1284-6	FSTN pos. transflective	it's fine with and without backlight	readable even without backlight	black on white	black on backlight color	white, blue, green, RGB
ELECTRONIC ASSEMBLY EA DOGL 128E-6	STN pos. yellow/green transmissive	backlight unit required	readable even without backlight	dark green on yellow/green	black on yellow/green or amber	yellow/green, amber
ELECTRONIC ASSEMBLY EA DOGL1288-6	STN neg. blue transmissive	usage only with backlight			backlight color on blue background	white, yellow/green
ELECTRONIC ASSEMBLY EA DOGL 1285-6	FSTN neg. transmissive	usage only with backlight			backlight color on black background	white, green, RGB
ELECTRONIC ASSEMBLY EA DOGL 128L-6	STN pos. yellow/green reflective	no backlight possible	finest readable without backlight	dark green on yellow/green		

6 AND MORE DIFFERENT BACKLIGHTS

6 and more different backlight colors are available to match equipments design as much as possible. The most effective and brightest one is the white one EA LED68x51-W.





If you see black and white pictures on this page but you want to see the colors of the displays, you can download a full-colored version of this document at http://www.lcd-module.de/eng/pdf/grafik/dogl128-6e.pdf

APPLICATION EXAMPLES

LOW POWER

+3.0V or +3.3V (single supply) operation requires 9 external capacitors







LOW VOLTAGE

If an external source of +10.5..+13.5V (does not have to be stabilized) is available, the charge pump is not needed and less external components are required. Power supply voltage for display and logic may be 1.8..3.3V then.


ZIF CONNECTOR EA WF100-04S


As an accessory for the touch panel we do provide a ZIF connector (4 pins) with pitch 1.0mm (SMD type). This connector is a "bottom side contact" type.





alle dimensions are in mm





SOCKET FOR THE DISPLAY

EA FL-20P provides a 20 pin socket which matched perfect to the display. Note that 2 pcs. per display are necessary.


TABLE OF PROGRAMMING COMMANDS

Commercial			Com	mano	d Cod	le				Eun-ti
Command	A0	D7	D6	D5	D4	D3	D2	D1	D0	Function
(1) Display ON/OFF	0	1	0	1	0	1	1	1	0	LCD display ON/OFF 0: OFF, 1: ON
(2) Display start line set	0	0	1		Displ	ay st	art a	ddre	ss	Sets the display RAM display start line address
(3) Page address set	0	1	0	1	1	Р	age	addr	ess	Sets the display RAM page address
(4) Column address set upper bit Column address set lower bit	0	0	0	0	1 0	co Le	ost s lumn ast s lumn	add ignifi	ress icant	Sets the most significant 4 bits of the display RAM column address. Sets the least significant 4 bits of the display RAM column address.
(6) Display data write	1						rite d		1633	Writes to the display RAM
(8) ADC select	0	1	0	1	0	0	0	0	0	Sets the display RAM address SEG output correspondence 0: normal, 1: reverse
(9) Display normal/ reverse	0	1	0	1	0	0	1	1	0	Sets the LCD display normal/ reverse 0: normal, 1: reverse
(10) Display all points ON/OFF	0	1	0	1	0	0	1	0	0	Display all points 0: normal display 1: all points ON
(11) LCD bias set	0	1	0	1	0	0	0	1	0	Sets the LCD drive voltage bias ratio 0: 1/9 bias, 1: 1/7 bias (ST7565R)
(14) Reset	0	1	1	1	0	0	0	1	0	Internal reset
(15) Common output mode select	0	1	1	0	0	0	*	*	*	Select COM output scan direction 0: normal direction 1: reverse direction
(16) Power control set	0	0	0	1	0	1	0	pera mod		Select internal power supply operating mode
(17) V ₀ voltage regulator internal resistor ratio set	0	0	0	1	0	0	Res	sistoi	r ratio	Select internal resistor ratio(Rb/Ra) mode
(18) Electronic volume mode set Electronic volume	0	1	0	0	0	0	0	0	1	Set the V ₀ output voltage electronic volume register
register set		0	0		lectro				alue 	
(19) Static indicator ON/OFF Static indicator	0	1	0	1	0	1	1	0	0 1	0: OFF, 1: ON
register set		0	0	0	0	0	0	0	Mode	Set the flashing mode
(20) Booster ratio set	0	1	1	1	1	1	0	0	0	select booster ratio 00: 2x,3x,4x
(0	0	0	0	0	0		ep-up alue	01: 5x 11: 6x
(21) Power save	0									Display OFF and display all points ON compound command
(22) NOP	0	1	1	1	0	0	0	1	1	Command for non-operation

0	Column address
D ₀	Page 0
D7	Page 0
D ₀	Page 1
D7	Page 1
D ₀	Page 2
D7	Page 2
D ₂ 0	Dogo 2
D7	Page 3
D ₀	Dogo 4
D7	Page 4
D ₂ 0	Dogo 5
D ₇	Page 5
D ₀	Dogo 6
D ₇	Page 6
D0 2 D7	Dogo 7
D7	Page 7

DATA TRANSFER

Data transfer is unidirectional. That means that data can only be written; it cannot be read again. In contrast to other displays, a busy query is not necessary with this display. The clock-pulse rate of the SCL line can be up to 20 MHz at 3.3V, depending on the supply voltage. You will find more detailed information on timing on pages 64 and 65 of the data sheet of the ST7565R controller, which you will find on our website at http://www.lcd-module.de/eng/pdf/zubehoer/st7565r.pdf





INITIALISATION EXAMPLE "LOW POWER"

Using the internal contrast voltage generator (single supply +3.0..+3.3V). Application "LOW POWER".

	Initialisation example for single supply +3.3V (bottom view)											
Comn	nand	Α0	D7	D6	D5	D4	D3	D2	D1	D0	Hex	Remark
(2)	Display start line set	0	0	1	0	0	0	0	0	0	\$40	Display start line 0
(8)	ADC set	0	1	0	1	0	0	0	0	1	\$A1	ADC reverse *)
(15)	Common output mode select	0	1	1	0	0	0	0	0	0	\$C0	Normal COM0~COM63
(9)	Display normal/reverse	0	1	0	1	0	0	1	1	0	\$A6	Display normal
(11)	LCD bias set	0	1	0	1	0	0	0	1	0	\$A2	Set bias 1/9 (Duty 1/65)
(16)	Power control set	0	0	0	1	0	1	1	1	1	\$2F	Booster, Regulator and Follower on
(00)	Deceter ratio est		1	1	1	1	1	0	0	0	\$F8	Set internal Booster to 4x
(20)	Booster ratio set	0	0	0	0	0	0	0	0	0	\$00	Set internal Booster to 4x
(17)	V0 voltage regulator set	0	0	0	1	0	0	1	1	1	\$27	
(10)	Clastronia valuma mada aat		1	0	0	0	0	0	0	1	\$81	Contrast set
(18)	Electronic volume mode set	0	0	0	0	1	0	1	1	0	\$10	
(10)	Static indicator act		1	0	1	0	1	1	0	0	\$AC	No indicator
(19)	(19) Static indicator set	0	0	0	0	0	0	0	0	0	\$00	No indicator
(1)	Display ON/OFF	0	1	0	1	0	1	1	1	1	\$AF	Display on

^{*)} Make sure that for 6:00 viewing direction ADC has to be set to "reverse" (mirrored layout)!



Orientation for 6 o'clock (Bottom View)

INITIALISATION EXAMPLE "LOW VOLTAGE"

Using an external power supply for contrast voltage (dual power supply). Application "LOW VOLTAGE".

	Initialisation example for dual power supply (bottom view)											
Comn	nand	A0	D7	D6	D5	D4	D3	D2	D1	D0	Hex	Remark
(2)	Display start line set	0	0	1	0	0	0	0	0	0	\$40	Display start line 0
(8)	ADC set	0	1	0	1	0	0	0	0	1	\$A1	ADC reverse *)
(15)	Common output mode select	0	1	1	0	0	0	0	0	0	\$C0	Normal COM0~COM63
(9)	Display normal/reverse	0	1	0	1	0	0	1	1	0	\$A6	Display normal
(11)	LCD bias set	0	1	0	1	0	0	0	1	0	\$A2	Set bias 1/9 (Duty 1/65)
(16)	Power control set	0	0	0	1	0	1	0	1	1	\$2B	Booster off, Regulator, Follower on
(17)	V0 voltage regulator set	0	0	0	1	0	0	1	1	1	\$27	
(10)	Electronic volume mode set	0	1	0	0	0	0	0	0	1	\$81	Contrast set
(10)	Electronic volume mode set	U	0	0	0	1	0	1	1	0	\$10	
(10)	Ctatia indicator act	_	1	0	1	0	1	1	0	0	\$AC	No indicator
(19)	Static indicator set	0	0	0	0	0	0	0	0	0	\$00	No indicator
(1)	Display ON/OFF	0	1	0	1	0	1	1	1	1	\$AF	Display on

^{*)} Make sure that for 6:00 viewing direction ADC has to be set to "reverse" (mirrored layout)!

12:00 VIEWING ANGLE, TOP VIEW OPTION

If the display is read mostly from above (on the front of a laboratory power supply unit, for example), the preferred angle of viewing can be set to 12 o'clock. This rotaties

A Column address 131

D0 Page 0

D0 Page 1

D0 Page 1

D0 Page 2

D0 Page 3

D0 Page 3

D0 Page 4

D0 Page 5

D0 Page 6

D0 Page 6

the display by 180°. A slightly different initialization setup is required for this. Also keep in mind that the leftmost column (normally numbered as 0) will now change to 4.




Orientation for 12 o'clock (Top View)

	Initialisation example top view											
Com	mand	A0	D7	D6	D5	D4	D3	D2	D1	D0	Hex	Remark
(8)	ADC set	0	1	0	1	0	0	0	0	0	\$A0	ADC normal
(15)	Common output mode select	0	1	1	0	0	1	0	0	0	\$C8	Reverse COM63~COM0

TOUCH PANEL EA TOUCH128-2 (OPTIONAL)

An analog touch panel is available as an accessory. It has a self-adhesive material on its rear surface and is simply stuck onto the display. The connection is made by means of a 4-pin flexible cable for a ZIF connector (e.g.



EA WF100-04S) with a grid of 1.0 mm. Bending radius is defined with min. 5mm. For optimum readability we recommend that you

use a backlight with the display.

Interfacing to a processor can be either done by an external touch panel controller or with a controller that is featured with analogue input. The touch panel is similar to a potentiometer: connecting a voltage of e.g. 3.3V to the pins *Top-Bottom* makes it possible to read out a voltage on pin *Left* or *Right* which is linear to the Y-coordinate of the pressed point. The X-coordinate will result when the voltage will be supplied to

Specification							
Specification	min	max	Unit				
Top-Bottom	100	400	Ω				
Left-Right	110	410	Ω				
Voltage	3	12	V				
Current	5	25	mA				
Linearity		1,5	%				
Force	45	65	g				
Contact Bounce	5	10	ms				
Op. Temperatur	-20	+60	°C				
Stor. Temperatur	-20	+70	°C				
Transmission	75	85	%				
Life Time	10000		Cycles				

Left-Right and measurement is done at Top or Bottom.

The pinout of the connecting cable is shown in the drawing.

USB-TEST BOARD EA 9780-4USB

For easy startup, a USB test board is available that can be connected to a PC. An USB cable and Windows software is supplied with the product. This allows text and images (BMP) to displayed directly on the connected display. You will find more information on

the test board in the EA 9780-4USB data sheet.


SIMULATION WITH WINDOWS


A simulator window also displays the contents of the display. The software can simulate all the displays and colors even without the hardware. You can download the software free from our website:


http://www.lcd-module.de/deu/disk/startdog.zip



DIMENSIONS EA DOGL128-6







all dimensions are in mm




ATTENTION


Pin	Symbol	Level	Function
1	NC		(A1+: LED backlight)
2	NC		(A2+: LED backlight)
3	NC		(A3+: LED backlight)
4			
5	•		
6			
7			
8			
9			
10			
11			
12			
13			
14			
15			
16			
17			
18	NC		(C1-: LED backlight)
19	NC		(C2-: LED backlight)
20	NC		(C3-: LED backlight)

Pin	Symbol	Level	Function
21	V0	-	LC Drive
22	V1	-	LC Drive
23	V2	-	LC Drive
24	V3	-	LC Drive
25	V4	-	LC Drive
26	VSS	L	Power Supply 0V (GND)
27	CAP2N	-	Voltage Converter
28	CAP2P	-	Voltage Converter
29	CAP1P	-	Voltage Converter
30	CAP1N	-	Voltage Converter
31	CAP3P	-	Voltage Converter
32	VOUT	-	Voltage Output about +12V
33	VSS	L	Power Supply 0V (GND)
34	VDD2	Н	Power Supply Booster
35	VDD	Н	Power Supply +1.83,3V
36	SI	H/L	Serial Data In
37	SCL	H/L	Serial Clock
38	A0	H/L	L= Command, H= Data
39	RST	L	Reset (active low)
40	CS1B	L	Chip Select (active low)

- LC displays are generally not suited for wave or reflow soldering. Temperatures of over 80°C can cause lasting damage.
- The surfaces of the displays and backlights are protected from scratching by self-adhesive protective foils. Please remove these before mounting.
- Make sure that either display nor backlight will never come into contact with any kind of liquid like Fluxer, Cleaner, Water.


DIMENSIONS EA LED68X51







The 6(4) LED pins A1 to A3 and C1 to C3 also have to be soldered from above to ensure good contact.



ELECTRONIC ASSEMBLY GmbH Zeppelinstraße 19 D-82205 Gilching Germany

Fon: +49 (0)8105-778090 +49 (0)8105-778099 Fax: e-Mail: info@lcd-module.de www.lcd-module.com Web:

