



MATERIALS:

Body: Gold Plated Beryllium Copper, Center Contacts: Gold Plated Beryllium Copper
 Finish: Body and Contact – Gold plated per MIL-G-45204, Type II, class 2.
 Marking: “Pomona 4295”

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.
 Inner Conductor/Shield: 335VRMS Max.
 Nominal Impedance: 50 Ohms
 Frequency Range: 0-12.4 GHz.
 Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

OPERATING INFORMATION: Model 4295

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

6/9/99

SY/EH/LS

S:\Engineering\Release\DataSheets\FI\LukeDataSheet\4295_1_01.doc

Sales: 800-490-2361 Fax: 888-403-3360

Technical Assistance: 800-241-2060

PomonaACCESS 90252 (800) 444-6785 or (425) 446-6010
 More drawings available at www.pomonaelectronics.com

Page 1 of 1