


Vishay Siliconix

## **Power MOSFET**

PRODUCT SUMMARY					
V <sub>DS</sub> (V)	600	600			
R <sub>DS(on)</sub> (Ω)	V <sub>GS</sub> = 10 V	0.75			
Q <sub>g</sub> max. (nC)	49				
Q <sub>gs</sub> (nC)	13				
Q <sub>gd</sub> (nC)	20				
Configuration	Single				



#### **FEATURES**

ullet Low gate charge  $\mathbf{Q}_{\mathbf{g}}$  results in simple drive requirement



Improved gate, avalanche and dynamic dV/dt ruggedness

RoHS\*

- Fully characterized capacitance and avalanche voltage and current
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### Note

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

### **APPLICATIONS**

- Switch mode power supply (SMPS)
- Uninterruptible power supply
- · High speed power switching
- High voltage isolation = 2.5 kV<sub>RMS</sub> (t = 60 s, f = 60 Hz)

#### TYPICAL SMPS TOPOLOGIES

- · Single transistor forward
- · Active clamped forward

ORDERING INFORMATION			
Package	TO-220 FULLPAK		
Lead (Pb)-free	IRFIB6N60APbF		
	SiHFIB6N60A-E3		
SnPb	IRFIB6N60A		
	SiHFIB6N60A		

<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>C</sub> = 25 °C, unless otherwise noted)						
PARAMETER			SYMBOL	LIMIT	UNIT	
Drain-Source Voltage			$V_{DS}$	600	W	
Gate-Source Voltage			$V_{GS}$	± 30	V	
Continuous Drain Current	V <sub>GS</sub> at 10 V	$T_C = 25 ^{\circ}C$ $T_C = 100 ^{\circ}C$		5.5		
	VGS at 10 V	T <sub>C</sub> = 100 °C	I <sub>D</sub>	3.5		
Pulsed Drain Current <sup>a</sup>			I <sub>DM</sub>	37		
Linear Derating Factor				0.48	W/°C	
Single Pulse Avalanche Energy <sup>b</sup>			E <sub>AS</sub>	290	mJ	
Repetitive Avalanche Current <sup>a</sup>			I <sub>AR</sub>	9.2	Α	
Repetitive Avalanche Energy <sup>a</sup>			E <sub>AR</sub>	6.0	mJ	
Maximum Power Dissipation	T <sub>C</sub> =	25 °C	$P_{D}$	60	W	
Peak Diode Recovery dV/dt <sup>c</sup>			dV/dt	5.0	V/ns	
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	-55 to +150		
Soldering Recommendations (Peak temperature) d	for 10 s		-	300	°C	
Mounting Torque	6-32 or M3 screw			10	lbf ⋅ in	
				1.1	N⋅m	

#### Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Starting  $T_J$  = 25 °C, L = 6.8 mH,  $R_G$  = 25  $\Omega$ ,  $I_{AS}$  = 9.2 A (see fig. 12).
- c.  $I_{SD} \le 9.2$  A,  $dI/dt \le 50$  A/ $\mu$ s,  $V_{DD} \le V_{DS}$ ,  $T_J \le 150$  °C.
- d. 1.6 mm from case.



www.vishay.com

Vishay Siliconix

THERMAL RESISTANCE RATINGS					
PARAMETER	SYMBOL	TYP.	MAX.	UNIT	
Maximum Junction-to-Ambient	$R_{thJA}$	-	65	°C/W	
Maximum Junction-to-Case (Drain)	$R_{thJC}$	-	2.1	G/ VV	

PARAMETER	SYMBOL	TES	MIN.	TYP.	MAX.	UNIT	
Static					•	•	
Drain-Source Breakdown Voltage	V <sub>DS</sub>	V <sub>GS</sub>	600	-	-	V	
V <sub>DS</sub> Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Referenc	Reference to 25 °C, I <sub>D</sub> = 1 mA d		660	-	mV/°C
Gate-Source Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> :	= V <sub>GS</sub> , I <sub>D</sub> = 250 μA	2.0	-	4.0	V
Gate-Source Leakage	I <sub>GSS</sub>		$V_{GS} = \pm 30 \text{ V}$		-	± 100	nA
Zero Gate Voltage Drain Current	l	V <sub>DS</sub> = 600 V, V <sub>GS</sub> = 0 V		-	-	25	μΑ
Zeio Gate Voltage Drain Gunent	I <sub>DSS</sub>	$V_{DS} = 480 \text{ V}$	$V_{V}$ , $V_{QS} = 0$ $V_{V}$ , $V_{J} = 125$ $^{\circ}$ C	1	-	250	μΑ
Drain-Source On-State Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	$I_D = 3.3 \text{ A}^{\text{ b}}$	1	-	0.75	Ω
Forward Transconductance	9 <sub>fs</sub>	V <sub>DS</sub>	V <sub>DS</sub> = 25 V, I <sub>D</sub> = 5.5 A		-	-	S
Dynamic							
Input Capacitance	$C_{iss}$	V <sub>GS</sub> = 0 V,		-	1400	-	
Output Capacitance	C <sub>oss</sub>		$V_{DS} = 25 \text{ V},$		180	-	
Reverse Transfer Capacitance	$C_{rss}$	f = 1.0 MHz, see fig. 5		-	7.1	-	pF
Output Capacitance			$V_{DS} = 1.0 \text{ V}, f = 1.0 \text{ MHz}$	-	1957	-	- pr -
Output Capacitance	C <sub>oss</sub>	$V_{GS} = 0 V$	$V_{DS} = 480 \text{ V}, f = 1.0 \text{ MHz}$	-	49	-	
Effective Output Capacitance	Coss eff.		$V_{DS} = 0 V \text{ to } 480 V^c$	-	96	-	
Total Gate Charge	$Q_g$		$V_{GS} = 10 \text{ V}$ $I_D = 9.2 \text{ A}, V_{DS} = 400 \text{ V},$ see fig. 6 and 13 b	ı	-	49	nC
Gate-Source Charge	$Q_{gs}$	V <sub>GS</sub> = 10 V		-	-	13	
Gate-Drain Charge	Q <sub>gd</sub>		goo ng. o ana ro		-	20	1
Turn-On Delay Time	t <sub>d(on)</sub>				13	-	ns ns
Rise Time	t <sub>r</sub>	$V_{DD}$ = 300 V, $I_{D}$ = 9.2 A, $R_{G}$ = 9.1 $\Omega$ , $R_{D}$ = 35.5 $\Omega$ , see fig. 10 b		-	25	-	
Turn-Off Delay Time	t <sub>d(off)</sub>			-	30	-	
Fall Time	t <sub>f</sub>			-	22	-	
Gate Input Resistance	R <sub>g</sub>	f = 1 MHz, open drain		0.5	-	3.2	Ω
<b>Drain-Source Body Diode Characteristic</b>	es						
Continuous Source-Drain Diode Current	Is	MOSFET symbol showing the integral reverse p - n junction diode		-	-	5.5	
Pulsed Diode Forward Current <sup>a</sup>	I <sub>SM</sub>			-	-	37	- A
Body Diode Voltage	$V_{SD}$	$T_J = 25  ^{\circ}\text{C},  I_S = 9.2  \text{A},  V_{GS} = 0  \text{V}^{ \text{b}}$		-	-	1.5	V
Body Diode Reverse Recovery Time	t <sub>rr</sub>	$T_J = 25 \text{ °C}, I_F = 9.2 \text{ A, dI/dt} = 100 \text{ A/}\mu\text{s}^{\text{b}}$		-	530	800	ns
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>			-	3.0	4.4	μC
Forward Turn-On Time	t <sub>on</sub>	Intrinsic turn-on time is negligible (turn-on is dominated by L <sub>S</sub> and L				L <sub>D</sub> )	

#### Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width  $\leq 300~\mu s;$  duty cycle  $\leq 2~\%.$
- c.  $C_{oss}$  eff. is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 % to 80 %  $V_{DS}$ .
- d. t = 60 s, f = 60 Hz.

Vishay Siliconix

## TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics




Fig. 2 - Typical Output Characteristics




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area

Vishay Siliconix




Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case






Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit



### Peak Diode Recovery dV/dt Test Circuit






Fig. 14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <a href="https://www.vishay.com/ppg?91175">www.vishay.com/ppg?91175</a>.



# **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000