

Wiha SYSTEM 4.

Ideal for precision work.



Colour-coded ChromTop® tips for maximum clarity.

Due to its versatility and quality the Wiha **SYSTEM 4** is a reversible blade system that convinces every user.

Either for slotted, Phillips, TORX® or hex screws, the wide product range provides the right model for every application.

All reversible blades are made of high-quality CVM-steel, through hardened and chrome-plated, which provides an extra long service-life. The Wiha ChromTop® tips guarantee a perfect fit every time.

Just choose from the **SYSTEM 4** products for the relevant tool. Following handles are offered.

- The ergonomic **SoftFinish® telescopic handle**.
- The dissipative **SoftFinish® telescopic ESD handle**.

Each with adjustable blade lengths from 18 – 90 mm.

We offer **SYSTEM 4** sets in compact roll-up pouches, rigid metal and easy access plastic boxes.




Convincing variety and quality. **SYSTEM 4** – a real multi-tasker.



Wiha **SYSTEM 4**.

- Versatile reversible precision blade system
- Sets in compact roll-up pouches, rigid metal- or easy access plastic-boxes
- Ergonomic handles for almost every application
- Colour-coded blades made of high-quality, tough chrome-vanadium-molybdenum steel, through hardened, chrome-plated
- Wiha ChromTop® tips ensure a perfect fit every time



The **ClickStop** ball clamp in each telescopic handle allows 24 different visible blade lengths between 18 and 90 mm in 3 mm increments.

SYSTEM 4 handles.


2691 SYSTEM 4 SoftFinish®-telescopic handle.
Ergonomic multi-component handle with roll-off protection.

Handle: With 4 mm hex retainer for all SYSTEM 4 blades.
 Enables adjustable blade lengths from 18 - 90 mm.
 ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Application: Ideal for all precision work in the fields of electronics and mechanics.

Order-No.	⌀	↔	⊕	⊖
30373	4.0	105	23	10


2691ESD SYSTEM 4 SoftFinish®-telescopic ESD handle.
Dissipative handle, ESD-safe.

Handle: Ergonomic multi-component handle with roll-off protection.
 With 4 mm hex retainer for all SYSTEM 4 blades.
 Enables adjustable blade lengths from 18 - 90 mm.
 ClickStop ball clamp guarantees a secure hold and rapid blade exchange.

Surface resistance $10^6 - 10^9$ ohms.

Standards: IEC 61340-5-1.

Application: For working on electrostatically sensitive components.

Order-No.	⌀	↔	⊕	⊖
31498	4.0	105	23	10

**Safety Notice:**

Wiha ESD screwdrivers are non-insulated, therefore not suitable for working on live parts.

SYSTEM 4 reversible blades.

**269** SYSTEM 4 slotted reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Colour-coded Wiha ChromTop® tips.

Order-No.	⌀	⌀	⊖	⊖	↔	⊕	⊖
00576	1.5	3.0	0.25	0.5	120	4.0	5
00577	2.0	3.5	0.4	0.6	120	4.0	5
00578	2.5	4.0	0.4	0.8	120	4.0	5

**269** SYSTEM 4 slotted Phillips reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Colour-coded Wiha ChromTop® tips.

Order-No.	⌀	⊕	⊖	↔	⊕	⊖
00601	2.0	PH00	0.4	120	4.0	5
00602	3.0	PH0	0.5	120	4.0	5
00603	4.0	PH1	0.8	120	4.0	5

**269** SYSTEM 4 Phillips reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Colour-coded Wiha ChromTop® tips.

Order-No.	⊕	⊕	↔	⊕	⊖
00579	PH000	PH00	120	4.0	5
00580	PH0	PH1	120	4.0	5

**269** SYSTEM 4 Pozidriv reversible blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Colour-coded Wiha ChromTop® tips.

Order-No.	⊕	⊕	↔	⊕	⊖
03186	PZ0	PZ1	120	4.0	5