

## ED-204 Ethernet to Digital I/O +RS232 +Switch

4 Digital I/O Lines with RS232 Serial Port

- 4 Digital Ports independently can be In or Out
- 1 RS232 Serial Port
- · 2 Ethernet Port
- User friendly software interface Simple web based configuration, monitoring and control
- · Software APIs for VB, C# and more

















Easy to set up with LED status lights for Digital I/O lines that correspond to simple to read webpage



+5 to +30 Volt Power Input enables the device to be run from USB, a vehicle battery or the factory floor



Integral wall mount option can be used with MK-048 clips to allow DIN rail mounting























### ED-204

### Ethernet to Digital I/O +RS232 +Switch

Integrate with popular software packages or use with our free APIs

LED status lights

Ethernet Switch Easy Wire Removable screw terminal blocks

Wide Range Input Power: +5VDC to +30VDC

Wall mount holes compatible with MK-048 DIN mount clips

View from webpage - no software required

ETHERNET 1

STATUS
DI/O ACTIVITY
NETWORK
RS232 PORT

ETHERNET
TO
REMOTE I/O

RS232 PORT

DIGITAL I/O

2 2 2 5 6 8 8 8 8 8

IP30 Non-conducting polyamide case

0°C to +60°C/+32°F to +140°F temperature range

Supports Modbus TCP or ASCII commands

RS232 Serial Port


4 Digital I/O Lines

Connectors			
Screw Terminals	3 way $\times$ 0.2inch/5.08mm and 10 way $\times$ 0.2inch/5.08mm pitch		
Wire Thickness	0.150 inch, 3.81mm, 20 pins, 12+8 screw terminals, #26 - #16 AWG, 0.14mm <sup>2</sup> -1.3mm <sup>2</sup>		
Power Supply			
Power Supply input	Unregulated +5V to +30Volts DC, reverse polarity protection		
Isolation	1500VRMS Magnetic isolation from Ethernet		
Environmental			
Operating Temperature	0 <sup>o</sup> C to +60 <sup>o</sup> C / +32°F to +140°F		
Storage Temperature	$0^{\circ}$ C to +70 $^{\circ}$ C / +32 $^{\circ}$ F to +158 $^{\circ}$ F		
Ambient Relative Humidity	5 to 95% (non-condensing)		
Magjack LED Information	'		
Link/Activity LED	Solid green	Connection established	
	Flashing Green	Data communication	
Speed LED	Green	100Base-Tx	
	Unlit	10Base-T	
Ethernet			
Ethernet Port	RJ45 jack, 10/100Mhz autosensing, crossover auto sensing (Auto MDIX)		
Protection	1,500 Volts magnetic isolation between ports		
Housing	IP-30 rated non-conducting polyamide case		



# ED-204

### Ethernet to Digital I/O +RS232 +Switch



#### Terminal Block Pin Outs

PIN	FUNCTION	
1	TxD	
2	RxD	
3	RTS	
4	CTS	
5	GND	
6	DIO 3	
7	DIO 2	
8	DIO 1	
9	DIO 0	
10	GND	

**Ethernet Port Pin Outs** 

PIN	FUNCTION
1	RD+ / TD+
2	RD- / TD-
3	TD+ / RD+
4	NC
5	NC
6	TD- / RD-
7	NC
8	NC

Power Terminal Pin Outs

PIN	FUNCTION	
1	+V	
2	-V	
3	Functional Earth	

### Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.



## ED-204 Ethernet to Digital I/O +RS232 +Switch

ED-204	Ethernet to Digital I/O +RS232 +Switch			
Digital Channels - 4 Ports individually selectable as Inputs or Outputs				
Inputs				
NPN/PNP	Individually jumper selectable pull up for NPN, active low, type sensors and pull down for PNP, active high, type sensors			
Logic Level 0:	0V to +1V			
Logic Level 1:	+2V to +30V			
Latched Inputs:	Triggered by user programmable positive or negative edges, stays true until acknowledged			
Counter Inputs:	User programmable- counts positive or negative transitions 0-65335			
Outputs				
Maximum output current	Sinks up to 0.85 Amp per pin, 30V max load Max combined load 3.4 Amps per ED device			
Characteristic:	Open drain output, protected MosFET intelligent short circuit protection up to 36V Over temperature shutdown :175°C typical 150°C min			
Maximum output load Voltage	30V			
ESD Production	16kV			
Quick-Stop function	When a user programmable input transitions to a preconfigured high or low state then all outputs go to a user programmable known good state			
Serial Port - RS232				
Baud Rate	From 110 - 1 MegaBaud - Any custom Baud rate accepted			
Data Bits	5,6,7 or 8			
Parity	Odd, Even, None, Mark or Space			
Stop Bits	1 or 2			
Flow Control	RTS/CTS, XON/XOFF			
Tx/Rx Modes	'Rx Modes Point to Point			
Power Supply				
Power Supply input	upply input Unregulated +5V to +30Volts DC, reverse polarity protection			
Isolation	1500VRMS Magnetic isolation from Ethernet			
Power Consumption	Consumption 2.5 Watts Max : 220 mAmps@+5VDC/36mAmps@+30VDC			
Ethernet Switch	Additional Ethernet Port allowing Daisy chaining			



## Software

OS Compatibility Brainboxes' software provides a TCP or Serial COM port interface. All

software versions and updates available to download from our website.

Microsoft Legacy COM port drivers for Microsoft OS up to latest Windows 10

Other TCP and web browser interface for other OSs & Linux, e.g. Android,

Raspberry Pi





















Boost.IO Manager	Lets you find, install and upgrade devices


Industry Standard Packages The COM port based driver means devices are compatible with popular

packages such as: LabView, MATLAB, Agilent VEE. So you can continue to get value from your existing development and process control system.

Software Platforms APIs and sample program code for: Microsoft .NET, C#, Visual Basic, C++,

JavaScript, PHP, Java, Objective-C, Python and more - www.brainboxes.com















#### Modbus

Device works as a Modbus TCP server. Modbus TCP can be used on the input and output lines.

	Modbus access type	Supported Modbus function codes	Logical address	984 style address	IEC 61131 address
Read DI counter values	Holding register	3	0x0000	40001	%MW0
Clear DI counters	Coil	5, 15	0x0200	00513	%M512
Set/read digital outputs	Coil	1, 5, 15	0x0000	00001	%M0

#### **ASCII**

The ED device's webpage has an interactive ASCII console where any command can be entered and it is immediately executed showing the device's response.

\$01M	read the name of device address 01	
!01ED-588	device 01 replies that its name is ED-588	
\$01F	read firmware version number of device address 01	
!012.54	firmware version of device 01 is 2.54	

Full command tables can be found in the device manual











### ED-204 Ethernet to Digital I/O +RS232 +Switch

Packaging Information

Packaging Installation CD including manual, Microsoft signed drivers & utilities,

Quick Start Guide

Device

Packaged Weight 0.230 kg, 8.11 ounces

Packaged Dims 160x135x49 mm, 6.3x5.3x1.9 inches

GTIN Universal Code 837324009842

**Approvals** 

Industry Approvals Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), CE

**Product Support** 

Warranty Lifetime - online registration required

Support Lifetime Web, Email and Phone Support from fully qualified, friendly staff

who work in and alongside the Product Development Team

Additional Information

OEM option Available for bulk buy OEM

Made In Manufactured in the UK by Brainboxes Winner 2005 European Electronics

Industry Awards 'Manufacturer of the Year'

Customisable Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users.

More info:sales@brainboxes.com



#### PW-600

Power supply with connectors for UK, USA, EU and AUS mains socket. 'Tails' are suitable for connecting to screw terminal blocks.



#### MK-048

DIN Rail Mounting Kit Enables device to be clipped onto a DIN rail.



### ED Range

Remote I/O products available in a range of formats and specifications.

www.brainboxes.com

© Brainboxes 2020 BBEDS050320