

SILICON PHOTO DIODES
BL-L512PD
■ Features:

- 5.1*3.0*7.4mm SILICON PHOTO DIODES
- Choice of various viewing angles.
- Diffused and Water clear lens are available.
- Fast response time.
- High photo sensitivity.
- Small junction capacitance.
- The epoxy package itself is an IR filter, spectrally matched to GaAs or GaAlAs IR emitter.


■ Applications:

- High speed photo detector
- Camera
- Infrared remote controller for TVs VCR, audio equipment, air conditioner, etc.

■ Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Rating	Unit
Power Dissipation	P_d	150	mW
Reverse Voltage	V_R	35	V
Operation Temperature	T_{OPR}	-40 to +80	°C
Storage Temperature	T_{STG}	-40 to +85	°C
Lead Soldering Temperature	TSOL	Max.260±5°C for 3 sec Max. (1.6mm from the base of the epoxy bulb)	°C


■ Electronic Optical Characteristics at Ta=25°C

Items	Symbol	Min.	Typ.	Max.	Unit	Condition
Wavelength of Peak Sensitivity	λ_p	-	940	-	nm	-
Open Circuit Voltage	V_{OC}	-	0.40	-	V	H=5mW/cm ²
Short Circuit Current	I_{SC}	-	2	-	uA	$\lambda_p=940nm$
Reverse Light Current	I_L	-	3.5	-	uA	H=5mW/cm ² $\lambda_p=940nm$ $V_R=5V$
Reverse Dark Current	I_D	-	-	10	nA	H=0mW/cm ² $V_R=10V$
Reverse Break down Voltage	V_{BR}	35	170	-	V	H=0mW/cm ² $I_R=100uA$
Viewing angle	$2\theta_{1/2}$	-	35	-	Deg	
Rise/Fall Time	T_r/T_f	-	6/6	-	nS	$R_L=1000\Omega$ $V_R=10V$

SILICON PHOTO DIODES

BL-L512PD

■ Package configuration & Internal circuit diagram



Notes:

1. All dimensions are in millimeters (inches)
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.
3. Specifications are subject to change without notice.







SILICON PHOTO DIODES

BL-L512PD

Typical electrical-optical characteristics curves:



- | | |
|-------------------------------------------|--------------------------------------|
| (1) - GaAsP/GaAs 655nm/Red | (9) - GaAlAs 880nm |
| (2) - GaP 570nm/Yellow Green | (10) - GaAs/GaAs & GaAlAs/GaAs 940nm |
| (3) - GaAsP/GaP 585nm/Yellow | (A) - GaN/SiC 430nm/Blue |
| (4) - GaAsP/GaP 635nm/Orange & Hi-Eff Red | (B) - InGaN/SiC 470nm/Blue |
| (5) - GaP 700nm/Bright Red | (C) - InGaN/SiC 505nm/Ultra Green |
| (6) - GaAlAs/GaAs 660nm/Super Red | (D) - InGaN/SiC 525nm/Ultra Green |
| (8) - GaAsP/GaP 610nm/Super Red | |



NOTE:25°C free air temperature unless otherwise specified