













bq27531-G1 SLUSBE7C - MARCH 2013-REVISED JANUARY 2016

# bg27531-G1 Battery Management Unit Impedance Track™ Fuel Gauge With MaxLife™ Technology for Use With the bg2419x Charger Controller

#### **Features**

- Battery Fuel Gauge and Charger Controller for 1-Cell Li-Ion Applications
- Resides on System Main Board
- Battery Fuel Gauge Based on Patented Impedance Track™ Technology
  - Models the Battery Discharge Curve for Accurate Time-to-Empty Predictions
  - Automatically Adjusts for Battery Aging, Battery Self-Discharge, and Temperature/Rate Inefficiencies
  - Low-Value Sense Resistor (5 m $\Omega$  to 20 m $\Omega$ )
- Battery Charger Controller With Customizable Charge Profiles
  - Configurable Charge Voltage and Current Based on Temperature
  - Optional State of Health (SoH) and Multilevel-**Based Charge Profiles**
- Host-Free Autonomous Battery Management System
  - Reduced Software Overhead Allows for Easy Portability Across Platforms and Shorter OEM Design Cycles
  - Higher Safety and Security
- Intelligent Charging—Customized and Adaptive **Charging Profiles** 
  - Charger Control Based on SoH
  - Temperature Level Charging (TLC)
- Battery Charger Controller for bg2419x Single-Cell Switched-Mode Battery Charger
  - Stand-Alone Charging Solution
  - SHIP Mode Capability
- 400-kHz I<sup>2</sup>C Interface for Connection to System Microcontroller Port
- In a 15-Pin NanoFree™ Packaging

## **Applications**

- Smart Phones, Feature Phones, and Tablets
- Digital Still and Video Cameras
- Handheld Terminals
- MP3 or Multimedia Players

#### 3 **Description**

The Texas Instruments bg27531-G1 system-side Li-Ion Battery Management Unit is a microcontroller peripheral that provides Impedance Track fuel gauging and charging control for single-cell Li-lon battery packs. The device requires little system microcontroller firmware development. Together with the bg2419x Single-Cell Switched-Mode Charger, the manages embedded bq27531-G1 an (nonremovable) or a removable battery pack.

The bq27531-G1 uses the patented Impedance Track algorithm for fuel gauging, and provides information such as remaining battery capacity (mAh), state-ofcharge (%), run time to empty (minimum), battery voltage (mV), temperature (°C), and state of health (%).


Battery fuel gauging with the bg27531-G1 requires only PACK+ (P+), PACK- (P-), and Thermistor (T) connections to a removable battery pack or embedded battery circuit. The CSP option is a 15-pin package in the dimensions of 2.61 mm x 1.96 mm with a 0.5-mm lead pitch, which is ideal for spaceconstrained applications.

# Device Information<sup>(1)</sup>

| PART NUMBER | PACKAGE    | BODY SIZE (NOM)   |
|-------------|------------|-------------------|
| bq27531-G1  | DSBGA (15) | 2.61 mm × 1.96 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### Simplified Schematic





# **Table of Contents**

| 1 | Features 1  |     | 7.14 Typical Characteristics                     | 8  |
|---|---|-----|--|----|
| 2 | Applications 1  | 8   | Detailed Description                             | 9  |
| 3 | Description 1   |     | 8.1 Overview                                     |    |
| 4 | Revision History2   |     | 8.2 Functional Block Diagram                     | 10 |
| 5 | Device Options  |     | 8.3 Feature Description                          | 11 |
| 6 | •   |     | 8.4 Device Functional Modes                      | 12 |
|   | Pin Configuration and Functions   |     | 8.5 Programming                                  | 16 |
| 7 | Specifications4   | 9   | Application and Implementation                   |    |
|   | 7.1 Absolute Maximum Ratings  |     | 9.1 Application Information                      |    |
|   | 7.2 ESD Ratings   |     | 9.2 Typical Application                          |    |
|   | 7.3 Recommended Operating Conditions  | 10  | Power Supply Recommendations                     |    |
|   | 7.4 Thermal Information   | . • | 10.1 Power Supply Decoupling                     |    |
|   | 7.5 Electrical Characteristics: Supply Current                                  | 11  | Layout   |    |
|   | 7.6 Digital Input and Output DC Characteristics 5                               |     | 11.1 Layout Guidelines                           |    |
|   | 7.7 Power-On Reset 5  |     | •  |    |
|   | 7.8 2.5-V LDO Regulator 5   | 40  |  |    |
|   | 7.9 Internal Clock Oscillators 5  | 12  | Device and Documentation Support                 |    |
|   | 7.10 ADC (Temperature and Cell Measurement)                                     |     | 12.1 Documentation Support                       |    |
|   | Characteristics   |     | 12.2 Community Resources                         |    |
|   | 7.11 Integrating ADC (Coulomb Counter)  |     | 12.3 Trademarks                                  |    |
|   | Characteristics   |     | 12.4 Electrostatic Discharge Caution             |    |
|   | 7.12 Data Flash Memory Characteristics  |     | 12.5 Glossary                                    | 28 |
|   | 7.13 I <sup>2</sup> C-Compatible Interface Communication Timing Characteristics | 13  | Mechanical, Packaging, and Orderable Information | 28 |

# 4 Revision History


| Changes from Revision B (September 2015) to Revision C      | Page |
|---|------|
| Changed ESD Ratings   |      |
| Changes from Revision A (June 2015) to Revision B           | Page |
| Changed a Pin Functions description to correct the TRM link |      |
| Changed Figure 6  | 13   |
| Added Figure 7  | 14   |



# **Device Options**

| PART NUMBER    | FIRMWARE<br>VERSION | COMMUNICATION<br>FORMAT |
|----------------|---------------------|-------------------------|
| bq27531YZFR-G1 | 1.02                | 120                     |
| bq27531YZFT-G1 | (0x0102)            | I-C                     |

# 6 Pin Configuration and Functions



| DIM | MIN  | TYP  | MAX  | UNITS |  |
|-----|------|------|------|-------|--|
| D   | 2580 | 2610 | 2640 | um    |  |
| E   | 1926 | 1956 | 1986 | μm    |  |

#### **Pin Functions**

| PIN             | l        | (1) |   |  |  |  |
|-----------------|----------|-----|---|--|--|--|
| NAME            | NAME NO. |     | DESCRIPTION   |  |  |  |
| BAT             | E2       | 1   | Cell voltage measurement input. ADC input. Recommend 4.8 V maximum for conversion accuracy.   |  |  |  |
| BI/TOUT         | E3       | I/O | Battery insertion detection input. Power pin for pack thermistor network. Thermistor multiplexer control pin. Use with pullup resistor >1 M $\Omega$ (1.8 M $\Omega$ typical).  |  |  |  |
| BSDA            | C3       | I/O | Battery Charger data line for chipset communication. Push-pull output.  |  |  |  |
| BSCL            | B2       | 0   | Battery Charger clock output line for chipset communication. Push-pull output.  |  |  |  |
| CE              | D2       | I   | Chip Enable. Internal LDO is disconnected from REGIN when driven low. <b>Note:</b> CE has an internal ESD protection diode connected to REGIN. Recommend maintaining V <sub>CE</sub> ≤ V <sub>REGIN</sub> under all conditions. |  |  |  |
| REGIN           | E1       | Р   | Regulator input. Decouple with 0.1-µF ceramic capacitor to Vss.   |  |  |  |
| SCL             | А3       | I   | Slave $^{12}$ C serial communications clock input line for communication with system (Master). Open-drain I/O. Use with $^{10-k\Omega}$ pullup resistor (typical).  |  |  |  |
| SDA             | В3       | I/O | Slave $I^2C$ serial communications data line for communication with system (Master). Open-drain I/O. Use with $10-k\Omega$ pullup resistor (typical).   |  |  |  |
| SOC_INT         | A2       | I/O | SOC state interrupts output. Generates a pulse as described in the <i>bq27531-G1 Technical Reference Manual</i> (SLUUA96). Open-drain output.   |  |  |  |
| SRN             | B1       | IA  | Analog input pin connected to the internal coulomb counter where SRN is nearest the Vss connection. Connect to 5- $m\Omega$ to 20- $m\Omega$ sense resistor.  |  |  |  |
| SRP             | A1       | IA  | Analog input pin connected to the internal coulomb counter where SRP is nearest the PACK– connection. Connect to $5-m\Omega$ to $20-m\Omega$ sense resistor.  |  |  |  |
| TS              | D3       | IA  | Pack thermistor voltage sense (use 103AT-type thermistor). ADC input.   |  |  |  |
| V <sub>CC</sub> | D1       | Р   | Regulator output and bq27531-G1 power. Decouple with 1-µF ceramic capacitor to Vss.   |  |  |  |
| V <sub>SS</sub> | C1, C2   | Р   | Device ground   |  |  |  |

(1) I/O = Digital input/output, IA = Analog input, P = Power connection



# 7 Specifications

## 7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                    |   | MIN  | MAX                   | UNIT     |
|--------------------|---|------|-----------------------|----------|
| V                  | Regulator input   | -0.3 | 5.5                   | <b>V</b> |
| V <sub>REGIN</sub> |   | -0.3 | 6.0 <sup>(2)</sup>    | V        |
| $V_{CE}$           | CE input pin  | -0.3 | $V_{REGIN} + 0.3$     | V        |
| $V_{CC}$           | Supply voltage  | -0.3 | 2.75                  | ٧        |
| $V_{IOD}$          | Open-drain I/O pins (SDA, SCL, SOC_INT)                             | -0.3 | 5.5                   | ٧        |
| V                  | DAT innut sin   | -0.3 | 5.5                   | <b>V</b> |
| $V_{BAT}$          | BAT input pin   | -0.3 | 6.0 <sup>(2)</sup>    | ٧        |
| VI                 | Input voltage to all other pins (BI/TOUT, TS, SRP, SRN, BSDA, BSCL) | -0.3 | V <sub>CC</sub> + 0.3 | V        |
| T <sub>A</sub>     | Operating free-air temperature                                      | -40  | 85                    | °C       |

<sup>(1)</sup> Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 7.2 ESD Ratings

|                    |                         |  | VALUE | UNIT |
|--------------------|-------------------------|--|-------|------|
|                    |                         | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, BAT pin <sup>(1)</sup> | ±1500 |      |
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001), All other pins (1)    | ±2000 | V    |
|                    | districtings            | Charged device model (CDM), per JEDEC specification JESD22-C101 (2)        | ±250  |      |

<sup>(1)</sup> JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 7.3 Recommended Operating Conditions

 $T_A = -40$ °C to 85°C,  $V_{REGIN} = V_{BAT} = 3.6$  V (unless otherwise noted)

|                    | -   |   | MIN  | NOM | MAX | UNIT |
|--------------------|---|---|------|-----|-----|------|
| V <sub>REGIN</sub> | Supply voltage  | No operating restrictions   | 2.8  |     | 4.5 | V    |
|                    | Supply voltage  | No flash writes   | 2.45 |     | 2.8 |      |
| C <sub>REGIN</sub> | External input capacitor for internal LDO between REGIN and $V_{\mbox{\footnotesize SS}}$ | Nominal capacitor values specified.  Recommend a 5% ceramic X5R type capacitor located close to the device. |      | 0.1 |     | μF   |
| C <sub>LDO25</sub> | External output capacitor for internal LDO between $V_{\text{CC}}$ and $V_{\text{SS}}$    |   | 0.47 | 1   |     | μF   |
| t <sub>PUCD</sub>  | Power-up communication delay  |   |      | 250 |     | ms   |

### 7.4 Thermal Information

| UNIT |
|------|
| T    |
|      |
| °C/W |
| _    |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

<sup>(2)</sup> Condition not to exceed 100 hours at 25°C lifetime.

<sup>(2)</sup> JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



# 7.5 Electrical Characteristics: Supply Current

 $T_A = 25$ °C and  $V_{REGIN} = V_{BAT} = 3.6$  V (unless otherwise noted)

| PARAMETER TEST CONDITIONS MIN TYP MAX |                                  |   |        |     |       |      |
|---------------------------------------|----------------------------------|---|--------|-----|-------|------|
|                                       | TANAMILILIN                      | TEST CONDITIONS   | IVIIIV |     | IVIAA | UNIT |
| I <sub>CC</sub> <sup>(1)</sup>        | NORMAL operating mode current    | Fuel gauge in NORMAL mode I <sub>LOAD</sub> > <i>Sleep current</i>        |        | 118 |       | μΑ   |
| I <sub>SLP+</sub> <sup>(1)</sup>      | SLEEP+ operating mode current    | Fuel gauge in SLEEP+ mode I <sub>LOAD</sub> < <i>Sleep current</i>        |        | 62  |       | μΑ   |
| I <sub>SLP</sub> <sup>(1)</sup>       | Low-power storage mode current   | Fuel gauge in SLEEP mode I <sub>LOAD</sub> < <i>Sleep current</i>         |        | 23  |       | μΑ   |
| I <sub>HIB</sub> <sup>(1)</sup>       | HIBERNATE operating mode current | Fuel gauge in HIBERNATE mode I <sub>LOAD</sub> < <i>Hibernate current</i> |        | 8   |       | μΑ   |

<sup>(1)</sup> Specified by design. Not production tested.

## 7.6 Digital Input and Output DC Characteristics

 $T_A = -40$ °C to 85°C, typical values at  $T_A = 25$ °C and  $V_{REGIN} = 3.6$  V (unless otherwise noted)

|                      | PARAMETER   | TEST CONDITIONS                                       | MIN                   | TYP MAX               | UNIT |  |
|----------------------|---|---|-----------------------|-----------------------|------|--|
| $V_{OL}$             | Output voltage, low (SCL, SDA, SOC_INT, BSDA, BSCL) | I <sub>OL</sub> = 3 mA                                |                       | 0.4                   | V    |  |
| V <sub>OH(PP)</sub>  | Output voltage, high (BSDA, BSCL)                   | I <sub>OH</sub> = -1 mA                               | V <sub>CC</sub> - 0.5 |                       |      |  |
| V <sub>OH(OD)</sub>  | Output voltage, high (SDA, SCL, SOC_INT)            | External pullup resistor connected to V <sub>CC</sub> | V <sub>CC</sub> - 0.5 |                       | V    |  |
| V                    | Input voltage, low (SDA, SCL)                       |   | -0.3                  | 0.6                   | V    |  |
| $V_{IL}$             | Input voltage, low (BI/TOUT)                        | BAT INSERT CHECK mode active                          | -0.3                  | 0.6                   |      |  |
| V                    | Input voltage, high (SDA, SCL)                      |   | 1.2                   |                       | .,   |  |
| $V_{IH}$             | Input voltage, high (BI/TOUT)                       | BAT INSERT CHECK mode active                          | 1.2                   | V <sub>CC</sub> + 0.3 | V    |  |
| $V_{IL(CE)}$         | Input voltage, low (CE)                             | 2011-151  |                       | 0.8                   |      |  |
| V <sub>IH(CE)</sub>  | Input voltage, high (CE)                            | V <sub>REGIN</sub> = 2.8 V to 4.5 V                   | 2.65                  |                       | V    |  |
| I <sub>lkg</sub> (1) | Input leakage current (I/O pins)                    |   |                       | 0.3                   | μΑ   |  |

<sup>(1)</sup> Specified by design. Not production tested.

### 7.7 Power-On Reset

 $T_A = -40$ °C to 85°C, typical values at  $T_A = 25$ °C and  $V_{REGIN} = 3.6$  V (unless otherwise noted)

|                  | PARAMETER   | TEST CONDITIONS | MIN  | TYP  | MAX  | UNIT |
|------------------|---|-----------------|------|------|------|------|
| V <sub>IT+</sub> | Positive-going battery voltage input at $V_{\text{CC}}$ |                 | 2.05 | 2.15 | 2.20 | V    |
| $V_{HYS}$        | Power-on reset hysteresis                               |                 |      | 115  |      | mV   |

## 7.8 2.5-V LDO Regulator

 $T_A = -40$ °C to 85°C,  $C_{LDO25} = 1 \mu F$ ,  $V_{REGIN} = 3.6 V$  (unless otherwise noted)

|                    | PARAMETER                        | TEST CONDITION  | MIN | TYP | MAX | UNIT |
|--------------------|----------------------------------|---|-----|-----|-----|------|
|                    |                                  | $2.8 \text{ V} \le \text{V}_{\text{REGIN}} \le 4.5 \text{ V}, \text{ I}_{\text{OUT}} \le 16 \text{ mA}^{(1)}$         | 2.3 | 2.5 | 2.6 |      |
| V <sub>REG25</sub> | Description and substitution (A) | $2.45 \text{ V} \le \text{V}_{\text{REGIN}} < 2.8 \text{ V (low battery)},$<br>$\text{I}_{\text{OUT}} \le 3\text{mA}$ | 2.3 |     |     | V    |

<sup>(1)</sup> LDO output current, I<sub>OUT</sub>, is the total load current. LDO regulator must be used to power internal fuel gauge only.

### 7.9 Internal Clock Oscillators

Copyright © 2013-2016, Texas Instruments Incorporated

 $T_A = -40$ °C to 85°C, 2.4 V <  $V_{CC}$  < 2.6 V; typical values at  $T_A = 25$ °C and  $V_{CC} = 2.5$  V (unless otherwise noted)

| PARAMETER  |                           | TEST CONDITIONS | MIN | TYP    | MAX | UNIT |
|------------|---------------------------|-----------------|-----|--------|-----|------|
| fosc       | High-frequency oscillator |                 |     | 8.389  |     | MHz  |
| $f_{LOSC}$ | Low-frequency oscillator  |                 |     | 32.768 |     | kHz  |

Draduat Folder Links, heart



# 7.10 ADC (Temperature and Cell Measurement) Characteristics

 $T_A = -40$ °C to 85°C, 2.4 V <  $V_{CC}$  < 2.6 V; typical values at  $T_A = 25$ °C and  $V_{CC} = 2.5$  V (unless otherwise noted)

|                                  | PARAMETER                                | TEST CONDITIONS                       | MIN                        | TYP | MAX | UNIT  |
|----------------------------------|--|---------------------------------------|----------------------------|-----|-----|-------|
| V <sub>ADC1</sub>                | Input voltage (TS)                       |                                       | V <sub>SS</sub> –<br>0.125 |     | 2   | V     |
| V <sub>ADC2</sub>                | Input voltage (BAT)                      |                                       | V <sub>SS</sub> –<br>0.125 |     | 5   | V     |
| V <sub>IN(ADC)</sub>             | Input voltage                            |                                       | 0.05                       |     | 1   | V     |
| G <sub>TEMP</sub>                | Internal temperature sensor voltage gain |                                       |                            | -2  |     | mV/°C |
| t <sub>ADC_CONV</sub>            | Conversion time                          |                                       |                            |     | 125 | ms    |
|                                  | Resolution                               |                                       | 14                         |     | 15  | bits  |
| V <sub>OS(ADC)</sub>             | Input offset                             |                                       |                            | 1   |     | mV    |
| Z <sub>ADC1</sub> (1)            | Effective input resistance (TS)          |                                       | 8                          |     |     | МΩ    |
|                                  | Effective involved in the CDATA          | bq27531-G1 not measuring cell voltage | 8                          |     |     | ΜΩ    |
| Z <sub>ADC2</sub> <sup>(1)</sup> | Effective input resistance (BAT)         | bq27531-G1 measuring cell voltage     |                            | 100 |     | kΩ    |
| I <sub>lkg(ADC)</sub> (1)        | Input leakage current                    |                                       |                            |     | 0.3 | μA    |

<sup>(1)</sup> Specified by design. Not tested in production.

## 7.11 Integrating ADC (Coulomb Counter) Characteristics

 $T_A = -40$ °C to 85°C, 2.4 V <  $V_{CC}$  < 2.6 V; typical values at  $T_A = 25$ °C and  $V_{CC} = 2.5$  V (unless otherwise noted)

| A = 40 0 to 00 0, 2.4 v < v <sub>CC</sub> < 2.5 v, typical values at 1 <sub>A</sub> = 20 0 and v <sub>CC</sub> = 2.5 v (unless otherwise noted) |  |                                  |        |         |         |      |
|---|--|----------------------------------|--------|---------|---------|------|
|   | PARAMETER                                  | TEST CONDITIONS                  | MIN    | TYP     | MAX     | UNIT |
| $V_{SR}$  | Input voltage, $V_{(SRP)}$ and $V_{(SRN)}$ | $V_{SR} = V_{(SRP)} - V_{(SRN)}$ | -0.125 |         | 0.125   | V    |
| t <sub>SR_CONV</sub>  | Conversion time                            | Single conversion                |        | 1       |         | s    |
|   | Resolution                                 |                                  | 14     |         | 15      | bits |
| V <sub>OS(SR)</sub>   | Input offset                               |                                  |        | 10      |         | μV   |
| INL   | Integral nonlinearity error                |                                  |        | ±0.007% | ±0.034% | FSR  |
| Z <sub>IN(SR)</sub> (1)   | Effective input resistance                 |                                  | 2.5    |         |         | ΜΩ   |
| I <sub>lkg(SR)</sub> (1)  | Input leakage current                      |                                  |        |         | 0.3     | μΑ   |

<sup>(1)</sup> Specified by design. Not tested in production.

# 7.12 Data Flash Memory Characteristics

 $T_A = -40$ °C to 85°C, 2.4 V <  $V_{CC}$  < 2.6 V; typical values at  $T_A = 25$ °C and  $V_{CC} = 2.5$  V (unless otherwise noted)

|                                | PARAMETER                                     | TEST CONDITIONS | MIN   | TYP | MAX | UNIT   |
|--------------------------------|---|-----------------|-------|-----|-----|--------|
| t <sub>DR</sub> <sup>(1)</sup> | Data retention                                |                 | 10    |     |     | Years  |
|                                | Flash-programming write cycles <sup>(1)</sup> |                 | 20000 |     |     | Cycles |
| twordprog (1)                  | Word programming time                         |                 |       |     | 2   | ms     |
| I <sub>CCPROG</sub> (1)        | Flash-write supply current                    |                 |       | 5   | 10  | mA     |
| t <sub>DFERASE</sub> (1)       | Data flash master erase time                  |                 | 200   |     |     | ms     |
| t <sub>IFERASE</sub> (1)       | Instruction flash master erase time           |                 | 200   |     |     | ms     |
| t <sub>PGERASE</sub> (1)       | Flash page erase time                         |                 | 20    |     |     | ms     |

(1) Specified by design. Not production tested.



# 7.13 I<sup>2</sup>C-Compatible Interface Communication Timing Characteristics

 $T_A = -40$ °C to 85°C, 2.4 V <  $V_{CC}$  < 2.6 V; typical values at  $T_A = 25$ °C and  $V_{CC} = 2.5$  V (unless otherwise noted)

|                       | PARAMETER                            | MIN | NOM MAX | UNIT |
|-----------------------|--------------------------------------|-----|---------|------|
| t <sub>r</sub>        | SCL/SDA rise time                    |     | 300     | ns   |
| t <sub>f</sub>        | SCL/SDA fall time                    |     | 300     | ns   |
| t <sub>w(H)</sub>     | SCL pulse duration (high)            | 600 |         | ns   |
| t <sub>w(L)</sub>     | SCL pulse duration (low)             | 1.3 |         | μs   |
| t <sub>su(STA)</sub>  | Setup for repeated start             | 600 |         | ns   |
| t <sub>d(STA)</sub>   | Start to first falling edge of SCL   | 600 |         | ns   |
| t <sub>su(DAT)</sub>  | Data setup time                      | 100 |         | ns   |
| t <sub>h(DAT)</sub>   | Data hold time                       | 0   |         | ns   |
| t <sub>su(STOP)</sub> | Setup time for stop                  | 600 |         | ns   |
| t <sub>(BUF)</sub>    | Bus free time between stop and start | 66  |         | μs   |
| f <sub>SCL</sub>      | Clock frequency (1)                  |     | 400     | kHz  |

(1) If the clock frequency ( $f_{SCL}$ ) is > 100 kHz, use 1-byte write commands for proper operation. All other transactions types are supported at 400 kHz. (See  $\frac{P}{C}$  Interface and  $\frac{P}{C}$  Command Waiting Time).





Figure 1. I<sup>2</sup>C-Compatible Interface Timing Diagrams



# 7.14 Typical Characteristics





# 8 Detailed Description

#### 8.1 Overview

The fuel gauge accurately predicts the battery capacity and other operational characteristics of a single, Libased, rechargeable cell. It can be interrogated by a system processor to provide cell information, such as remaining capacity and state-of-charge (SOC) as well as SOC interrupt signal to the host.

The fuel gauge can control a bq2419x Charger IC without the intervention from an application system processor. Using the bq27531-G1 and bq2419x chipset, batteries can be charged with the typical constant-current, constant-voltage (CCCV) profile or charged using a Multi-Level Charging (MLC) algorithm.

#### NOTE

## Formatting conventions used in this document:

Commands: italics with parentheses and no breaking spaces, for example, Control()


Data flash: italics, bold, and breaking spaces, for example, Design Capacity

Register bits and flags: brackets and italics, for example, [TDA] Data flash bits: brackets, italics and bold, for example, [LED1]

Modes and states: ALL CAPITALS, for example, UNSEALED mode



# 8.2 Functional Block Diagram





#### 8.3 Feature Description

Information is accessed through a series of commands, called *Standard Commands*. Further capabilities are provided by the additional *Extended Commands* set. Both sets of commands, indicated by the general format *Command()*, are used to read and write information contained within the control and status registers, as well as its data flash locations. Commands are sent from system to gauge using the I<sup>2</sup>C serial communications engine, and can be executed during application development, pack manufacture, or end-equipment operation.

Cell information is stored in nonvolatile flash memory. Many of these data flash locations are accessible during application development. They cannot, generally, be accessed directly during end-equipment operation. Access to these locations is achieved by either use of the companion evaluation software, through individual commands, or through a sequence of data-flash access commands. To access a desired data flash location, the correct data flash subclass and offset must be known.

The key to the high-accuracy gas gauging prediction is the TI proprietary Impedance Track algorithm. This algorithm uses cell measurements, characteristics, and properties to create SOC predictions that can achieve less than 1% error across a wide variety of operating conditions and over the lifetime of the battery.

The fuel gauge measures the charging and discharging of the battery by monitoring the voltage across a small-value series sense resistor (5 to 20 m $\Omega$ , typical) located between the system VSS and the battery PACK-terminal. When a cell is attached to the fuel gauge, cell impedance is computed, based on cell current, cell open-circuit voltage (OCV), and cell voltage under loading conditions.

The external temperature sensing is optimized with the use of a high-accuracy negative temperature coefficient (NTC) thermistor with R25 = 10.0 k $\Omega$  ±1%, B25/85 = 3435 K ±1% (such as Semitec NTC 103AT). The fuel gauge can also be configured to use its internal temperature sensor. When an external thermistor is used, a 18.2-k $\Omega$  pullup resistor between the BI/TOUT and TS pins is also required. The fuel gauge uses temperature to monitor the battery-pack environment, which is used for fuel gauging and cell protection functionality.

To minimize power consumption, the fuel gauge has different power modes: NORMAL, SLEEP, SLEEP+, HIBERNATE, and BAT INSERT CHECK. The fuel gauge passes automatically between these modes, depending upon the occurrence of specific events, though a system processor can initiate some of these modes directly.

For complete operational details, see the bq27531-G1 Technical Reference Manual (SLUUA96).

## 8.3.1 Functional Description

The fuel gauge measures the cell voltage, temperature, and current to determine battery SOC. The fuel gauge monitors the charging and discharging of the battery by sensing the voltage across a small-value resistor (5 m $\Omega$  to 20 m $\Omega$ , typical) between the SRP and SRN pins and in series with the cell. By integrating charge passing through the battery, the battery SOC is adjusted during battery charge or discharge.

The total battery capacity is found by comparing states of charge before and after applying the load with the amount of charge passed. When an application load is applied, the impedance of the cell is measured by comparing the OCV obtained from a predefined function for present SOC with the measured voltage under load. Measurements of OCV and charge integration determine chemical SOC and chemical capacity (Qmax). The initial Qmax values are taken from a cell manufacturer's data sheet multiplied by the number of parallel cells. It is also used for the value in Design Capacity. The fuel gauge acquires and updates the battery-impedance profile during normal battery usage. It uses this profile, along with SOC and the Qmax value, to determine FullChargeCapacity() and StateOfCharge(), specifically for the present load and temperature. FullChargeCapacity() is reported as capacity available from a fully-charged battery under the present load and temperature Voltage() reaches the Terminate Voltage. NominalAvailableCapacity() FullAvailableCapacity() are the uncompensated (no or light load) versions of RemainingCapacity() and FullChargeCapacity(), respectively.

The fuel gauge has two flags accessed by the *Flags()* function that warn when the battery SOC has fallen to critical levels. When *RemainingCapacity()* falls below the first capacity threshold as specified in **SOC1 Set Threshold**, the *[SOC1]* (State of Charge Initial) flag is set. The flag is cleared once *RemainingCapacity()* rises above *SOC1 Clear Threshold*.

When the voltage is discharged to *Terminate Voltage*, the SOC will be set to 0.

Copyright © 2013–2016, Texas Instruments Incorporated



#### 8.4 Device Functional Modes

#### 8.4.1 Power Modes

The fuel gauge has different power modes:

- BAT INSERT CHECK: The BAT INSERT CHECK mode is a powered-up, but low-power halted, state where the fuel gauge resides when no battery is inserted into the system.
- NORMAL: In NORMAL mode, the fuel gauge is fully powered and can execute any allowable task.
- SLEEP: In SLEEP mode, the fuel gauge turns off the high-frequency oscillator and exists in a reduced-power state, periodically taking measurements and performing calculations.
- SLEEP+: In SLEEP+ mode, both low-frequency and high-frequency oscillators are active. Although the SLEEP+ mode has higher current consumption than the SLEEP mode, it is also a reduced power mode.
- HIBERNATE: In HIBERNATE mode, the fuel gauge is in a low power state, but can be woken up by communication or certain I/O activity.

The relationship between these modes is shown in Figure 6 and Figure 7.

#### 8.4.1.1 BAT INSERT CHECK Mode

This mode is a halted-CPU state that occurs when an adapter, or other power source, is present to power the fuel gauge (and system), yet no battery has been detected. When battery insertion is detected, a series of initialization activities begin, which include: OCV measurement, setting the *Flags()* [BAT\_DET] bit, and selecting the appropriate battery profiles.

Some commands, issued by a system processor, can be processed while the fuel gauge is halted in this mode. The gauge wakes up to process the command, then returns to the halted state awaiting battery insertion.

#### 8.4.1.2 NORMAL Mode

The fuel gauge is in NORMAL mode when not in any other power mode. During this mode, *AverageCurrent()*, *Voltage()*, and *Temperature()* measurements are taken, and the interface data set is updated. Decisions to change states are also made. This mode is exited by activating a different power mode.

Because the gauge consumes the most power in NORMAL mode, the Impedance Track algorithm minimizes the time the fuel gauge remains in this mode.

#### 8.4.1.3 **SLEEP Mode**

SLEEP mode is entered automatically if the feature is enabled (*Op Config [SLEEP]* = 1) and *AverageCurrent()* is below the programmable level *Sleep Current*. Once entry into SLEEP mode has been qualified, but prior to entering it, the fuel gauge performs a coulomb counter autocalibration to minimize offset.

During SLEEP mode, the fuel gauge periodically takes data measurements and updates its data set. However, a majority of its time is spent in an idle condition.

The fuel gauge exits SLEEP mode if any entry condition is broken, specifically when:

- AverageCurrent() rises above **Sleep Current**, or
- A current in excess of I<sub>WAKE</sub> through R<sub>SENSE</sub> is detected.

In the event that a battery is removed from the system while a charger is present (and powering the gauge), Impedance Track updates are not necessary. Hence, the fuel gauge enters a state that checks for battery insertion and does not continue executing the Impedance Track algorithm.



### **Device Functional Modes (continued)**




Figure 6. Power Mode Diagram—System Sleep



## **Device Functional Modes (continued)**




Figure 7. Power Mode Diagram—System Shutdown



#### **Device Functional Modes (continued)**

#### 8.4.2 SLEEP+ Mode

Compared to the SLEEP mode, SLEEP+ mode has the high-frequency oscillator in operation. The communication delay could be eliminated. The SLEEP+ mode is entered automatically if the feature is enabled (CONTROL\_STATUS [SNOOZE] = 1) and AverageCurrent() is below the programmable level **Sleep Current**.

During SLEEP+ mode, the fuel gauge periodically takes data measurements and updates its data set. However, a majority of its time is spent in an idle condition.

The fuel gauge exits SLEEP+ mode if any entry condition is broken, specifically when:

- Any communication activity with the gauge, or
- AverageCurrent() rises above Sleep Current, or
- A current in excess of I<sub>WAKE</sub> through R<sub>SENSE</sub> is detected.

#### 8.4.3 HIBERNATE Mode

HIBERNATE mode should be used when the system equipment needs to enter a low-power state, and minimal gauge power consumption is required. This mode is ideal when system equipment is set to its own HIBERNATE, SHUTDOWN, or OFF mode.

Before the fuel gauge can enter HIBERNATE mode, the system must set the CONTROL\_STATUS [HIBERNATE] bit. The gauge waits to enter HIBERNATE mode until it has taken a valid OCV measurement and the magnitude of the average cell current has fallen below **Hibernate Current**. The gauge can also enter HIBERNATE mode if the cell voltage falls below **Hibernate Voltage** and a valid OCV measurement has been taken. The gauge remains in HIBERNATE mode until the system issues a direct I 2 C command to the gauge or a POR occurs. Any I 2 C communication that is not directed to the gauge does not wake the gauge.

It is the responsibility of the system to wake the fuel gauge after it has gone into HIBERNATE mode. After waking, the gauge can proceed with the initialization of the battery information (OCV, profile selection, and so forth).



# 8.5 Programming

### 8.5.1 Data Commands

### 8.5.1.1 Standard Data Commands

The bq27531-G1 uses a series of 2-byte standard commands to enable system reading and writing of battery information. Each standard command has an associated command-code pair, as indicated in Table 1. Because each command consists of two bytes of data, two consecutive I<sup>2</sup>C transmissions must be executed both to initiate the command function, and to read or write the corresponding two bytes of data. Additional details are found in the *bq27531-G1 Technical Reference Manual* (SLUUA96).

**Table 1. Standard Commands** 

| NAME                           | COMMAND CODE  | UNIT     | SEALED<br>ACCESS | UNSEALED ACCESS  |
|--------------------------------|---------------|----------|------------------|------------------|
| Control()                      | 0x00 and 0x01 | NA       | R/W              | R/W              |
| AtRate()                       | 0x02 and 0x03 | mA       | R/W              | R/W              |
| AtRateTimeToEmpty()            | 0x04 and 0x05 | Minutes  | R                | R/W              |
| Temperature()                  | 0x06 and 0x07 | 0.1 K    | R/W              | R/W              |
| Voltage()                      | 0x08 and 0x09 | mV       | R                | R/W              |
| Flags()                        | 0x0A and 0x0B | Hex      | R                | R/W              |
| NominalAvailableCapacity()     | 0x0C and 0x0D | mAh      | R                | R/W              |
| FullAvailableCapacity()        | 0x0E and 0x0F | mAh      | R                | R/W              |
| RemainingCapacity()            | 0x10 and 0x11 | mAh      | R                | R/W              |
| FullChargeCapacity()           | 0x12 and 0x13 | mAh      | R                | R/W              |
| AverageCurrent()               | 0x14 and 0x15 | mA       | R                | R/W              |
| TimeToEmpty()                  | 0x16 and 0x17 | Minutes  | R                | R/W              |
| RemainingCapacityUnfiltered()  | 0x18 and 0x19 | mAh      | R                | R/W              |
| StandbyCurrent()               | 0x1A and 0x1B | mA       | R                | R/W              |
| RemainingCapacityFiltered()    | 0x1C and 0x1D | mAh      | R                | R/W              |
| ProgChargingCurrent()          | 0x1E and 0x1F | mA       | R <sup>(1)</sup> | R <sup>(1)</sup> |
| ProgChargingVoltage()          | 0x20 and 0x21 | mV       | R <sup>(1)</sup> | R <sup>(1)</sup> |
| FullChargeCapacityUnfiltered() | 0x22 and 0x23 | mAh      | R                | R/W              |
| AveragePower()                 | 0x24 and 0x25 | mW       | R                | R/W              |
| FullChargeCapacityFiltered()   | 0x26 and 0x27 | mAh      | R                | R/W              |
| StateOfHealth()                | 0x28 and 0x29 | %/num    | R                | R/W              |
| CycleCount()                   | 0x2A and 0x2B | Counters | R                | R/W              |
| StateOfCharge()                | 0x2C and 0x2D | %        | R                | R/W              |
| TrueSOC()                      | 0x2E and 0x2F | %        | R                | R/W              |
| InstantaneousCurrentReading()  | 0x30 and 0x31 | mA       | R                | R/W              |
| InternalTemperature()          | 0x32 and 0x33 | 0.1 K    | R                | R/W              |
| ChargingLevel()                | 0x34 and 0x35 | Num      | R                | R                |
| LevelTaperCurrent()            | 0x6E and 0x6F | mA       | R                | R                |
| CalcChargingCurrent()          | 0x70 and 0x71 | mA       | R                | R                |
| CalcChargingVoltage()          | 0x72 and 0x73 | V        | R                | R                |

<sup>(1)</sup> Only writeable when *Charger Options [BYPASS]* is set.



### 8.5.1.1.1 Control(): 0x00/0x01

Issuing a *Control()* command requires a subsequent 2-byte subcommand. These additional bytes specify the particular control function desired. The *Control()* command allows the system to control specific features of the bq27531-G1 during normal operation and additional features when the device is in different access modes, as described in Table 2. Additional details are found in the *bq27531-G1 Technical Reference Manual* (SLUUA96).

Table 2. Control() Subcommands

| CNTL FUNCTION      | CNTL<br>DATA | SEALED<br>ACCESS | DESCRIPTION   |
|--------------------|--------------|------------------|---|
| CONTROL_STATUS     | 0x0000       | Yes              | Reports the status of hibernate, IT, and so forth   |
| DEVICE_TYPE        | 0x0001       | Yes              | Reports the device type (for example, 0x0531 for bq27531)   |
| FW_VERSION         | 0x0002       | Yes              | Reports the firmware version on the device type   |
| HW_VERSION         | 0x0003       | Yes              | Reports the hardware version of the device type   |
| PREV_MACWRITE      | 0x0007       | Yes              | Returns previous MAC subcommand code  |
| CHEM_ID            | 0x0008       | Yes              | Reports the chemical identifier of the Impedance Track configuration  |
| BOARD_OFFSET       | 0x0009       | No               | Forces the device to measure and store the board offset   |
| CC_OFFSET          | 0x000a       | No               | Forces the device to measure the internal CC offset   |
| CC_OFFSET_SAVE     | 0x000b       | No               | Forces the device to store the internal CC offset   |
| OCV_CMD            | 0x000c       | Yes              | Request the gauge to take a OCV measurement   |
| BAT_INSERT         | 0x000d       | Yes              | Forces the BAT_DET bit set when the [BIE] bit is 0  |
| BAT_REMOVE         | 0x000e       | Yes              | Forces the BAT_DET bit clear when the [BIE] bit is 0  |
| SET_HIBERNATE      | 0x0011       | Yes              | Forces CONTROL_STATUS [HIBERNATE] to 1  |
| CLEAR_HIBERNATE    | 0x0012       | Yes              | Forces CONTROL_STATUS [HIBERNATE] to 0  |
| SET_SLEEP+         | 0x0013       | Yes              | Forces CONTROL_STATUS [SNOOZE] to 1   |
| CLEAR_SLEEP+       | 0x0014       | Yes              | Forces CONTROL_STATUS [SNOOZE] to 0   |
| OTG_ENABLE         | 0x0015       | Yes              | Commands the bq2419x into USB On The Go mode  |
| OTG_DISABLE        | 0x0016       | Yes              | Disables OTG mode at the bq2419x  |
| DIV_CUR_ENABLE     | 0x0017       | Yes              | Makes the programmed charge current to be half of what is calculated by the gauge charging algorithm.   |
| CHG_ENABLE         | 0x001A       | Yes              | Enable charger. Charge will continue as dictated by gauge charging algorithm.   |
| CHG_DISABLE        | 0x001B       | Yes              | Disable charger (Set CE bit of bq2419x)   |
| GG_CHGRCTL_ENABLE  | 0x001C       | Yes              | Enables the gas gauge to control the charger while continuously resetting the charger watchdog  |
| GG_CHGRCTL_DISABLE | 0x001D       | Yes              | The gas gauge stops resetting the charger watchdog  |
| DIV_CUR_DISABLE    | 0x001E       | Yes              | Makes the programmed charge current to be same as what is calculated by the gauge charging algorithm.   |
| DF_VERSION         | 0x001F       | Yes              | Returns the data flash version  |
| SEALED             | 0x0020       | No               | Places device in SEALED access mode   |
| IT_ENABLE          | 0x0021       | No               | Enables the Impedance Track algorithm   |
| RESET              | 0x0041       | No               | Forces a full reset of the bq27531-G1   |
| SHIPMODE_ENABLE    | 0x0050       | Yes              | Commands the bq2419x to turn off BATFET after a delay time programmed in data flash so that system load does not draw power from battery                                |
| SHIPMODE_DISABLE   | 0x0051       | Yes              | Commands the bq2419x to disregard turning off BATFET before delay time or turns on commands BATFET to turn on if an VBUS had power during the SHIPMODE enabling process |



### 8.5.1.2 Charger Data Commands

The charger registers are mapped to a series of single byte Charger Data Commands to enable system reading and writing of battery charger registers. During charger power up, the registers are initialized to Charger Reset State. The fuel gauge can change the values of these registers during the System Reset State.

Each of the bits in the Charger Data Commands can be read/write. It is important to note that System Access can be different from the read/write access as defined in bq2419x charger hardware. The fuel gauge may block write access to the charger hardware when the bit function is controlled by the fuel gauge exclusively. For example, the [VREGx] bits of Chrgr\_Voltage\_Reg4 are controlled by the fuel gauge and cannot be modified by system.

The bq27531 reads the corresponding registers of System\_Stat\_Reg8() and Fault\_Reg9() every second to mirror the charger status. Other registers in the bq2419x are read when registers are modified by the bq27531.

**Table 3. Charger Data Commands** 

| NAME                    |          | COMMAND CODE | bq2419x<br>CHARGER<br>MEMORY<br>LOCATION | SEALED<br>ACCESS | UNSEALED<br>ACCESS | REFRESH RATE |
|-------------------------|----------|--------------|--|------------------|--------------------|--------------|
| ChargerStatus()         | CHGRSTAT | 0x74         | NA                                       | R                | R                  | Every second |
| Chrgr_InCtrl_Reg0()     | CHGR0    | 0x75         | 0x00                                     | R/W              | R/W                | Data Change  |
| Chrgr_POR_Config_Reg1() | CHGR1    | 0x76         | 0x01                                     | R/W              | R/W                | Data Change  |
| Chrgr_Current_Reg2()    | CHGR2    | 0x77         | 0x02                                     | R/W              | R/W                | Data Change  |
| Chrgr_PreTerm_Reg3()    | CHGR3    | 0x78         | 0x03                                     | R/W              | R/W                | Data Change  |
| Chrgr_Voltage_Reg4()    | CHGR4    | 0x79         | 0x04                                     | R/W              | R/W                | Data Change  |
| Chrgr_TermTimer_Reg5()  | CHGR5    | 0x7a         | 0x05                                     | R/W              | R/W                | Data Change  |
| Chrgr_IRThermal_Reg6()  | CHGR6    | 0x7b         | 0x06                                     | R/W              | R/W                | Data Change  |
| Chrgr_OpCtrl_Reg7()     | CHGR7    | 0x7c         | 0x07                                     | R/W              | R/W                | Data Change  |
| Chrgr_Status_Reg8()     | CHGR8    | 0x7d         | 0x08                                     | R/W              | R/W                | Every Second |
| Chrgr_Fault_Reg9()      | CHGR9    | 0x7e         | 0x09                                     | R/W              | R/W                | Every Second |
| Chrgr_Rev_RegA()        | CHGRA    | 0x7f         | 0x0a                                     | R/W              | R/W                | Data Change  |



#### 8.5.2 Communications

### 8.5.2.1 PC Interface

The fuel gauge supports the standard I<sup>2</sup>C read, incremental read, quick read, one-byte write, and incremental write functions. The 7-bit device address (ADDR) is the most significant 7 bits of the hex address and is fixed as 1010101. The first 8 bits of the I<sup>2</sup>C protocol are, therefore, 0xAA or 0xAB for write or read, respectively.




Figure 8. Supported I<sup>2</sup>C Formats

The quick read returns data at the address indicated by the address pointer. The address pointer, a register internal to the I<sup>2</sup>C communication engine, increments whenever data is acknowledged by the bq27531-G1 or the I<sup>2</sup>C master. "Quick writes" function in the same manner and are a convenient means of sending multiple bytes to consecutive command locations (such as two-byte commands that require two bytes of data).

The following command sequences are not supported:

Attempt to write a read-only address (NACK after data sent by master):




Figure 9. Attempt to Write a Read-Only Address

Attempt to read an address above 0x6B (NACK command):




Figure 10. Attempt to Read an Address Above 0x6B


### 8.5.2.2 PC Time-Out


The I<sup>2</sup>C engine releases both SDA and SCL if the I<sup>2</sup>C bus is held low for 2 seconds. If the bq27531-G1 is holding the lines, releasing them frees them for the master to drive the lines. If an external condition is holding either of the lines low, the I<sup>2</sup>C engine enters the low-power SLEEP mode.




## 8.5.2.3 PC Command Waiting Time

To ensure proper operation at 400 kHz, a  $t_{(BUF)} \ge 66$  µs bus-free waiting time must be inserted between all packets addressed to the bq27531-G1. In addition, if the SCL clock frequency ( $f_{SCL}$ ) is > 100 kHz, use individual 1-byte write commands for proper data flow control. The following diagram shows the standard waiting time required between issuing the control subcommand the reading the status result. For read-write standard command, a minimum of 2 seconds is required to get the result updated. For read-only standard commands, there is no waiting time required, but the host must not issue any standard command more than two times per second. Otherwise, the gauge could result in a reset issue due to the expiration of the watchdog timer.





Waiting time inserted between incremental 2-byte write packet for a subcommand and reading results (acceptable for  $f_{SCI} \le 100 \text{ kHz}$ )



Waiting time inserted after incremental read

Figure 11. I<sup>2</sup>C Command Waiting Time

#### 8.5.2.4 PC Clock Stretching

A clock stretch can occur during all modes of fuel gauge operation. In SLEEP and HIBERNATE modes, a short clock stretch occurs on all I<sup>2</sup>C traffic as the device must wake up to process the packet. In the other modes (BAT INSERT CHECK, NORMAL, SLEEP+) clock stretching only occurs for packets addressed for the fuel gauge. The majority of clock stretch periods are small as the I<sup>2</sup>C interface performs normal data flow control. However, less frequent yet more significant clock stretch periods may occur as blocks of Data Flash are updated. The following table summarizes the approximate clock stretch duration for various fuel gauge operating conditions.

Table 4. I<sup>2</sup>C Clock Stretching

| GAUGING<br>MODE    | OPERATING CONDITION/COMMENT   | APPROXIMATE DURATION |
|--------------------|---|----------------------|
| SLEEP<br>HIBERNATE | Clock stretch occurs at the beginning of all traffic as the device wakes up.                        | ≤ 4 ms               |
| BAT INSERT         | Clock stretch occurs within the packet for flow control (after a start bit, ACK or first data bit). | ≤ 4 ms               |
| CHECK<br>NORMAL    | Normal Ra table Data Flash updates.   | 24 ms                |
| SLEEP+             | Data Flash block writes.  | 72 ms                |
|                    | Restored Data Flash block write after loss of power.  | 116 ms               |
|                    | End of discharge Ra table Data Flash update.  | 144 ms               |



# 9 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## 9.1 Application Information

The fuel gauge can control a bq2419x Charger IC without the intervention from an application system processor. Using the bq27531-G1 and bq2419x chipset, batteries can be charged with the typical constant-current, constant-voltage (CCCV) profile or charged using a Multi-Level Charging (MLC) algorithm.

## 9.2 Typical Application




Figure 12. Typical Application Schematic



## **Typical Application (continued)**

## 9.2.1 Design Requirements

Several key parameters must be updated to align with a given application's battery characteristics. For highest accuracy gauging, it is important to follow-up this initial configuration with a learning cycle to optimize resistance and maximum chemical capacity (Qmax) values prior to sealing and shipping systems to the field. Successful and accurate configuration of the fuel gauge for a target application can be used as the basis for creating a "golden" gas gauge (.fs) file that can be written to all gauges, assuming identical pack design and Li-ion cell origin (chemistry, lot, and so on). Calibration data is included as part of this golden GG file to cut down on system production time. If going this route, TI recommends averaging the voltage and current measurement calibration data from a large sample size and use these in the golden file. Table 5 lists the items that must be configured to achieve reliable protection and accurate gauging with minimal initial configuration.

Table 5. Key Data Flash Parameters for Configuration

| NAME                  | DEFAULT | UNIT | RECOMMENDED SETTING  |
|-----------------------|---------|------|--|
| Design Capacity       | 2425    | mAh  | Set based on the nominal pack capacity as interpreted from cell manufacturer's datasheet. If multiple parallel cells are used, must be set to N × Cell Capacity.   |
| Reserve Capacity-mAh  | 0       | mAh  | Set to desired runtime remaining (in seconds/3600) × typical applied load between reporting 0% SOC and reaching <i>Terminate Voltage</i> , if needed.  |
| Cycle Count Threshold | 900     | mAh  | Set to 90% of configured <b>Design Capacity</b> .  |
| Chem ID               | 1202    | hex  | Must be configured using TI-supplied Battery Management Studio software. Default open-circuit voltage and resistance tables are also updated in conjunction with this step. Do not attempt to manually update reported Device Chemistry as this does not change all chemistry information. Always update chemistry using the appropriate evaluation software tool. |
| Load Mode             | 0       | _    | Set to applicable load model, 0 for constant current or 1 for constant power.  |
| Load Select           | 1       | _    | Set to load profile which most closely matches typical system load.  |
| Qmax Cell 0           | 2425    | mAh  | Set to initial configured value for Design Capacity. The gauge will update this parameter automatically after the optimization cycle and for every regular Qmax update thereafter.   |
| V at Chg Term Cell 0  | 4200    | mV   | Set to nominal cell voltage for a fully charged cell. The gauge will update this parameter automatically each time full charge termination is detected.  |
| Terminate Voltage     | 3200    | mV   | Set to empty point reference of battery based on system needs. Typical is between 3000 and 3200 mV.  |
| Ra Max Delta          | 44      | mΩ   | Set to 15% of Cell0 R_a 4 resistance after an optimization cycle is completed.   |
| Charging Voltage      | 4200    | mV   | Set based on nominal charge voltage for the battery in normal conditions (25°C, and so forth). Used as the reference point for offsetting by <i>Taper Voltage</i> for full charge termination detection.   |
| Taper Current         | 121     | mA   | Set to the nominal taper current of the charger + taper current tolerance to ensure that the gauge will reliably detect charge termination.  |
| Taper Voltage         | 100     | mV   | Sets the voltage window for qualifying full charge termination. Can be set tighter to avoid or wider to ensure possibility of reporting 100% SOC in outer JEITA temperature ranges that use derated charging voltage.  |
| Dsg Current Threshold | 60      | mA   | Sets threshold for gauge detecting battery discharge. Must be set lower than minimal system load expected in the application and higher than <b>Quit Current</b> .   |
| Chg Current Threshold | 75      | mA   | Sets the threshold for detecting battery charge. Can be set higher or lower depending on typical trickle charge current used. Also must be set higher than <i>Quit Current</i> .   |
| Quit Current          | 40      | mA   | Sets threshold for gauge detecting battery relaxation. Can be set higher or lower depending on typical standby current and exhibited in the end system.  |
| Avg I Last Run        | -299    | mA   | Current profile used in capacity simulations at onset of discharge or at all times if <b>Load Select</b> = 0. Must be set to nominal system load. Is automatically updated by the gauge every cycle.   |
| Avg P Last Run        | -1131   | mW   | Power profile used in capacity simulations at onset of discharge or at all times if <b>Load Select</b> = 0. Must be set to nominal system power. Is automatically updated by the gauge every cycle.  |
| Sleep Current         | 10      | mA   | Sets the threshold at which the fuel gauge enters SLEEP mode. Take care in setting above typical standby currents else entry to SLEEP may be unintentionally blocked.  |

Submit Documentation Feedback

Copyright © 2013–2016, Texas Instruments Incorporated



# **Typical Application (continued)**

# Table 5. Key Data Flash Parameters for Configuration (continued)

| NAME                         | DEFAULT | UNIT      | RECOMMENDED SETTING  |
|------------------------------|---------|-----------|--|
| Charge T0                    | 0       | °C        | Sets the boundary between charging inhibit and charging with T0 parameters.  |
| Charge T1                    | 10      | °C        | Sets the boundary between charging with T0 and T1 parameters.  |
| Charge T2                    | 45      | °C        | Sets the boundary between charging with T1 and T2 parameters.  |
| Charge T3                    | 50      | °C        | Sets the boundary between charging with T2 and T3 parameters.  |
| Charge T4                    | 60      | °C        | Sets the boundary between charging with T3 and T4 parameters.  |
| Charge Current T0            | 50      | % Des Cap | Sets the charge current parameter for T0.  |
| Charge Current T1            | 100     | % Des Cap | Sets the charge current parameter for T1.  |
| Charge Current T2            | 100     | % Des Cap | Sets the charge current parameter for T2.  |
| Charge Current T3            | 100     | % Des Cap | Sets the charge current parameter for T3.  |
| Charge Current T4            | 0       | % Des Cap | Sets the charge current parameter for T4.  |
| Charge Voltage T0            | 262     | 16 mV     | Sets the charge voltage parameter for T0.  |
| Charge Voltage T1            | 262     | 16 mV     | Sets the charge voltage parameter for T1.  |
| Charge Voltage T2            | 259     | 16 mV     | Sets the charge voltage parameter for T2.  |
| Charge Voltage T3            | 256     | 16 mV     | Sets the charge voltage parameter for T3.  |
| Charge Voltage T4            | 0       | 16 mV     | Sets the charge voltage parameter for T4.  |
| Chg Temp Hys                 | 5       | °C        | Adds temperature hysteresis for boundary crossings to avoid oscillation if temperature is changing by a degree or so on a given boundary.  |
| Chg Disabled<br>Regulation V | 4200    | mV        | Sets the voltage threshold for voltage regulation to system when charge is disabled. TI recommends programming to same value as Charging Voltage and maximum charge voltage that is obtained from Charge Voltage Tn parameters.                |
| CC Gain                      | 10      | mΩ        | Calibrate this parameter using TI-supplied evaluation software and calibration procedure in the TRM. Determines conversion of coulomb counter measured sense resistor voltage to current.  |
| CC Delta                     | 10      | mΩ        | Calibrate this parameter using TI-supplied evaluation software and calibration procedure in the TRM. Determines conversion of coulomb counter measured sense resistor voltage to passed charge.  |
| CC Offset                    | -1418   | Counts    | Calibrate this parameter using TI-supplied evaluation software and calibration procedure in the TRM. Determines native offset of coulomb counter hardware that must be removed from conversions.   |
| Board Offset                 | 0       | Counts    | Calibrate this parameter using TI-supplied evaluation software and calibration procedure in the TRM. Determines native offset of the printed-circuit-board parasitics that must be removed from conversions.                                   |
| Pack V Offset                | 0       | mV        | Calibrate this parameter using TI-supplied evaluation software and calibration procedure in the TRM. Determines voltage offset between cell tab and ADC input node to incorporate back into or remove from measurement, depending on polarity. |



#### 9.2.2 Detailed Design Procedure

#### 9.2.2.1 BAT Voltage Sense Input

A ceramic capacitor at the input to the BAT pin is used to bypass AC voltage ripple to ground, greatly reducing its influence on battery voltage measurements. It proves most effective in applications with load profiles that exhibit high-frequency current pulses (that is, cell phones) but is recommended for use in all applications to reduce noise on this sensitive high-impedance measurement node.

#### 9.2.2.2 SRP and SRN Current Sense Inputs

The filter network at the input to the coulomb counter is intended to improve differential mode rejection of voltage measured across the sense resistor. These components must be placed as close as possible to the coulomb counter inputs and the routing of the differential traces length-matched to best minimize impedance mismatch-induced measurement errors.

#### 9.2.2.3 Sense Resistor Selection

Any variation encountered in the resistance present between the SRP and SRN pins of the fuel gauge will affect the resulting differential voltage, and derived current, it senses. As such, TI recommends selecting a sense resistor with minimal tolerance and temperature coefficient of resistance (TCR) characteristics. The standard recommendation based on best compromise between performance and price is a 1% tolerance, 100-ppm drift sense resistor with a 1-W power rating.

#### 9.2.2.4 TS Temperature Sense Input

Similar to the BAT pin, a ceramic decoupling capacitor for the TS pin is used to bypass AC voltage ripple away from the high-impedance ADC input, minimizing measurement error. Another helpful advantage is that the capacitor provides additional ESD protection, because the TS input to system may be accessible in systems that use removable battery packs. The capacitor must be placed as close as possible to the respective input pin for optimal filtering performance.

#### 9.2.2.5 Thermistor Selection

The fuel gauge temperature sensing circuitry is designed to work with a negative temperature coefficient-type (NTC) thermistor with a characteristic  $10\text{-k}\Omega$  resistance at room temperature ( $25^{\circ}\text{C}$ ). The default curve-fitting coefficients configured in the fuel gauge specifically assume a 103AT-2 type thermistor profile and so that is the default recommendation for thermistor selection purposes. Moving to a separate thermistor resistance profile (for example, JT-2 or others) requires an update to the default thermistor coefficients in data flash to ensure highest accuracy temperature measurement performance.

### 9.2.2.6 REGIN Power Supply Input Filtering


A ceramic capacitor is placed at the input to the fuel gauge internal LDO to increase power supply rejection (PSR) and improve effective line regulation. It ensures that voltage ripple is rejected to ground instead of coupling into the internal supply rails of the fuel gauge.

# 9.2.2.7 V<sub>CC</sub> LDO Output Filtering

A ceramic capacitor is also needed at the output of the internal LDO to provide a current reservoir for fuel gauge load peaks during high peripheral utilization. It acts to stabilize the regulator output and reduce core voltage ripple inside of the fuel gauge.



## 9.2.3 Application Curves





# 10 Power Supply Recommendations

# 10.1 Power Supply Decoupling

Both the REGIN input pin and the VCC output pin require low equivalent series resistance (ESR) ceramic capacitors placed as close as possible to the respective pins to optimize ripple rejection and provide a stable and dependable power rail that is resilient to line transients. A 0.1- $\mu$ F capacitor at the REGIN and a 1- $\mu$ F capacitor at V<sub>CC</sub> will suffice for satisfactory device performance.

## 11 Layout

### 11.1 Layout Guidelines

#### 11.1.1 Sense Resistor Connections

Kelvin connections at the sense resistor are just as critical as those for the battery terminals themselves. The differential traces must be connected at the inside of the sense resistor pads and not anywhere along the high-current trace path to prevent false increases to measured current that could result when measuring between the sum of the sense resistor and trace resistance between the tap points. In addition, the routing of these leads from the sense resistor to the input filter network and finally into the SRP and SRN pins needs to be as closely matched in length as possible else additional measurement offset could occur. It is further recommended to add copper trace or pour-based "guard rings" around the perimeter of the filter network and coulomb counter inputs to shield these sensitive pins from radiated EMI into the sense nodes. This prevents differential voltage shifts that could be interpreted as real current change to the fuel gauge. All of the filter components need to be placed as close as possible to the coulomb counter input pins.

#### 11.1.2 Thermistor Connections

The thermistor sense input must include a ceramic bypass capacitor placed as close to the TS input pin as possible. The capacitor helps to filter measurements of any stray transients as the voltage bias circuit pulses periodically during temperature sensing windows.

#### 11.1.3 High-Current and Low-Current Path Separation

For best possible noise performance, it is extremely important to separate the low-current and high-current loops to different areas of the board layout. The fuel gauge and all support components must be situated on one side of the boards and tap off of the high-current loop (for measurement purposes) at the sense resistor. Routing the low-current ground around instead of under high-current traces will further help to improve noise rejection.



# 11.2 Layout Example




Figure 17. Layout Schematic



# 12 Device and Documentation Support

### 12.1 Documentation Support

#### 12.1.1 Related Documentation

To obtain a copy of any of the following TI documents, go to the TI website at www.ti.com.

- bg27531-G1 Technical Reference Manual User's Guide (SLUUA96)
- bq27531EVM with bq27531 Battery Management Unit Impedance Track™ Fuel Gauge and bq24192 4.5-A, Switch-Mode Battery Charger for Single-Cell Applications User's Guide (SLUUA90)

## 12.2 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 12.3 Trademarks

Impedance Track, MaxLife, NanoFree, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

## 12.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

#### 12.5 Glossary

SLYZ022 — TI Glossarv.

This glossary lists and explains terms, acronyms, and definitions.

# 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



# PACKAGE OPTION ADDENDUM

10-Dec-2020

#### PACKAGING INFORMATION

www.ti.com

| Orderable Device | Status | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan     | Lead finish/<br>Ball material | MSL Peak Temp      | Op Temp (°C) | Device Marking<br>(4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| BQ27531YZFR-G1   | ACTIVE | DSBGA        | YZF                | 15   | 3000           | RoHS & Green | SNAGCU                        | Level-1-260C-UNLIM | -40 to 85    | BQ27531                 | Samples |
| BQ27531YZFT-G1   | ACTIVE | DSBGA        | YZF                | 15   | 250            | RoHS & Green | SNAGCU                        | Level-1-260C-UNLIM | -40 to 85    | BQ27531                 | Samples |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





10-Dec-2020

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 15-Jan-2016

# TAPE AND REEL INFORMATION





|    | Dimension designed to accommodate the component width     |
|----|---|
| B0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

|   | Device         | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|---|----------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
|   | BQ27531YZFR-G1 | DSBGA           | YZF                | 15 | 3000 | 180.0                    | 8.4                      | 2.1        | 2.76       | 0.81       | 4.0        | 8.0       | Q1               |
| BQ27531YZFR-G1 DSBGA YZF 15 3000 180.0 8.4 2.1 2.76 0.81 4.0 8.0 Q1 | BQ27531YZFT-G1 | DSBGA           | YZF                | 15 | 250  | 180.0                    | 8.4                      | 2.1        | 2.76       | 0.81       | 4.0        | 8.0       | Q1               |

www.ti.com 15-Jan-2016




#### \*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| BQ27531YZFR-G1 | DSBGA        | YZF             | 15   | 3000 | 182.0       | 182.0      | 20.0        |
| BQ27531YZFT-G1 | DSBGA        | YZF             | 15   | 250  | 182.0       | 182.0      | 20.0        |



DIE SIZE BALL GRID ARRAY




### NOTES:

NanoFree Is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
  2. This drawing is subject to change without notice.
- 3. NanoFree<sup>™</sup> package configuration.



DIE SIZE BALL GRID ARRAY




NOTES: (continued)

4. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 (www.ti.com/lit/snva009).



DIE SIZE BALL GRID ARRAY



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated