






REVISIONS				
P.	LTN	DESCRIPTION	DATE	APV
E		REVISED PER ECO-14-005095	11APR2014	AP RP
F		REVISED PER ECO-16-008845	24SEP2016	AP RP



- △ REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- △ MATERIAL:  
SHIELD - PHOSPHOR BRONZE  
CONTACT - COPPER-NICKEL-SILICON  
HOUSING, CHICKLET AND CHICKLET COVER - GLASS FILLED POLYESTER, UL 94V-0 RATED.
- △ FINISH: SIGNAL AND GROUND CONTACTS:  
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS  
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN-LEAD OVER BASE PLATING
- △ CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.



TOP SURFACE OF DAUGHTER CARD



1469028-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: R.S. KLINE 12OCT2000	TE Connectivity
DIMENSIONS: mm		CHK: R. PATTERSON 10MAY2007	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APV: R. PATTERSON 10MAY2007	NAME: RECEPTACLE ASSEMBLY, 2 PAIR, 25mm, HMZd
0 PLC	±	PRODUCT SPEC	SIZE: CAGE CODE DRAWING NO
1 PLC	±	APPLICATION SPEC	RESTRICTED TO
2 PLC	±		
3 PLC	±		
4 PLC	±		
ANGLES	±		
MATERIAL		WEIGHT	A100779C=1469028
FINISH		CUSTOMER DRAWING	SCALE 8:1 SHEET 1 OF 1 REV F

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1469028-1](#)