TOSHIBA Transistor Silicon NPN Epitaxial Type (PCT process)

2SC2240


Low Noise Audio Amplifier Applications

The 2SC2240 is a transistor for low frequency and low noise applications. This device is designed to lower noise figure in the region of low signal source impedance, and to lower the pulse noise. This is recommended for the first stages of Equalizer amplifiers.

- Low noise: NF = 4dB (typ.) $R_G = 100 \Omega$, $V_{CE} = 6 V$, $I_C = 100 \mu A$,
 - f = 1 kHz
 - : NF = 0.5dB (typ.) RG = 1 kΩ, VCE = 6 V, IC = 100 $\mu A,$ f = 1 kHz
- Low pulse noise: Low 1/f noise
- High DC current gain: $h_{FE} = 200 \sim 700$
- High breakdown voltage: VCEO = 120 V

Maximum Ratings (Ta = 25°C)

Characteristics	Symbol	Rating	Unit
Collector-base voltage	V _{CBO}	120	V
Collector-emitter voltage	V _{CEO}	120	V
Emitter-base voltage	V _{EBO}	5	V
Collector current	Ι _C	100	mA
Base current	Ι _Β	20	mA
Collector power dissipation	P _C	300	mW
Junction temperature	Tj	125	°C
Storage temperature range	T _{stg}	-55~125	°C




Weight: 0.21 g (typ.)

Electrical Characteristics (Ta = 25°C)


Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Collector cut-off current	I _{CBO}	$V_{CB} = 120 \text{ V}, I_E = 0$			0.1	μA
Emitter cut-off current	I _{EBO}	$V_{EB} = 5 \text{ V}, \text{ I}_{C} = 0$			0.1	μA
Collector-emitter breakdown voltage	V (BR) CEO	$I_C = 1 \text{ mA}, I_B = 0$	120	_	_	V
DC current gain	h _{FE} (Note)	$V_{CE} = 6 V, I_{C} = 2 mA$	200	_	700	
Collector-emitter saturation voltage	V _{CE (sat)}	$I_{C} = 10 \text{ mA}, I_{B} = 1 \text{ mA}$			0.3	V
Base-emitter voltage	V _{BE}	$V_{CE} = 6 V, I_C = 2 mA$	_	0.65	_	V
Transition frequency	fT	$V_{CE} = 6 V, I_{C} = 1 mA$		100		MHz
Collector output capacitance	C _{ob}	$V_{CB} = 10 \text{ V}, \text{ I}_{E} = 0, \text{ f} = 1 \text{ MHz}$		3.0		pF
Noise figure		V_{CE} = 6 V, I _C = 0.1 mA, f = 10 Hz, R_{G} = 10 k Ω	_	_	6	dB
	NF	V_{CE} = 6 V, I _C = 0.1 mA, f = 1 kHz, R_{G} = 10 $k\Omega$	_	_	2	
		$\label{eq:Vce} \begin{array}{l} V_{CE} = 6 \ V, \ I_{C} = 0.1 \ mA, \ f = 1 \ kHz, \\ R_{G} = 100 \ \Omega \end{array}$	_	4	_	

Note: hFE classification GR: 200~400, BL: 350~700

TOSHIBA



TOSHIBA



RESTRICTIONS ON PRODUCT USE

Handbook" etc.,

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
 In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability"
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

This datasheet has been download from:

www.datasheetcatalog.com

Datasheets for electronics components.