



## CHB300-300S SERIES 300 WATT 2:1 INPUT DC-DC CONVERTERS



### FEATURES

- \* 300W Isolated Output
- \* Efficiency to 90%
- \* Fixed Switching Frequency
- \* Input Under Voltage Protection
- \* Over Temperature Protection
- \* Low No Load Power Consumption
- \* Over Voltage/Current Protection
- \* Remote On/Off
- \* Half-Brick Size Meet Industrial standard
- \* UL60950-1 2<sup>nd</sup> (Reinforced Insulation) Approval
- \* CB Test Certificate IEC60950-1
- \* Safety Meets IEC/EN/UL 62368-1



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% Eff.	CAPACITIVE LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD		
CHB300-300S05	180-425 VDC	5 VDC	0 mA	60 A	10 mA	1125 mA	89	10000uF
CHB300-300S12	180-425 VDC	12 VDC	0 mA	25 A	10 mA	1135 mA	88	10000uF
CHB300-300S24	180-425 VDC	24 VDC	0 mA	12.5 A	10 mA	1110 mA	90	6000uF
CHB300-300S28	180-425 VDC	28 VDC	0 mA	10.7 A	10 mA	1110 mA	90	6000uF
CHB300-300S48	180-425 VDC	48 VDC	0 mA	6.25 A	10 mA	1110 mA	90	3000uF

#### NOTE:

1. Nominal Input Voltage 300 VDC.
2. An External Input Capacitor 150uF for All Models are Recommended to Reduce Input Ripple Voltage.
3. Measure at Nominal Input Voltage.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cincon:](#)

[CHB300-300S12](#) [CHB300-300S48](#) [CHB300-300S05](#) [CHB300-300S24](#) [CHB300-300S28](#) [CHB300-300S24N](#)  
[CHB300-300S48N](#) [CHB300-300S05N](#) [CHB300-300S28N](#) [CHB300-300S12N](#)