

Specification Sheet

Part Number: 157-00380



Design gives quick and easy assembly by hand without the need for tools.

Mount can be used in a wide variety of applications where 5mm weld studs or 5mm ISO bolts.

Design provides low insertion force and high extraction force.

Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg

Article Number 157-00380

Type T50SSBS6OT-E

Color Black (BK)

Quantity Per bag

Product Description The Standoff Stud Mount tie applies easily to weld studs and secures bundles away from fixing holes. These are used primarily in the automotive industry, but can be used in a variety of applications.

| | |
|-------------------------------------|---------------------------------------------------------------------------|
| Short Description | Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg |
| Global Part Name | T50SSBS6OT-E-PA66HS-BK |
| Minimum Tensile Strength (Imperial) | 45.0 |
| Minimum Tensile Strength (Metric) | 200 |
| Length L (Imperial) | 6.3 |
| Length L (Metric) | 160.0 |
| Fixation Method | Weld Stud Fixing |
| Identification Plate Position | none |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Width W (Imperial) | 0.18 |
| Width W (Metric) | 4.6 |
| Bundle Diameter Min (Imperial) | 0.16 |
| Bundle Diameter Min (Metric) | 1.0 |
| Bundle Diameter Max (Imperial) | 1.38 |

| | |
|------------------------------|----------------------------------------|
| Bundle Diameter Max (Metric) | 35.0 |
| Stud Diameter (Metric) | 6.0 mm |
| Stud Diameter (Imperial) | 0.24 |
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut | PA66HS |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |
| Customs Number | 3926909988 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00380](#)