

B32522

General purpose (stacked/wound)

Ordering codes and packing units (lead spacing 15 mm)

V_R	V_{RMS} $f \leq 60$ Hz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./ MOQ	Untaped pcs./ MOQ
V DC	V AC	μF					
63	40	0.68	5.0 × 10.5 × 18.0	B32522C0684+***	4680	5200	4000
		1.0	5.0 × 10.5 × 18.0	B32522C0105+***	4680	5200	4000
		1.5	5.0 × 10.5 × 18.0	B32522C0155+***	4680	5200	4000
		2.2	5.0 × 10.5 × 18.0	B32522C0225+***	4680	5200	4000
		3.3	6.0 × 11.0 × 18.0	B32522C0335+***	3840	4400	4000
		4.7	7.0 × 12.5 × 18.0	B32522C0475+***	3320	3600	4000
		6.8	8.5 × 14.5 × 18.0	B32522C0685+***	2720	2800	2000
		10	9.0 × 17.5 × 18.0	B32522C0106+***	2560	2800	2000
100	63	0.33	5.0 × 10.5 × 18.0	B32522C1334+***	4680	5200	4000
		0.47	5.0 × 10.5 × 18.0	B32522C1474+***	4680	5200	4000
		0.68	5.0 × 10.5 × 18.0	B32522C1684+***	4680	5200	4000
		1.0	5.0 × 10.5 × 18.0	B32522C1105+***	4680	5200	4000
		1.0 ▽	6.0 × 11.0 × 18.0	B32522Q1105+***	3840	4400	4000
		1.5	6.0 × 11.0 × 18.0	B32522C1155+***	3840	4400	4000
		1.5 ▽	7.0 × 12.5 × 18.0	B32522Q1155+***	3320	3600	4000
		2.2	7.0 × 12.5 × 18.0	B32522C1225+***	3320	3600	4000
		2.2 ▽	8.5 × 14.5 × 18.0	B32522Q1225+***	2720	2800	2000
		3.3	8.5 × 14.5 × 18.0	B32522C1335+***	2720	2800	2000
		3.3 ▽	9.0 × 17.5 × 18.0	B32522Q1335+***	2560	2800	2000
		4.7	9.0 × 17.5 × 18.0	B32522C1475+***	2560	2800	2000
		4.7 ▽	11.0 × 18.5 × 18.0	B32522Q1475+***	–	2200	1200

▽ Wound capacitor technology

MOQ = Minimum Order Quantity, consisting of 4 packing units.
Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%


J = ±5%

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 6 – 1 mm)


Ordering codes and packing units (lead spacing 15 mm)

V_R	V_{RMS} $f \leq 60$ Hz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./ MOQ	Untaped pcs./ MOQ
V DC	V AC	μF					
250	160	0.10	5.0 × 10.5 × 18.0	B32522C3104+***	4680	5200	4000
		0.15	5.0 × 10.5 × 18.0	B32522C3154+***	4680	5200	4000
		0.22	5.0 × 10.5 × 18.0	B32522C3224+***	4680	5200	4000
		0.33	5.0 × 10.5 × 18.0	B32522C3334+***	4680	5200	4000
		0.47	6.0 × 11.0 × 18.0	B32522C3474+***	3840	4400	4000
		0.68	7.0 × 12.5 × 18.0	B32522C3684+***	3320	3600	4000
		1.0	8.5 × 14.5 × 18.0	B32522C3105+***	2720	2800	2000
		1.0 ▽	8.5 × 14.5 × 18.0	B32522N3105+***	2720	2800	2000
		1.5	9.0 × 17.5 × 18.0	B32522C3155+***	2560	2800	2000
		1.5 ▽	9.0 × 17.5 × 18.0	B32522N3155+***	2560	2800	2000
400	200	0.047	5.0 × 10.5 × 18.0	B32522E6473+***	4680	5200	4000
		0.068	5.0 × 10.5 × 18.0	B32522E6683+***	4680	5200	4000
		0.10	5.0 × 10.5 × 18.0	B32522E6104+***	4680	5200	4000
		0.15	5.0 × 10.5 × 18.0	B32522E6154+***	4680	5200	4000
		0.22	6.0 × 11.0 × 18.0	B32522E6224+***	3840	4400	4000
		0.33	7.0 × 12.5 × 18.0	B32522E6334+***	3320	3600	4000
		0.47	9.0 × 17.5 × 18.0	B32522E6474+***	2560	2800	2000
		0.68	9.0 × 17.5 × 18.0	B32522E6684+***	2560	2800	2000
450	200	0.10 ▽	5.0 × 10.5 × 18.0	B32522N6104+***	4680	5200	4000
		0.15 ▽	5.0 × 10.5 × 18.0	B32522N6154+***	4680	5200	4000
		0.22 ▽	6.0 × 11.0 × 18.0	B32522N6224+***	3840	4400	4000
		0.33 ▽	7.0 × 12.5 × 18.0	B32522N6334+***	3320	3600	4000
		0.47 ▽	8.5 × 14.5 × 18.0	B32522N6474+***	2720	2800	2000
		0.68 ▽	9.0 × 17.5 × 18.0	B32522N6684+***	2560	2800	2000
		1.0	11.0 × 18.5 × 18.0	B32522N6105+***	—	2200	1200

▽ Wound capacitor technology

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

J = ±5%

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 6 – 1 mm)