



**1-CONDUCTOR PCB TERMINAL
STRIP 1 SOLDER PIN/POLE IN LINE
PIN SPACING 5 MM / 0.197 IN WITH
PUSH BUTTONS
250-502 TO 250-516**

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 250-503 |
| Cross section1 (Cross section / mm²) | 0.5 - 1.5 |
| Cross section2 (Cross section / AWG) | 20 - 14 |
| Strip length (Strip length / mm) | 9 - 10 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 17.5 |
| RM (PIN SPACING / mm) | 5 |
| P (NO. OF POLES) | 3 |
| Height (Height / mm) | 16.5 |
| Width (Width / mm) | 16.5 |
| Depth (Depth / mm) | 13 |
| No. of connection Points (No. of connection Points) | 3 |
| No. of potentials (No. of potentials) | 3 |
| COLOR (COLOR) | grau |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 1.5 mm |
| Dimensions (Dimensions) | 1.2 -0.1 mm |