

695 LED Signal Tower CleanSIGN

- LED signal tower for use in the food and cosmetic industry as well as in cleanroom applications
- Hygienic and cleaning-friendly design
- Compliant with EHEDG directives
- Resistant to cleaning agents
- Flexible colour distribution thanks to electronic modularity
- Integrated, high-output buzzer (85 dB)
- LED permanent light with additional light effects depending on variant
- User-friendly mounting




TECHNICAL SPECIFICATIONS:

Dimensions (WxHxD)	112 mm x 485 mm x 125 mm
Housing:	PA, black
Lens:	PA, transparent
Fixture:	Wall mounting, integrated mounting bracket
Connection:	RGY and RGB LED versions: Screwable connection, max. 1.5 mm ² SMD technology version: Cable, 2m long, included with product
Operating voltage:	24 V =
Current consumption:	Optical: Max. 500 mA per tier (depending on colour/variant) Buzzer: 20 mA



VARIANTS AND ORDER SPECIFICATIONS:




CleanSIGN - SMD technology

- ▶ LED signal tower with permanent lights in red, yellow and green (SMD technology)
- ▶ Preset, three-tier colour distribution
- ▶ Integrated, high output buzzer (85 dB)



Order No.
695 300 55



Fixed colour distribution with SMD technology




CleanSIGN - RGY LEDs

- ▶ LED signal tower with permanent lights in red, yellow and green (RGY LEDs)
- ▶ Complete illumination in one colour possible (can be triggered externally)
- ▶ Colour distribution can be selected and adjusted via DIP switch as required
- ▶ Integrated, high output buzzer (85 dB)



Order No.
695 200 55



RGY LEDs give completely flexible colour distribution



CleanSIGN - RGB LEDs

- ▶ LED signal tower with permanent light and additional light effects
- ▶ 7 colours: red, yellow, green, clear, blue, violet, turquoise (RGB LEDs)
- ▶ Complete illumination in one colour possible (can be triggered externally)
- ▶ Colour distribution can be selected and adjusted via DIP switch as required
- ▶ Integrated, high output buzzer (85 dB)



Order No.
695 000 55



7 colour settings from RGB LEDs



www.werma.co.uk Made in Germany



WERMA
SIGNALTECHNIK

WERMA (UK) Ltd. Linnell Way, Telford Way Industrial Estate, Kettering NN16 8PS
Tel: 01536 486930, Fax: 01536 514810, email: uksales@werma.co.uk