



# DIN RAIL Series

## 40/60/100 Watt Single Output



### Features

- \* Universal Input Range 90~264VAC
- \* Efficiency up to 90%
- \* Meets EN55022 and CISPR/FCC Class B
- \* Continuous Short Circuit Protection
- \* LED Indicator for Power ON
- \* Can be Installed on DIN rail TS-35/7.5 or 15



### CFM40CXXX-DR Series

MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	RIPPLE & NOISE	VOLTAGE ACCURACY	LINE REGULATION	LOAD REGULATION	%EFF. (Typ.)
CFM40C033-DR	3.3 V	6 A	50mV	±1%	±0.5%	±1%	70%
CFM40C050-DR	5 V	6 A	1%	±1%	±0.5%	±1%	76%
CFM40C090-DR	9 V	4.45 A	1%	±1%	±0.5%	±1%	84%
CFM40C120-DR	12 V	3.34 A	1%	±1%	±0.5%	±1%	85%
CFM40C150-DR	15 V	2.67 A	1%	±1%	±0.5%	±1%	85%
CFM40C240-DR	24 V	1.67 A	1%	±1%	±0.5%	±1%	85%
CFM40C300-DR	30 V	1.33 A	1%	±1%	±0.5%	±1%	86%
CFM40C360-DR	36 V	1.11 A	1%	±1%	±0.5%	±1%	87%
CFM40C480-DR	48 V	0.834 A	1%	±1%	±0.5%	±1%	87%

### CFM60CXXX-DR Series

MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	RIPPLE & NOISE	VOLTAGE ACCURACY	LINE REGULATION	LOAD REGULATION	%EFF. (Typ.)
CFM60C033-DR	3.3 V	8 A	50mV	±1%	±0.5%	±1%	72%
CFM60C050-DR	5 V	8 A	1%	±1%	±0.5%	±1%	77%
CFM60C090-DR	9 V	6.67 A	1%	±1%	±0.5%	±1%	84%
CFM60C120-DR	12 V	5 A	1%	±1%	±0.5%	±1%	85%
CFM60C150-DR	15 V	4 A	1%	±1%	±0.5%	±1%	86%
CFM60C240-DR	24 V	2.5 A	1%	±1%	±0.5%	±1%	86%
CFM60C300-DR	30 V	2 A	1%	±1%	±0.5%	±1%	86%
CFM60C360-DR	36 V	1.67 A	1%	±1%	±0.5%	±1%	88%
CFM60C480-DR	48 V	1.25 A	1%	±1%	±0.5%	±1%	88%

### CFM101CXXX-DR Series

MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	RIPPLE & NOISE	VOLTAGE ACCURACY	LINE REGULATION	LOAD REGULATION	%EFF. (Typ.)	PF (Typ.)
CFM101C120-DR	12 V	8.4 A	1%	±1%	±0.5%	±1%	87%	0.9
CFM101C150-DR	15 V	6.7 A	1%	±1%	±0.5%	±1%	87%	0.9
CFM101C200-DR	20 V	5 A	1%	±1%	±0.5%	±1%	88%	0.9
CFM101C240-DR	24 V	4.2 A	1%	±1%	±0.5%	±1%	88%	0.9
CFM101C480-DR	48 V	2.1 A	1%	±1%	±0.5%	±1%	90%	0.9



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cincon:](#)

[CFM60C150-DR](#) [CFM60C360-DR](#) [CFM60C033-DR](#) [CFM101C150-DR](#) [CFM60C090-DR](#) [CFM60C050-DR](#)  
[CFM60C120-DR](#) [CFM60C480-DR](#) [CFM101C200-DR](#) [CFM60C240-DR](#) [CFM60C300-DR](#) [CFM101C120-DR](#)