

Coaxial Cable Connector 21_SMA-50-3-5/111_N

Description

Straight cable jack

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0029 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00006289
Catalogue drawing	DOU-00005889
Assembly instruction	DOC-0000179078

Ordering Information

Single package	21_SMA-50-3-5/111_NE
----------------	----------------------

Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272
-----------------	------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[21_SMA-50-3-5/111_NE](#)