MINIATURE CERAMIC SMD CRYSTAL



5.0 X 3.2 X 1.3mm

Smaller package alternative for ABM7 series

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

Pb in Glass, exemption 7C-I per RoHS II Directive | RoHS/RoHS II Compliant.

2011/65/EU Annex

FEATURES:

- AT-cut fundamental or 3rd OT mode
- Suitable for RoHS reflow profile

ABM3

- Tight Stability available ±10
- Ceramic package hermetically glass sealed assures high precision and reliability.

STANDARD SPECIFICATIONS:

> APPLICATIONS:

- Cellular telephones, pagers
- Communication and test equipment
- PCMCIA and wireless applications

Parameters	Minimum	Typical	Maximum	Units	Notes	
Ere more av Dan se	8.000		54.000	MII-	Fundamental	
Frequency Range	54.100		80.000	MHz	3 rd Overtone	
Operation Mode	Fundamental or 3 rd Overtone					
Operating Temperature	-10 +60		°C	See options		
Storage Temperature	-40		+90	°C		
Frequency Tolerance @+25°C	-50		+50	ppm	m See options	
Frequency Stability over the Operating Temperature (ref. to +25°C)	-50		+50	ppm	See options	
Equivalent series resistance (R1)			140		$8.000 \le F < 9.000$ (Fund)	
			120	1	$9.000 \le F < 10.000$ (Fund)	
			60	1	$10.000 \le F < 16.000$ (Fund)	
			40	Ω	$16.000 \le F < 20.000$ (Fund)	
			30	1	$20.000 \le F < 30.000$ (Fund)	
			25	1	$30.000 \le F \le 54.000$ (Fund)	
			60	1	$54.000 < F \le 80.000 (3^{rd} OT)$	
Shunt capacitance (C0)			7	pF		
Load capacitance (CL)	18			pF	Standard (See options if other than STD)	
Drive Level		10	100	μW		
Aging	-5		+5	ppm	@25°C±3°C First year	
Insulation Resistance	500			MΩ	(<i>a</i>) 100 Vdc ± 15 V	



CERTIFIED




Table 1 Available Combinations of Operating Temp. and Freq. Stability

K: -40°C ~ +125°C

Operating Temp.	Freq. Stability										
	U:±10ppm	G:±15ppm	X:±20ppm	W:±25ppm	Y:±30ppm	H:±35ppm	Std:±50ppm	Q:±100ppm			
Std: -10°C ~ +60°C	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark			
E: 0°C ~ +70°C		\checkmark	\checkmark	\checkmark	\checkmark		\checkmark	\checkmark			
B: -20°C ~ +70°C	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark			
C: -30°C ~ +70°C		\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark				
N: -30°C ~ +85°C		\checkmark	\checkmark	\checkmark	\checkmark		\checkmark				
D: -40°C ~ +85°C			\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark			
J: -40°C ~ +105°C							\checkmark	\checkmark			
K: -40°C ~ +125°C							\checkmark				



1501 Hidden Creek Lane Spicewood TX 78751 Phone: 949-546-8000 | Fax: 949-546-8001 For terms and conditions of sales visit: www.abracon.com

ISO9001-2015

CERTIFIED


MINIATURE CERAMIC SMD CRYSTAL



5.0 X 3.2 X 1.3mm

ABM3

OUTLINE DRAWING:




Pb in Glass, exemption 7C-I per RoHS II Directive | RoHS/RoHS II Compliant.

2011/65/EU Annex

<mark>⊳ TAPE & REEL:</mark>

REFLOW PROFILE





Need a test socket for the ABM3 Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, **click here. P/N: AXS-5032-02-06**

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



1501 Hidden Creek Lane Spicewood TX 78751 Phone: 949-546-8000 | Fax: 949-546-8001 For terms and conditions of sales visit: www.abracon.com REVISED: 07/19/2018 ABRACON IS ISO9001-2015 CERTIFIED