

# KERN EHA 1000-1



The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries and for teaching



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	2x1.5 V AA
Input voltage:	100 V - 240 V
Mains adapter/adaptor included:	CH EURO UK
Operating time:	400 h

## Service

Adjustment at the location of installation:	961-247
DAkkS Certificate:	963-127

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	245 x 204 x 76 mm
Gross weight:	750 g
Net weight:	500 g
Shipping method:	Parcel service

## Construction

Dimensions housing (WxDxH):	225 x 160 x 50 mm
Dimensions of weighing plate (WxDxH):	120 x 120 x 7 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	120 x 120 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Minimum weight (USP):	600 g
Number of weighing ranges:	1
Readability [d]:	100 mg
Recommended adjusting weight:	1 kg (M1)
Repeatability:	300 mg
Resolution:	10000
Stabilisation time under laboratory conditions:	3 s
Tare range:	1 kg
Warm up time:	30 min
Weighing capacity [Max]:	1 kg
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn oz

## Display

Display digit height:	2,200 cm
-----------------------	----------

## Counting

Counting resolution:	10000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g

## Functions

Counting function:	yes
--------------------	-----