

Straight Blade Devices 20/16A, 250V AC, 2 Pole, 3 Wire Grounding Connector

HUBBELL

Features

- Compatible with IEC320
- Hinged one piece body design for easy assembly
- Two captive multiple drive assembly screws

Ordering Information

Description	Device Color	UPC	Catalog Number
IEC Detachable straight blade connector	Black	783585777108	H320C

Listings

UL Listed 20A 250V AC-File No. E1706
 CSA certified 20A 250V AC-File No. 17337
 UL classified to IEC 320, 16A 250V AC-File No. E111246



Specifications


Device Type	2 Pole + earth
Configuration	IEC 60320-1 Style appliance coupler, C19
Terminal Retainer	Nylon
Power Contacts	.032" (.81) Brass
Terminal Screws	Stainless steel
Terminal Clamp	Nickel plated steel
Assembly Screws	Zinc plated steel

Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum
Rating	16A 250V AC for European service; 20A 250V AC for North American service

Mechanical	
Cord Accommodation	.325" - .475" (8.0-12.0)
Terminal Accommodation	North American – #16-12 AWG stranded or solid copper conductor only. International – 1.55mm ² -2.5mm ²
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental	
Flammability	UL 94 HB or better
IP Suitability	IP20
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

