

### **LILIAN-ON**

~10° + 80° beam for wall grazing

### **TECHNICAL SPECIFICATIONS:**

286.4 x 27.0 mm **Dimensions** 14.8 mm Height **ROHS** compliant yes 🕕



#### **MATERIAL SPECIFICATIONS:**

Component Type Material Colour **Finish** LILIAN-ON Linear lens **PMMA** clear

#### **ORDERING INFORMATION:**

» Box size: 400 x 300 x 160 mm


Component Qty in box MOQ MPQ Box weight (kg)

84 C16507\_LILIAN-ON 84 14 4.3

Published: 14/01/2019 Last update: 02/09/2019 Subject to change without prior notice 1/8




## PRODUCT DATASHEET C16507\_LILIAN-ON



2/8



# **PRODUCT** C16507\_LILIAN-ON




See also our general installation guide: <a href="www.ledil.com/installation\_guide">www.ledil.com/installation\_guide</a>

3/8



### PHOTOMETRIC DATA (MEASURED):





### PHOTOMETRIC DATA (SIMULATED):


## CREE 💠

LED XD16

FWHM / FWTM 64.0 + 12.0° / 117.0 + 46.0°

Efficiency 87 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White

Required components:




## CREE \$

LED XM-L

FWHM / FWTM 76.0 + 18.0° / 118.0 + 54.0°

Efficiency 86 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour RGBW

Required components:




## CREE \$

LED XP-E

FWHM / FWTM 57.0 + 11.0° / 106.0 + 34.0°

Efficiency 88 %
Peak intensity 2.1 cd/lm
LEDs/each optic 1
Light colour White

Required components:




## CREE 💠

.ED XP-G

FWHM / FWTM 66.0 + 11.0° / 112.0 + 36.0°

Efficiency 87 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White

Required components:



Published: 14/01/2019



## PHOTOMETRIC DATA (SIMULATED):


## CREE 💠

LED XP-G2

FWHM / FWTM 70.0 + 12.0° / 115.0 + 40.0°

Efficiency 88 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White

Required components:




### **MUMILEDS**

LED LUXEON 2835 Line FWHM / FWTM 72.0 + 12.0° / 118.0 + 32.0°

Efficiency 90 %
Peak intensity 2 cd/lm
LEDs/each optic 1
Light colour RGBW


Required components:



## **DESCRIPTION** LUMILEDS

LED LUXEON 3030 2D (Square LES) FWHM / FWTM 72.0 + 18.0° / 118.0 + 58.0°

Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:




## **DESCRIPTION** LUMILEDS

LED LUXEON 5050 Round LES FWHM / FWTM 70.0 + 18.0 ° / 118.0 + 58.0 °

Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White

Required components:





### PHOTOMETRIC DATA (SIMULATED):


### **LUMILEDS**

LED LUXEON CZ

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 72.0 + 9.0° / 118.0 + 31.0°

Efficiency 91 % Peak intensity 2.4 cd/lm LEDs/each optic Light colour **RGBW** 

Required components:




### **WNICHIA**

LED NF2x757G

FWHM / FWTM 76.0 + 16.0° / 118.0 + 32.0°

Efficiency 87 % Peak intensity 1.7 cd/lm LEDs/each optic 1 White Light colour

Required components:




## OSRAM Opto Semiconductors

LED Duris S5 (Single chip) FWHM / FWTM 66.0 + 12.0° / 114.0 + 47.0°

Efficiency 87 % Peak intensity 1.4 cd/lm LEDs/each optic 1 Light colour White

Required components:




## **SAMSUNG**

LM28xB Series

FWHM / FWTM 74.0 + 14.0° / 116.0 + 32.0°

Efficiency 88 % Peak intensity 1.9 cd/lm LEDs/each optic 1 White Light colour

Required components:



Published: 14/01/2019



## **PRODUCT** DATASHEET C16507\_LILIAN-ON

#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

#### **Ledil Optics Technology** (Shenzhen) Co., Ltd.

# 405, Block B **Casic Motor Building** Shenzhen 518057 P.R.CHINA

#### Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

www.ledil.com/ where\_to\_buy

Published: 14/01/2019

8/8