



**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Protection**

Revision date: 09.12.2019

Product code: 115

Page 2 of 8

**Pictograms:**

**Hazard statements**

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

**Precautionary statements**

P332+P313	If skin irritation occurs: Get medical advice/attention.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P211	Do not spray on an open flame or other ignition source.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

**SECTION 3: Composition/information on ingredients**
**3.2. Mixtures**
**Hazardous components**

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	GHS Classification			
	Hydrocarbons, C6, isoalkanes, <5% n-hexane			30-60%
	931-254-9		01-2119484651-34	
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411			
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol			25-50%
	200-661-7	603-117-00-0		
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336			
124-38-9	Carbondioxide			2,5-10%
	204-696-9			
	Compressed gas; H280			

Full text of H and EUH statements: see section 16.

**SECTION 4: First aid measures**
**4.1. Description of first aid measures**
**After inhalation**

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

**After contact with skin**

After contact with skin, wash immediately with: Water. Change contaminated clothing.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Protection**

Revision date: 09.12.2019

Product code: 115

Page 3 of 8

**After contact with eyes**

If product gets into the eye, keep eyelid open and rinse immediately with large quantities of water, for at least 5 minutes. Subsequently consult an ophthalmologist.

**After ingestion**

If swallowed, immediately drink: Water.

**4.2. Most important symptoms and effects, both acute and delayed**

No data available

**4.3. Indication of any immediate medical attention and special treatment needed**

No data available

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media**

Carbon dioxide (CO<sub>2</sub>). Foam. Extinguishing powder.

**Unsuitable extinguishing media**

Water with tenside additive. Water.

**5.2. Special hazards arising from the substance or mixture**

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

**5.3. Advice for firefighters**

Wear a self-contained breathing apparatus and chemical protective clothing.

**Additional information**

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

**6.2. Environmental precautions**

Do not allow to enter into surface water or drains. Explosion hazard.

**6.3. Methods and material for containment and cleaning up**

Ventilate affected area.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

**Advice on protection against fire and explosion**

Keep away from sources of ignition - No smoking.

**7.2. Conditions for safe storage, including any incompatibilities****Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

**Hints on joint storage**

Do not store together with: Material, rich in oxygen, oxidizing.

## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Protection

Revision date: 09.12.2019

Product code: 115

Page 4 of 8

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits (EH40)

CAS No	Substance	ppm	mg/m <sup>3</sup>	fibres/ml	Category	Origin
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

### 8.2. Exposure controls



#### Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

#### Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

#### Eye/face protection

Tightly sealed safety glasses.

#### Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

#### Skin protection

Protective clothing:

#### Respiratory protection

In case of inadequate ventilation wear respiratory protection.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	light yellow
Odour:	characteristic

#### Test method

#### Changes in the physical state

Initial boiling point and boiling range:	60 °C
Pour point:	ISO 3016
Flash point:	< -20 °C ASTM D 3828
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	7 vol. %
Ignition temperature:	300 °C

## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Protection

Revision date: 09.12.2019

Product code: 115

Page 5 of 8

Vapour pressure: (at 20 °C)	227 hPa
Vapour pressure: (at 50 °C)	719 hPa
Density (at 20 °C):	0,72 g/cm <sup>3</sup>

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

No data available

#### 10.2. Chemical stability

No data available

#### 10.3. Possibility of hazardous reactions

No data available

#### 10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

#### 10.5. Incompatible materials

No data available

#### 10.6. Hazardous decomposition products

No data available

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

##### Acute toxicity

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane				
	oral	LD50 >1000 mg/kg	Fisch 1		

##### Irritation and corrosivity

Irritating to eyes. Vapours may cause drowsiness and dizziness. After skin contact: irritant.

### SECTION 12: Ecological information

#### 12.1. Toxicity

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h]   [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	Acute algae toxicity	ErC50 >1000 mg/l	72 h	Alge		
	Acute crustacea toxicity	EC50 >1000 mg/l	48 h	Daphnia pulex (water flea)		

##### Further information

Do not allow to enter into surface water or drains.

### SECTION 13: Disposal considerations

## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Protection

Revision date: 09.12.2019

Product code: 115

Page 6 of 8

#### 13.1. Waste treatment methods

##### Advice on disposal

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

##### Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

##### Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

##### Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

### SECTION 14: Transport information

#### Land transport (ADR/RID)

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2  
Hazard label: 2.1



Classification code: 5F  
Special Provisions: 190 327 625  
Limited quantity: 1 L  
Transport category: 2  
Tunnel restriction code: D

#### Other applicable information (land transport)

E0

#### Inland waterways transport (ADN)

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2  
Hazard label: 2.1



Classification code: 5F  
Special Provisions: 190 327 344 625  
Limited quantity: 1 L

#### Other applicable information (inland waterways transport)

E0

#### Marine transport (IMDG)

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Protection**

Revision date: 09.12.2019

Product code: 115

Page 7 of 8

**14.4. Packing group:** -  
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959  
Limited quantity: See SP277  
EmS: F-D, S-U

**Other applicable information (marine transport)**  
E0

**Air transport (ICAO-TI/IATA-DGR)**

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS, flammable  
**14.3. Transport hazard class(es):** 2.1  
Hazard label: 2.1



Special Provisions: A145 A167  
Limited quantity Passenger: 30 kg G  
IATA-packing instructions - Passenger: 203  
IATA-max. quantity - Passenger: 75 kg  
IATA-packing instructions - Cargo: 203  
IATA-max. quantity - Cargo: 150 kg

**Other applicable information (air transport)**  
E0  
: Y203

**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: yes

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane

2004/42/EC (VOC): 45,45 % (327,24 g/l)

**National regulatory information**

Water contaminating class (D): 2 - clearly water contaminating

**SECTION 16: Other information****Relevant H and EUH statements (number and full text)**

H222 Extremely flammable aerosol.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Protection**

Revision date: 09.12.2019

Product code: 115

Page 8 of 8

H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

*(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)*