



preci-dip

# SPRING-LOADED CONNECTORS & PAD CONNECTORS


**SERIES**  
**813**

**813-SS-NNN-30-XXX101**

Double Row

2.54 mm, Surface mount perpendicular with positioning pins

Basic modular connectors with spring-loaded contacts (SLC), surface mount with positioning pins. Contacts with hollow piston design for low profile.



## TECHNICAL SPECS.:

<b>Flammability</b>	UL 94V-O
<b>Piston and barrel</b>	Brass CuZn36Pb3 (C36000)
<b>Spring</b>	Stainless steel X12 CrNi177, DIN 17224
<b>Max. stroke</b>	1.4 mm (1.15 mm for 813-...-021101)
<b>Forces initial</b>	0.25 N
<b>Forces initial at 1/2 stroke</b>	0.6 N
<b>Mechanical life</b>	100'000 cycles
<b>Max. operating current</b>	3.5 A
<b>Contact resistance</b>	15 m (static measurement, halfway position)
<b>Coplanarity SMD terminations</b>	Max. 0.1 mm (measured on 25 mm long connectors)
<b>Plating</b>	Gold 0.5 µm barrel and piston

## ORDERING INFORMATION:

Initial height A (mm)	Height plastic body B (mm)	XXX code
4.5	2.95	021
5	2.95	022
5.5	2.95	023
6	4	024
6.5	4	025
7	4	026
7.5	4	027

NNN number of poles. Replace NNN with the requested number of poles, e.g. 813-SS-NNN-30-021101, for a double row version with 16 pins becomes 813-SS-016-30-021101.

# TECHNICAL ASSISTANCE

## GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP spring-loaded connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/85/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP products are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442.

## ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

## ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
  - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
  - 2) Sulfur dioxide (SO<sub>2</sub>) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO<sub>2</sub>, 25 °C, 75 %rH
  - 3) Hydrogen sulfide (H<sub>2</sub>S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H<sub>2</sub>S, 25 °C, 75 %rH

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Preci-dip:

[813-SS-006-30-002101](#) [813-SS-008-30-007101](#) [813-SS-008-30-006101](#) [813-SS-010-30-002101](#) [813-SS-020-30-027101](#) [813-SS-018-30-025101](#) [813-SS-016-30-002101](#) [813-SS-014-30-002101](#) [813-SS-012-30-002101](#) [813-SS-008-30-002101](#) [813-SS-010-30-003101](#) [813-SS-014-30-004101](#) [813-SS-018-30-001101](#) [813-SS-008-30-003101](#) [813-SS-020-30-001101](#) [813-SS-004-30-003101](#) [813-SS-020-30-002101](#) [813-SS-018-30-002101](#) [813-SS-004-30-004101](#) [813-SS-020-30-003101](#) [813-SS-018-30-003101](#) [813-SS-016-30-003101](#) [813-SS-014-30-003101](#) [813-SS-012-30-003101](#) [813-SS-004-30-002101](#) [813-SS-006-30-003101](#) [813-SS-012-30-024101](#) [813-SS-010-30-004101](#) [813-SS-008-30-004101](#) [813-SS-006-30-004101](#) [813-SS-012-30-001101](#) [813-SS-010-30-001101](#) [813-SS-008-30-001101](#) [813-SS-006-30-001101](#) [813-SS-004-30-001101](#) [813-SS-006-30-022101](#) [813-SS-004-30-022101](#) [813-SS-008-30-023101](#) [813-SS-012-30-004101](#) [813-SS-016-30-004101](#) [813-SS-016-30-001101](#) [813-SS-018-30-022101](#) [813-SS-016-30-022101](#) [813-SS-014-30-022101](#) [813-SS-012-30-022101](#) [813-SS-010-30-022101](#) [813-SS-008-30-022101](#) [813-SS-012-30-023101](#) [813-SS-010-30-023101](#) [813-SS-016-30-021101](#) [813-SS-006-30-023101](#) [813-SS-018-30-021101](#) [813-SS-020-30-022101](#) [813-SS-006-30-024101](#) [813-SS-004-30-024101](#) [813-SS-020-30-023101](#) [813-SS-018-30-023101](#) [813-SS-016-30-023101](#) [813-SS-014-30-023101](#) [813-SS-008-30-021101](#) [813-SS-006-30-021101](#) [813-SS-004-30-021101](#) [813-SS-020-30-021101](#) [813-SS-004-30-023101](#) [813-SS-008-30-024101](#) [813-SS-018-30-007101](#) [813-SS-016-30-007101](#) [813-SS-014-30-007101](#) [813-SS-014-30-021101](#) [813-SS-012-30-021101](#) [813-SS-010-30-021101](#) [813-SS-004-30-005101](#) [813-SS-020-30-004101](#) [813-SS-018-30-004101](#) [813-SS-006-30-006101](#) [813-SS-010-30-007101](#) [813-SS-020-30-007101](#) [813-SS-016-30-005101](#) [813-SS-014-30-005101](#) [813-SS-012-30-005101](#) [813-SS-010-30-005101](#) [813-SS-008-30-005101](#) [813-SS-006-30-005101](#) [813-SS-014-30-006101](#) [813-SS-012-30-006101](#) [813-SS-010-30-006101](#) [813-SS-004-30-006101](#) [813-SS-012-30-007101](#) [813-SS-018-30-005101](#) [813-SS-020-30-005101](#) [813-SS-006-30-007101](#) [813-SS-004-30-007101](#) [813-SS-020-30-006101](#) [813-SS-018-30-006101](#) [813-SS-016-30-006101](#) [813-SS-018-30-027101](#) [813-SS-016-30-027101](#) [813-SS-014-30-027101](#) [813-SS-012-30-027101](#) [813-SS-010-30-024101](#)