



ENGLISH

Datasheet

Stock No. 146-6751

RS PRO Capacitive Sensor



Specifications:

Mounting: Flush

Rated distance S_n : 2mm (Adjustable)

Assured distance S_a : 0...1.6mm

Shape size: M12*52mm

Output way: PNP

Output status: NO

Supply voltage: 10...30 VDC

Standard target: Fe 12*12*1t

Switch point offset[%/Sr]: $\pm 20\%$

Hysteresis range [%/Sr]: 3...20%

Repeated error: $\leq 3\%$

Load current: $\leq 200\text{mA}$

Residual voltage: $\leq 2.5\text{V}$

Current consumption: $\leq 15\text{mA}$

Protection circuit: Short-circuit protection, overload protection and reverse polarity protection

Output indicator: Yellow LED

Ambient temperature: $-25^\circ\text{C} \dots 70^\circ\text{C}$

Ambient humidity: 35-95%RH

Switch frequency: 50 Hz

20/09/2017

High pressure resistance: 1000V/AC 50/60Hz 60s

Insulation resistance: $\geq 50\text{M}\Omega$ (500VDC)

Vibration resistance: Complex amplitude 1.5mm 10...50Hz(2H per X,Y,Z direction)

Protection degree: IP67

Housing material: Nickel-copper alloy

Connection: 2m PVC cable

Features:

Contactless detection, no damage to the detected target;

High detection precision and fast response frequency;

Able to detect metal and nonmetal objects,with wider application;

Different media in the container can be detected by a non-metallic tube wall.