




preci-dip

PCB CONNECTORS

SERIES
851

851-PP-NNN-40-001101
Single row
1.27 mm, Surface mount parallel

Ultraminiature PCB socket connectors Solder tail / SMD parallel mount.



TECHNICAL SPECS.:

Insulator	Black glass filled polyester PCT-GF30-FR
Flammability	UL 94V-O
Sleeve	Brass CuZn36Pb3 (C36000)
Contact	Clip (3 finger): Beryllium copper (C17200)
Mating pin Ø	0.38 to 0.50 mm
Insertion forces	0.5 N typ.
Withdrawal forces	0.2 N typ. (polished steel gauge Ø 0.41 mm)
Mechanical life	Min. 500 cycles
Rated current	1 A
Contact resistance	Max. 20 m
Dielectric strength	Min. 500 V RMS
Coplanarity SMD terminations	Max. 0.1 mm (measured on 25 mm long connectors)

ORDERING INFORMATION:

PP Plating code	Sleeve	Clip
87	Tin	Gold flash
83	Tin	Gold 0.75 µm

NNN number of poles. Replace NNN with the requested number of poles, e.g. 851-83-NNN-40-001101 for a single row version with 8 pins becomes 851-83-008-40-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole \varnothing : $0.7 + 0.09/-0.06$ mm | Drilled hole \varnothing : 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole \varnothing : $1 + 0.09/-0.06$ mm | Drilled hole \varnothing : 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

PACKAGING:

Standard connector packaging is card box.

SMD mount connectors available on request with Tape & Reel packaging acc. to EIA Standard 481.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[851-83-029-40-001101](#) [851-83-040-40-001101](#) [851-83-039-40-001101](#) [851-83-038-40-001101](#) [851-83-037-40-001101](#) [851-83-036-40-001101](#) [851-87-045-40-001101](#) [851-87-044-40-001101](#) [851-87-041-40-001101](#) [851-87-050-40-001101](#) [851-87-049-40-001101](#) [851-87-048-40-001101](#) [851-87-047-40-001101](#) [851-87-046-40-001101](#) [851-87-023-40-001101](#) [851-87-022-40-001101](#) [851-87-021-40-001101](#) [851-87-020-40-001101](#) [851-87-019-40-001101](#) [851-87-031-40-001101](#) [851-87-043-40-001101](#) [851-87-028-40-001101](#) [851-87-027-40-001101](#) [851-87-026-40-001101](#) [851-87-025-40-001101](#) [851-87-024-40-001101](#) [851-87-035-40-001101](#) [851-87-034-40-001101](#) [851-87-033-40-001101](#) [851-87-032-40-001101](#) [851-87-042-40-001101](#) [851-87-030-40-001101](#) [851-87-029-40-001101](#) [851-87-040-40-001101](#) [851-87-039-40-001101](#) [851-87-038-40-001101](#) [851-87-037-40-001101](#) [851-87-036-40-001101](#) [851-83-005-40-001101](#) [851-83-017-40-001101](#) [851-83-003-40-001101](#) [851-83-002-40-001101](#) [851-83-006-40-001101](#) [851-87-016-40-001101](#) [851-83-012-40-001101](#) [851-83-011-40-001101](#) [851-83-010-40-001101](#) [851-83-009-40-001101](#) [851-83-008-40-001101](#) [851-83-007-40-001101](#) [851-83-018-40-001101](#) [851-83-004-40-001101](#) [851-87-018-40-001101](#) [851-83-015-40-001101](#) [851-83-014-40-001101](#) [851-83-013-40-001101](#) [851-83-047-40-001101](#) [851-83-046-40-001101](#) [851-83-045-40-001101](#) [851-83-044-40-001101](#) [851-83-016-40-001101](#) [851-87-006-40-001101](#) [851-83-042-40-001101](#) [851-87-003-40-001101](#) [851-87-002-40-001101](#) [851-83-050-40-001101](#) [851-83-049-40-001101](#) [851-83-048-40-001101](#) [851-87-010-40-001101](#) [851-87-009-40-001101](#) [851-87-008-40-001101](#) [851-87-007-40-001101](#) [851-83-041-40-001101](#) [851-87-005-40-001101](#) [851-87-004-40-001101](#) [851-87-015-40-001101](#) [851-87-014-40-001101](#) [851-87-013-40-001101](#) [851-87-012-40-001101](#) [851-87-011-40-001101](#) [851-83-023-40-001101](#) [851-83-022-40-001101](#) [851-83-021-40-001101](#) [851-83-020-40-001101](#) [851-83-019-40-001101](#) [851-83-031-40-001101](#) [851-83-043-40-001101](#) [851-83-028-40-001101](#) [851-83-027-40-001101](#) [851-83-026-40-001101](#) [851-83-025-40-001101](#) [851-83-024-40-001101](#) [851-83-035-40-001101](#) [851-83-034-40-001101](#) [851-83-033-40-001101](#) [851-83-032-40-001101](#) [851-87-017-40-001101](#) [851-83-030-40-001101](#)