

TECHNICAL DATA SHEET

Stainless steel type SA.B

General notes:

- Austenitic steel (Material number 1.4301, DIN X5CrNi1810, AISI number 304)
- contains from 17.5 to 20 wt% chromium and has important quantities of nickel
- non-magnetizable
- good corrosion resistance to a wide range of atmospheric environments and many corrosive media
- generally used where corrosion resistance and toughness are primary requirements
- typical applications include tweezers for the electronic industry, screws, machinery parts and food-handling equipment

Composition

Component	Wt.%	Component	Wt.%	Component	Wt.%
С	≤0.08	Si	≤1.0	Mn	≤2.0
Р	≤0.045	S	≤0.03	Cr	17.5-20.0
Мо	2.5-3.0	Ni	8.0-11.0		

Mechanical properties

annealed
8.0 g/cm ³
210 HV
600 MPa
330
≥ 290 MP a
55%
193 GPa

Thermal properties

Coef. of lin. therm expansion	16.0 E-6/°C	20°C-100°C
Coef. of lin. therm expansion	17.0 E-6/°C	20°C-300°C
Specific heat capacity	0.50 J/(g·K)	
Thermal conductivity	16 W/(m·K)	
Continuos use temperature	350°C	
Max service temperature, air	925°C	

Electrical properties

0.72 E-4 Ohm.cm Resistivity

This document contains information based on average values as obtained from the results of laboratory tests and observations made on the material. Ideal-Tek SA declines all responsibility from an improper use of the product described in this document.

