


# STM1061

## Low Power Voltage Detector

### Features

- Factory-trimmed Voltage Thresholds in 0.1V Increments from 1.6 to 5.5V
- ±2% Voltage Threshold Accuracy
- Operating Voltage 0.7 to 6.0V
- Open Drain Output
- Low Supply Current of 0.9µA (typ)
- Guaranteed OUT Assertion Down to V<sub>CC</sub> = 0.7V
- Power Supply Transient Immunity
- Available in SOT23-3 and SOT323-3 (SC70-3) packages
- Operating Temperature –40 to 85°C.



1. Contact local sales office for availability.

## Contents

1	Summary Description 5				
2	Pin Descriptions7				
	2.1 OUT (Open Drain)				
	2.2 V <sub>CC</sub>				
	2.3 V <sub>SS</sub>				
3	Operation				
	3.1 Output				
	3.2 Negative-Going V <sub>CC</sub> Transients and Undershoot				
4	Typical Operating Characteristics9				
5	Maximum Rating				
6	DC and AC Parameters				
7	Package Mechanical				
8	Part Numbering				
9	Revision History				



## List of tables

Table 1.	Signal Names
Table 2.	Pin Functions
Table 3.	Absolute Maximum Ratings
Table 4.	Operating and AC Measurement Conditions14
Table 5.	DC and AC Characteristics
Table 6.	SOT23-3 – 3-lead Small Outline Transistor Package Mechanical Data
Table 7.	SOT323-3 (SC70-3) – 3-lead Small Outline Transistor Package Mechanical Data 19
Table 8.	Ordering Information Scheme
Table 9.	Factory-Trimmed Thresholds with Marking Description
Table 10.	Document Revision History



# List of figures

Figure 1.	Packages	1
Figure 2.	Logic Diagram	5
Figure 3.	SOT23-3 Connections	5
Figure 4.	SOT323-3 (SC70-3) Connections	6
Figure 5.	N-Channel Open Drain Output Block Diagram	
Figure 6.	STM1061N Active-Low, Open Drain Hardware Hookup	6
Figure 7.	Supply Current vs. Input Voltage	9
Figure 8.	Supply Current vs. Ambient Temperature	9
Figure 9.	Output Detect Delay Time vs. Ambient Temperature 1	0
Figure 10.	Output Release Delay Time vs. Ambient Temperature10	
Figure 11.	Maximum Transient Duration vs. Reset Threshold Overdrive1	1
Figure 12.	Detect, Release Voltage vs. Ambient Temperature for $V_{TH-} = 3.4V$	
Figure 13.	N-channel Driver Output Current vs. V <sub>DS</sub>	2
Figure 14.	N-channel Driver Output Current vs. Input Voltage for $V_{DS} = 0.5V$	2
Figure 15.	AC Testing Input/Output Waveforms 14	4
Figure 16.	Voltage Timing Waveform1	5
Figure 17.	SOT23-3 – 3-lead Small Outline Transistor Package Outline 1	7
Figure 18.	SOT323-3 (SC70-3) – 3-lead Small Outline Transistor Package Outline	9



### **1** Summary Description

The STM1061 low power voltage detector provides monitoring of battery, power-supply, and regulated system voltages. A precision voltage reference and comparator monitors the V<sub>CC</sub> input and compares it with a specified voltage threshold condition. When V<sub>CC</sub> falls below a specified trip point threshold, the output ( $\overline{OUT}$ ) is forced low and remains asserted as long as the V<sub>CC</sub> input remains below V<sub>TH</sub> + hysteresis (V<sub>HYST</sub>). The STM1061 device is guaranteed to output the correct logic state for V<sub>CC</sub> down to 0.7V. They are also designed to ignore fast transients on V<sub>CC</sub>.

This small, low power device is ideal for portable applications and is available in spacesaving SOT23-3 and SOT323-3 (SC70-3) packages.








Table 1.Signal Names


OUT	Open Drain Active-Low Output
V <sub>CC</sub>	Supply Voltage
V <sub>SS</sub>	Ground

#### Figure 3. SOT23-3 Connections



















## 2 Pin Descriptions

See *Figure 2 on page 5* and *Table 1 on page 5* for a brief overview of the signals connected to this device.

## 2.1 OUT (Open Drain)

This is the Open Drain Output. It goes low when V<sub>CC</sub> drops below V<sub>TH</sub>, and remains low as long as V<sub>CC</sub> is below V<sub>TH</sub> + V<sub>HYST</sub>.

## 2.2 V<sub>CC</sub>

This is the Supply voltage and input for the Voltage Detector.

## 2.3 V<sub>SS</sub>

Ground,  $\mathsf{V}_{\text{SS}}$  is the reference for the power supply. It must be connected to the system ground.

P	in		Function		
SOT23-3	SOT323-3 (SC70-3)	Name			
1	2	OUT	Active-Low Open Drain Output		
3	3	V <sub>CC</sub>	Supply Voltage		
2	1	$V_{SS}$	Ground		



### 3 Operation

### 3.1 Output

The STM1061 Voltage Detector monitors system voltages from 1.6 to 5V in 100mV increments. The detector is designed to ignore fast transients on V<sub>CC</sub> and has a voltage hysteresis (V<sub>HYST</sub>). The STM1061 asserts an output signal ( $\overline{OUT}$ ) whenever V<sub>CC</sub> goes below the Voltage Detect Threshold (V<sub>TH</sub>). The output signal ( $\overline{OUT}$ ) stays asserted until V<sub>CC</sub> goes above the Voltage Detect Release (V<sub>TH+</sub>). Output voltage (V<sub>OUT</sub>) is guaranteed valid down to V<sub>CC</sub> =0.7V at 25°C.

The STM1061has an open drain active-low output which will sink current when output is asserted. Connect a pull-up resistor from OUT to any supply voltage up to 6V (see *Figure 6 on page 6*). Select a resistor value large enough to register a logic low, and small enough to register a logic high while all of the input current and leakage paths connected to the reset output line are being supplied. A 10k pull-up is sufficient in most applications.

The advantages of open drain output is the ability to connect more open drain outputs in parallel (wired OR connections) as well as connect the output to a power supply voltage different from  $V_{CC}$ .


### 3.2 Negative-Going V<sub>CC</sub> Transients and Undershoot

The STM1061 device is relatively immune to negative-going V<sub>CC</sub> transients (glitches). The graph (see *Figure 11 on page 11*) indicates the maximum pulse width a negative V<sub>CC</sub> transient can have without causing a reset pulse. As the magnitude of the transient increases (further below the threshold), the maximum allowable pulse width decreases. Any combination of duration and overdrive which lies under the curve will NOT generate a reset signal.


A 0.1 $\mu$ F bypass capacitor mounted as close as possible to the V<sub>CC</sub> pin provides additional transient immunity.





## 4 Typical Operating Characteristics












#### Figure 9. **Output Detect Delay Time vs. Ambient Temperature**



### Figure 10. Output Release Delay Time vs. Ambient Temperature

10/23




Figure 11. Maximum Transient Duration vs. Reset Threshold Overdrive

1. Reset occurs above the curve.






Figure 12. Detect, Release Voltage vs. Ambient Temperature for  $V_{TH-} = 3.4V$ 







#### 12/23

## 5 Maximum Rating

Stressing the device above the rating listed in the *Table 3: Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in the Operating sections of this specification is not implied. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics SURE Program and other relevant quality documents.

Symbol	Parameter	Value	Unit
T <sub>STG</sub>	Storage Temperature (V <sub>CC</sub> Off, V <sub>BAT</sub> Off)	-55 to 150	°C
T <sub>SLD</sub> <sup>(1)</sup>	Lead Solder Temperature for 10 seconds	260	°C
V <sub>IO</sub>	Input or Output Voltage	–0.3 to V <sub>CC</sub> +0.3	V
V <sub>CC</sub>	Supply Voltage	-0.3 to 7.0	V
۱ <sub>0</sub>	Output Current	20	mA
PD	Power Dissipation	320	mW

Table 3. Absolute Maximum Ratings

1. Reflow at peak temperature of 260°C (total thermal budget not to exceed 245°C for greater than 30 seconds).




## 6 DC and AC Parameters

This section summarizes the operating measurement conditions, and the DC and AC characteristics of the device. The parameters in the DC and AC characteristics Tables that follow, are derived from tests performed under the Measurement Conditions summarized in *Table 4: Operating and AC Measurement Conditions*. Designers should check that the operating conditions in their circuit match the operating conditions when relying on the quoted parameters.

Sym	Parameter	STM1061	Unit
V <sub>CC</sub>	Supply Voltage	0.7 to 6.0	V
T <sub>A</sub>	Ambient Operating Temperature	-40 to 85	°C
	Input Rise and Fall Times	≤ 5	ns
	Input Pulse Voltages	0.2 to 0.8V <sub>CC</sub>	V
	Input and Output Timing Ref. Voltages	0.3 to 0.7V <sub>CC</sub>	V

Table 4.	<b>Operating and AC Measurement Conditions</b>
----------	--

### Figure 15. AC Testing Input/Output Waveforms






Figure 16. Voltage Timing Waveform



Sym.	Description	Test Condition <sup>(1)</sup>	Min	Тур	Max	Unit
V <sub>CC</sub>	Operating Voltage		0.7		6.0	V
		V <sub>CC</sub> = 3.0V, No Load		0.9	3.0	μA
I <sub>CC</sub>	V <sub>CC</sub> Supply Current	V <sub>CC</sub> = 5.5V, No Load		1.1	3.6	μA
		V <sub>CC</sub> = 1.0V	1.0	1.7		mA
	Output Current, N-channel	V <sub>CC</sub> = 2.0V	3.0	14		mA
I <sub>OUT</sub>	$(V_{DS} = 0.5V),$	$V_{CC} = 3.0V$	5.0	22		mA
	Reset asserted	$V_{CC} = 4.0V$	6.0	26		mA
		$V_{CC} = 5.0V$	7.0	30		mA
Voltage 7	hresholds					
V <sub>TH-</sub>	Detect Voltage <sup>(2)</sup> (see <i>Table 9 on page 21</i> for detailed listing)		V <sub>TH-</sub> – 2%	V <sub>TH-</sub>	V <sub>TH-</sub> + 2%	V
V <sub>TH+</sub>	Release Voltage			V <sub>TH–</sub> + V <sub>HYST</sub>		V
V <sub>HYST</sub>	Threshold Hysteresis		0.02∨ <sub>TH–</sub>	0.05∨ <sub>TH−</sub>	0.08∨ <sub>TH−</sub>	V
t <sub>PD</sub>	V <sub>CC</sub> to OUT Detect Delay	V <sub>CC</sub> falling from (V <sub>TH</sub> + 100mV) to (V <sub>TH</sub> – 100mV) at 10mV/µs		25		μs
t <sub>PR</sub>	V <sub>CC</sub> to OUT Release Delay	V <sub>CC</sub> rising from (V <sub>TH+</sub> - 100mV) to (V <sub>TH+</sub> + 100mV) at 10mV/µs		30	200	μs
	Threshold Temperature Coefficient			±100		ppm/ <sup>o</sup> C

Table 5. DC and AC Characteristics

1. Valid for Ambient Operating Temperature:  $T_A = 25^{\circ}C$ .

2. Other  $V_{TH-}$  threshold are offered. Minimum order quantities may apply. Contact local sales office for availability.

## 7 Package Mechanical

In order to meet environmental requirements, ST offers these devices in ECOPACK<sup>®</sup> packages. These packages have a Lead-free second level interconnect. The category of second Level Interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97.

The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com.




Figure 17. SOT23-3 – 3-lead Small Outline Transistor Package Outline

1. Drawing is not to scale.



Symbol	mm				inches		
	Тур	Min	Max	Тур	Min	Max	
А		0.89	1.12		0.035	0.044	
A1		0.01	0.10		0.001	0.004	
A2		0.88	1.02		0.035	0.042	
b		0.30	0.50		0.012	0.020	
С		0.08	0.20		0.003	0.008	
D		2.80	3.04		0.110	0.120	
E		2.10	2.64		0.083	0.104	
E1		1.20	1.40		0.047	0.055	
е		0.89	1.03		0.035	0.041	
e1		1.78	2.05		0.070	0.081	
L	0.54			0.021			
L1		0.40	0.60		0.016	0.024	
Q		0°	8°		0°	8°	
Ν		3			3		

 Table 6.
 SOT23-3 – 3-lead Small Outline Transistor Package Mechanical Data






Figure 18. SOT323-3 (SC70-3) – 3-lead Small Outline Transistor Package Outline

1. Drawing is not to scale.


Table 7.	SOT323-3 (SC70-3) – 3-lead Small Ou Data	tline Transistor Package Mechanical	

Data						
Symbol -	mm			inches		
	Тур	Min	Max	Тур	Min	Max
А		0.80	1.10		0.031	0.043
A1		0.00	0.10		0.000	0.004
A2		0.80	1.00		0.031	0.039
b		0.25	0.40		0.010	0.016
С		0.10	0.18		0.004	0.007
D		1.80	2.20		0.071	0.087
E		1.80	2.40		0.071	0.094
E1		1.15	1.35		0.045	0.053
е		0.65			0.026	
e1		1.30			0.051	
L		0.35	0.45		0.014	0.018
L1		0.10	0.30		0.004	0.012
Q		0°	30°		0°	30°
Θ1		8°	12°		8°	12°
Ν		3			3	



## 8 Part Numbering

### Table 8.Ordering Information Scheme



F = ECOPACK Package, Tape & Reel

1. Other thresholds voltage options are offered. Minimum order quantities may apply. Contact local sales office for availability.

For other options, or for more information on any aspect of this device, please contact the ST Sales Office nearest you.

Table 9. Factory-Trimmed Thresholds with Marking Description							
Suffix	Threshold	Topoido Morking					
Suffix	Min (–2%)	Тур	Max (+2%)	<ul> <li>Topside Marking</li> </ul>			
16	1.568 1.600 1.632		16Nx				
17	1.666	1.700	1.734	17Nx			
19	1.862	1.862 1.900		19Nx			
21	2.058	2.100	2.142	21Nx			
22	2.156	2.200	2.244	22Nx			
23	2.254	2.300	2.346	23Nx			
25	2.450	2.450 2.500 2.5		25Nx			
26	2.548	2.548 2.600		26Nx			
27	2.646	2.700	2.754	27Nx			
28	2.744	2.800	2.856	28Nx			
29	2.842	2.900	2.958	29Nx			
30	2.940	3.000	3.060	30Nx			
31	3.038	3.100	3.162	31Nx			
34	3.332	3.400	3.468	34Nx			
38	3.724	3.800	3.876	38Nx			

 Table 9.
 Factory-Trimmed Thresholds with Marking Description

Other V<sub>TH</sub>- thresholds are offered. Minimum order quantities may apply. Contact local sales office for availability.



# 9 Revision History

Table 10. Document Revision History

Date	Version	Description	
20-January- 2004	1.0	First Edition	
01-Aug-05	1.1	Update Operation section, characteristics; insert new graphics; add ECOPACK information ( <i>Figure 7, 8, 9, 10, 11, 12, 13</i> , and <i>14</i> ; Table <i>Table 5, 8</i> , and <i>9</i> )	
02-Sep-05	1.2	Update characteristics, remove 'push-pull output' reference ( <i>Figure 8</i> , <i>9</i> , <i>10</i> , <i>11</i> , <i>12</i> , and <i>16</i> ; Table <i>Table 2</i> , , <i>5</i> , and <i>8</i> )	
19-Oct-05	2.0	Status upgrade; update characteristics; add Marking information ( <i>Figure 7, 8, 9, 10, 11, 12, 13, and 14</i> ; Table <i>Table 8</i> , and <i>9</i> )	
18-Nov-05	3.0	Update characteristics (Table 3, and 4)	
27-Jul-2006	4	Update Chapter : Features, Figure 1, 5, 6, Table 8 and 9.	



#### Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2006 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

