



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2013-09-18	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	969973-5	<b>Amount</b>	779.74	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	964818-1				1.0	94.0	mg	
Material	2	LCP-GF30				1.0	94.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	0.376	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.2	1.0	65.048	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	28.2	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.4	1.0	0.376	mg	
Sub-Item	1	966737-5				1.0	685.74	mg	
Material	2	Tin Plate				1.0	2.01	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00200799	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	2.00799	mg	
Material	2	Gold Plate				1.0	0.42	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	0.4158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.0042	mg	
Material	2	PA46-GF30				1.0	350.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.5	1.0	19.25	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.6	1.0	5.6	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.5	1.0	68.25	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0060	1.0	0.021	mg	
Substance	3	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	43.386	1.0	151.851	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	105.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0080	1.0	0.028	mg	
Material	2	Gold Plate				1.0	0.03	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.02991	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	9.0E-5	mg	
Material	2	Phos Bronze				1.0	332.8	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	1.0	315.10669	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.06656	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.03328	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	14.976	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	0.04992	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.3328	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03328	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.003328	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.9984	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.3328	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.3328	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.03328	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1664	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.3328	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001664	mg	
Material	2	Nickel Plate				1.0	0.48	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	1.0	9.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.8E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.47856	mg	