





preci-dip

PCB CONNECTORS

SERIES
861

861-PP-NNN-40-001101
Single row
1 mm, Surface mount parallel

Ultraminiature PCB socket connectors Solder tail / SMD parallel mount.



TECHNICAL SPECS.:

| | |
|-------------------------------------|---|
| Insulator | Black glass filled polyester PCT-GF30-FR |
| Flammability | UL 94V-O |
| Sleeve | Brass CuZn36Pb3 (C36000) |
| Contact | Clip (4 finger): Beryllium copper (C17200) |
| Mating pin Ø | 0.36 to 0.46 mm |
| Insertion forces | 0.25 N typ. |
| Withdrawal forces | 0.15 N typ. (polished steel gauge Ø 0.40 mm) |
| Mechanical life | Min. 500 cycles |
| Rated current | 1 A |
| Contact resistance | Max. 10 m |
| Dielectric strength | Min. 1000 V RMS |
| Coplanarity SMD terminations | Max. 0.1 mm (measured on 25 mm long connectors) |

ORDERING INFORMATION:

| | | |
|-----------------|--------|--------------|
| PP Plating code | Sleeve | Clip |
| 87 | Tin | Gold flash |
| 83 | Tin | Gold 0.75 µm |

NNN number of poles. Replace NNN with the requested number of poles, e.g. 861-87-NNN-10-001101 for a single row version with 8 pins becomes 861-87-008-10-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

| | |
|-----------------------------|---------------------------------|
| Operating temperature range | -55 ... +125 °C |
| Climatic category (IEC) | 55/125/21 |
| Operating humidity range | annual mean 75 % |
| Max working voltage | 100 VRMS/150 VDC (2.54 mm grid) |

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

| | |
|-----------------------------------|---|
| Clip retention | Min. 40 N (no displacement under axial force applied) |
| Contact (sleeve / clip) retention | Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2 |

ELECTRICAL CHARACTERISTICS:

| | |
|---|---------------------------|
| Insulation resistance between any two adjacent contacts | Min. 10'000 M at 500 V AC |
| Capacitance between any two adjacent contacts | Max. 1 pF |

Air and creepage distances between any two adjacent contacts :

| SERIES | 3xx/4xx/7xx | 80x | 83x | 85x | 86x |
|--------|-------------|------------|-----|-----------|-----|
| mm | 0.7 | 0.85 / 0.7 | 0.5 | 0.4 / 0.5 | 0.5 |

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole \varnothing : $0.7 + 0.09/-0.06$ mm | Drilled hole \varnothing : 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole \varnothing : $1 + 0.09/-0.06$ mm | Drilled hole \varnothing : 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

PACKAGING:

Standard connector packaging is card box.

SMD mount connectors available on request with Tape & Reel packaging acc. to EIA Standard 481.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[861-87-023-40-001101](#) [861-87-034-40-001101](#) [861-87-033-40-001101](#) [861-87-032-40-001101](#) [861-87-031-40-001101](#) [861-87-030-40-001101](#) [861-83-002-40-001101](#) [861-83-011-40-001101](#) [861-83-008-40-001101](#) [861-83-007-40-001101](#) [861-83-006-40-001101](#) [861-83-005-40-001101](#) [861-83-004-40-001101](#) [861-83-003-40-001101](#) [861-83-038-40-001101](#) [861-83-010-40-001101](#) [861-83-049-40-001101](#) [861-83-012-40-001101](#) [861-87-011-40-001101](#) [861-83-009-40-001101](#) [861-83-044-40-001101](#) [861-83-043-40-001101](#) [861-83-042-40-001101](#) [861-83-041-40-001101](#) [861-83-040-40-001101](#) [861-83-039-40-001101](#) [861-83-050-40-001101](#) [861-83-035-40-001101](#) [861-83-048-40-001101](#) [861-83-036-40-001101](#) [861-83-046-40-001101](#) [861-83-045-40-001101](#) [861-87-007-40-001101](#) [861-87-006-40-001101](#) [861-87-005-40-001101](#) [861-87-004-40-001101](#) [861-87-003-40-001101](#) [861-87-002-40-001101](#) [861-83-014-40-001101](#) [861-83-013-40-001101](#) [861-83-025-40-001101](#) [861-83-047-40-001101](#) [861-87-009-40-001101](#) [861-87-008-40-001101](#) [861-83-020-40-001101](#) [861-83-019-40-001101](#) [861-83-018-40-001101](#) [861-83-017-40-001101](#) [861-83-016-40-001101](#) [861-83-015-40-001101](#) [861-83-027-40-001101](#) [861-83-026-40-001101](#) [861-83-024-40-001101](#) [861-83-037-40-001101](#) [861-83-022-40-001101](#) [861-83-021-40-001101](#) [861-83-033-40-001101](#) [861-83-032-40-001101](#) [861-83-031-40-001101](#) [861-83-030-40-001101](#) [861-83-029-40-001101](#) [861-83-028-40-001101](#) [861-87-038-40-001101](#) [861-87-049-40-001101](#) [861-87-010-40-001101](#) [861-87-012-40-001101](#) [861-83-023-40-001101](#) [861-83-034-40-001101](#) [861-87-044-40-001101](#) [861-87-043-40-001101](#) [861-87-042-40-001101](#) [861-87-041-40-001101](#) [861-87-040-40-001101](#) [861-87-039-40-001101](#) [861-87-050-40-001101](#) [861-87-035-40-001101](#) [861-87-048-40-001101](#) [861-87-036-40-001101](#) [861-87-046-40-001101](#) [861-87-045-40-001101](#) [861-87-016-40-001101](#) [861-87-015-40-001101](#) [861-87-014-40-001101](#) [861-87-013-40-001101](#) [861-87-025-40-001101](#) [861-87-047-40-001101](#) [861-87-022-40-001101](#) [861-87-021-40-001101](#) [861-87-020-40-001101](#) [861-87-019-40-001101](#) [861-87-018-40-001101](#) [861-87-017-40-001101](#) [861-87-029-40-001101](#) [861-87-028-40-001101](#) [861-87-027-40-001101](#) [861-87-026-40-001101](#) [861-87-024-40-001101](#) [861-87-037-40-001101](#)