
Precision Thin Film Chip Resistors



PFC Special Series

Features

- Standard 60/40 Sn/Pb and Pb-free (RoHS compliant) terminations available
- Available in 0402, 0603, 0805 and 1206
- Tested for COTS applications
- Absolute TCR to ±10ppm/°C
- MIL screening available
- Superior anti-sulfuration characteristics



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

The TaNFilm [®] PFC chip resistor series provides the high precision and ultra stable performance of our Tantalum Nitride resistive film system in 0402, 0603, 0805 and 1206 sizes. The unique characteristics of the passivated Tantalum Nitride film ensure long term life stability and reliability in most environments. Qualified for resistance to sulfur bearing gases, the PFC series is an excellent solution for automotive and heavy equipment applications where precision, exceptional reliability with anti-sulfuration characteristics is imperative.

Using the same manufacturing line as the PFC Military Series, these precision chips maintain the same superior environmental performance. Specially selected materials and processes ensure initial precision is maintained in the harshest surface mount soldering environment. Wrap-around terminations with leach-resistant nickel barriers ensure high integrity solder connections.

Electrical Data

Model	Power Rating (70°C)	Max Voltage Rating ($\leq \sqrt{P x R}$)	Temperature Range	ESD Sensitivity	Noise	Termination	Substrate
W0402	50mW	75V					
W0603	100mW	75V			<-25dB	100% matte tin (RoHS compliant) plated over	99.5% Alumina
W0805	250mW	100V	-65°C to +150°C	2KV to 4KV (HBM)			
W1206	333mW	200V				nickel barrier	

Environmental Data

Environmental Test	Test Method	Performance		
Environmentar rest	Test Method	Typical	Maximum	
Sulfuration Test (ASLF terminations only)	ASTM B-809 (Modified) 105°C Dry, 1000 Hours		+0.05%	
Summation rest (ASLF terminations only)	EIA-977 Condition B, 105°C Dry, 750 Hours	±0.02%	±0.05%	
Thermal Shock	MIL-PRF-55342	±0.02%	±0.10%	
Low Temperature Operation	MIL-PRF-55342	±0.01%	±0.05%	
Short Time Overload	MIL-PRF-55342	±0.01%	±0.05%	
High Temperature Exposure	MIL-PRF-55342	±0.03%	±0.10%	
Effects of Solder	MIL-PRF-55342	±0.01%	±0.10%	
Moisture Resistance	MIL-PRF-55342	±0.03%	±0.10%	
Life	MIL-PRF-55342	±0.03%	±0.10%	

General Note

Downloaded from Arrow.com.

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

www.ttelectronics.com/resistors

Precision Thin Film Chip Resistors





Manufacturing Capabilities Data

TCR ppm/°C						Тс	lerance %					
	W0402			W0603		W0805 W1206						
pp, -	0.02	0.05	0.1-5	0.02	0.05	0.1-5	0.02	0.05	0.1-5	0.02	0.05	0.1-5
10	100Ω	-16kΩ	$100\Omega - 16k\Omega^1$	100Ω-	-50kΩ	100Ω - $50k\Omega^1$	100Ω	-100kΩ	100Ω-125kΩ³	100Ω-	400kΩ	100Ω -400k Ω^1
15	50Ω-	16kΩ	$50\Omega - 16k\Omega^1$	50Ω-	50kΩ	$50\Omega-50k\Omega^1$	50Ω-	100kΩ	50Ω-125kΩ³	50Ω-4	100kΩ	50Ω -400k Ω^1
25	500 1ck0	10Ω-24kΩ	10Ω-30kΩ ² 50Ω-50kΩ 10Ω-75kΩ	100 7540	10Ω - $100k\Omega^1$	50Ω-100kΩ		10Ω -267k Ω^1	500 400k0	100 (50k0	$10\Omega - 1M\Omega^1$	
50, 100	50Ω-16kΩ 00	1002-24K02	7.5Ω-30kΩ²	2077-20KU	10Ω-75ΚΩ	5Ω -100k Ω^1	2075-T00K0	10Ω-180kΩ	5Ω -267k Ω^1	50Ω-400kΩ	10Ω-650kΩ	5Ω - $1M\Omega^1$

Notes


1. For unscreened PFC chips see separate PFC Commercial Series datasheet

2. For unscreened PFC chips at values ≥15R see separate PFC Commercial Series datasheet

3. For unscreened PFC chips at values ≤100K see separate PFC Commercial Series datasheet

4. The anti-sulfur (AS / ASLF) option is only available at values of 100R and higher.

Power Derating Curve



Physical Data

L С SIDE TOP W BOTTOM b Model L. w н h c (min.) а 0.04 ±0.002 0.021 ±0.002 0.012 ±0.003 0.008 ±0.002 0.01 ±0.002 0.017 W0402 (1.02 ± 0.05) (0.53 ±0.05) (0.3 ± 0.08) (0.2 ± 0.05) (0.25 ±0.05) (0.43)0.063 ±0.004 0.031 ±0.004 0.02 ±0.006 0.012 ±0.005 0.015 ±0.005 0.03 W0603 (1.6 ±0.1) (0.79 ±0.1) (0.51 ±0.15) (0.3 ±0.13) (0.38 ±0.13) (0.76)0.081 ±0.005 0.05 ±0.005 0.02 ±0.006 0.015 ±0.008 0.016 ±0.008 0.046 W0805 (1.27 ±0.13) (0.38 ±0.2) (2.06 ±0.13) (0.51 ±0.15) (0.41 ±0.2) (1.17)0.126 ±0.006 0.063 ±0.005 0.024 ±0.004 0.025 ±0.01 0.025 ±0.01 0.085 W1206 (0.64 ±0.25) (3.2 ±0.15) (1.6 ±0.13) (0.61 ±0.1) (0.64 ±0.25) (2.16)

MIL Screened Precision Chip Resistors

IRC's PFC chip resistors are available with MIL screening. These chips are manufactured on the same production line as our Mil-qualified chip resistors and screened in accordance with MIL-PRF-55342. These chips are identified with IRC's ordering information and not with MIL marking.

See separate MIL-CHIP datasheet.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print

Downloaded from Arrow.com.


www.ttelectronics.com/resistors



Ordering Procedure


This product has two valid part numbers:

European (Welwyn) Part Number: W1206R-01-1K0AI (1206, 100ppm/°C, 1 kilohm ±0.05%, Pb-free)



1	2	3	4	5	6	7	,	
Туре	Size	Option	TCR	Value	Tolerance	Terminatior	n & Packing	
W=PFC	0402	R=Standard	-12 = ±10ppm/°C	E24 = 3/4 characters	Q = ±0.02%	I ¹ = Pb-free, S	tandard pack	
	0603	AS=Anti-sulfur	-11 = ±15ppm/°C	E96 = 3/4 characters	$A = \pm 0.05\%$	PB ² = SnPb finish	, Standard pack	
	0805	(values ≥100R only)	Blank = ±25ppm/°C	R = ohms	B = ±0.1%	All sizes	1000/reel	
	1206		-02 = ±50ppm/°C	K = kilohms	D = ±0.5%	Note 1 – Alternative of	e code PL is also valid	
		-	-01 = ±100ppm/°C	M = megohms	F = ±1%	Note 2 – Alternative of		
					G = ±2%			
					J = ±5%			

USA (IRC) Commercial Part Number: PFC-W1206LF-01-1001-A (1206, 100ppm/°C, 1 kilohm ±0.05%, Pb-free)



1	2	3	4	5	6		
Family	Model	Termination	TCR	Value	Tolerance	Pac	king
PFC	W0402	R ¹ = SnPb (60/40)	12 = ±10ppm/°C	3 digits + multiplier	Q = ±0.02%	All sizes	1000/reel
	W0603	LF ² = Pb-free (100%Sn)	11 = ±15ppm/°C	R = ohms for	A = ±0.05%		
	W0805	AS=Anti-sulfur & SnPb (60/40)	03 = ±25ppm/°C	values <100 ohms	B = ±0.1%		
	W1206	ASLF=Anti-sulfur & Pb-free	02 = ±50ppm/°C		D = ±0.5%		
		(100%Sn) (values ≥100R only)	01 = ±100ppm/°C		F = ±1%		
	Note 1 – Alt	ternative code PR is also valid	G = ±2%				
		ternative code PLF is also valid		J = ±5%			

USA (IRC) Mil Screened Part Number*: PFC-W1206R-05-1001-B (1206, 100ppm/°C, 1 kilohm ±0.1%,)

F С W 1 2 0 6 R 0 5 1 0 0 1 В Ρ ----2 3 5 6 4

1	2	3	4	5	6	
Family	Model	Termination	TCR	Value	Tolerance	Packing
PFC	W0402	R = SnPb (60/40)	16 = ±10ppm/°C	3 digits + multiplier	B = ±0.1%	All sizes 1000/reel
	W0603		15 = ±15ppm/°C	R = ohms for	D = ±0.5%	
	W0805		14 = ±20ppm/°C	values <100 ohms	F = ±1%	
	W1206		07 = ±25ppm/°C		G = ±2%	
			06 = ±50ppm/°C		J = ±5%	
			05 = ±100ppm/°C			
			04 = ±300ppm/°C			

* Please refer to the MIL-CHIP datasheet to order parts qualified to MIL-PRF-55342.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print. BI Technologies IRC Welwyn

Downloaded from Arrow.com.