

# AN2448 Application note

## EVALTSM1052: Ultra small battery charger using TSM1052

#### Introduction

This document describes a low power adapter that can be used in travel battery charger applications. It uses the new Constant Voltage Constant Current (CVCC) controller TSM1052, which is housed in one of the smallest packages available (SOT23-6L). Thanks to its low consumption and low operating voltage, good electrical performance is achieved. Another important feature of this SMPS is the absence of the Y1 safety capacitor between primary and secondary grounds.

Figure 1. EVALTSM1052 demo board





Contents AN2448

# **Contents**

1	Adap	Adapter teatures						
	1.1	Main characteristics						
	1.2	Circuit description						
2	Elect	rical behavior7						
3	Elect	trical performance						
	3.1	Efficiency						
	3.2	Output characteristics						
	3.3	Hold-up time						
4	Cond	ducted noise measurements (pre-compliance test) 16						
5	Ther	mal measurements17						
6	вом							
7	РСВ	layout 20						
8	Revi	sion history						

AN2448 List of figures

# **List of figures**

Figure 1.	EVALTSM1052 demo board	1
Figure 2.	Electrical diagram	5
Figure 3.	V <sub>in</sub> = 115 Vrms - 60 Hz	
Figure 4.	V <sub>in</sub> = 230 Vrms - 50 Hz	
Figure 5.	Maximum supply voltages	
Figure 6.	Minimum supply voltages	9
Figure 7.	$V_{in} = 115 V_{ac}$ - no-load	10
Figure 8.	V <sub>in</sub> = 230 V <sub>ac</sub> - no-load	10
Figure 9.	V <sub>in</sub> = 115 V <sub>ac</sub> - short circuit	11
Figure 10.	V <sub>in</sub> = 230 V <sub>ac</sub> - short circuit	11
Figure 11.	Efficiency vs. output current	13
Figure 12.	Output characteristics at 115 V <sub>ac</sub> with CDC (cable drop compensation)	13
Figure 13.	Power down at 115 V <sub>ac</sub> - 60 Hz	14
Figure 14.	Power down at 230 V <sub>ac</sub> - 50 Hz	15
Figure 15.	CE peak measure at 115 V <sub>ac</sub> and full load	16
Figure 16.	CE peak measure at 230 V <sub>ac</sub> and full load	16
Figure 17.	V <sub>in</sub> = 115 V <sub>ac</sub> - full load - bottom and top sides	
Figure 18.	V <sub>in</sub> = 230 V <sub>ac</sub> - full load - bottom and top sides	
Figure 19.	THT components placing (top side)	20
Figure 20.	SMT components placing (bottom side) and copper tracks	20

5/

Adapter features AN2448


# 1 Adapter features

#### 1.1 Main characteristics

- Input:
  - V<sub>in</sub>: 90 ~ 264 Vrms
  - f: 45 ~ 66 Hz
- Output:
  - 5.1Vdc ± 2%
  - 600 mA
  - Cable drop compensation (0.33 mV/mA)
- No-load:
  - Pin below 0.3 W
- Short circuit: protected with nominal current regulation
- PCB type & size:
  - CEM-1
  - Single side 35 μm
  - 48 x 18 mm
- Safety: according to EN60065
- EMI: according to EN55022 class B

AN2448 Adapter features





**577** 

Adapter features AN2448

#### 1.2 Circuit description

The circuit used implements a flyback topology, which is ideal for a low power, low cost isolated converter.

At primary side a VIPer12A-E has been used. This IC includes a current mode PWM controller and a Power MOSFET in a small SO-8 package. The converter works in both continuous and discontinuous conduction mode depending on the input voltage (the circuit has a wide range input) and the output load. The switching frequency is internally fixed at 60 KHz. The design has been developed to reduce overall component count and adapter cost.

The input section includes a resistor for inrush current limiting, a diode bridge, two electrolytic bulk capacitors and an inductor as front-end ac-dc converter and EMC filter. The transformer is a layer type, uses a standard EF12.6 ferrite core and is designed to have a reflected voltage of about 90 V. The peculiarity of this transformer is the winding technique which allows the elimination of the usual Y1 safety capacitor between the primary and the secondary. A RCD clamp network is used for leakage inductance demagnetization. The power supply for the VIPer12A-E is obtained with a self supply winding from the transformer connected in forward configuration. This circuit provides a voltage that is directly proportional to the input rectified voltage and independent from the load voltage. In this way even in short circuit condition ( $V_{OUT} = 0$ ), the IC is correctly supplied. The wide  $V_{DD}$  operating range (9 V to 38 V) of the VIPer12A-E allows a wide range mains input voltage.

At secondary side, the TSM1052 constant voltage constant current (CVCC) controller is used. Like the VIPer12A-E, the TSM1052 is also supplied with a forward configuration, in order to obtain the same benefit. The voltage is taken on one half of the secondary winding (between pins 8 and 6), rectified with diode D5 and added to the output voltage. Under all working conditions, the voltage supply for the TSM1052 and the photodiode IC1B is equal to the output voltage plus forward rectified voltage on half secondary. With this configuration a correct supply is provided over the whole input range, even with the output short circuited.

With this configuration a small ripple at twice line frequency is present at the output. This is due to the supply of the photodiode IC1B, which is a replica of the voltage on C2. Usually this is not a problem in battery chargers. There are two ways to eliminate this phenomenon if necessary:


- C9 can be substituted by an electrolytic capacitor (at least 47 μF)
- The TSM1052 and IC1B can be attached directly to the output voltage. In this case the current regulation is guaranteed only for output voltages down to 1.7 V


Resistor R7 has been added for cable drop compensation (the higher the output current the higher the output voltage). R7 has been chosen according to the cable characteristics (it has about  $0.3~\Omega$  of resistance).

AN2448 Electrical behavior

## 2 Electrical behavior

*Figure 3* and *Figure 4* show all the VIPer12A-E waveforms during normal operation at full load. The converter operates in DCM at both 115 Vrms and 230 Vrms:





Electrical behavior AN2448




Figure 4.  $V_{in} = 230 \text{ Vrms} - 50 \text{ Hz}$ 


Due to the forward supply, the  $V_{DD}$  voltage is directly proportional to the input voltage, so it is nearly double at 230  $V_{ac}$  with respect to 115  $V_{ac}$ .

The worst case (maximum / minimum) supply voltages for both primary and secondary sides are shown in *Figure 5* and *Figure 6*.

For the maximum voltages, the converter operates with the maximum load in CV mode (that is, the maximum output voltage is present, thanks to the cable drop compensation) and with the maximum input voltage (264  $\rm V_{ac}$ ). In this condition the VIPer12A-E has a maximum supply voltage of 35.2 V and the TSM1052 16.16 V. Minimum voltages are taken with short circuit on the output (CC regulation) and minimum input voltage (90  $\rm V_{ac}$ ). Given this condition the VIPer12A-E has a minimum supply voltage of 10.48 V and the TSM1052 2.12 V.

8/21

AN2448 Electrical behavior








Figure 6. Minimum supply voltages





Electrical behavior AN2448


Let's see what happens at the extreme conditions: no load and short circuit.

During no load conditions, the circuit operates in burst mode allowing an input power of less than 300 mW over the whole input voltage range.









**AN2448 Electrical behavior** 





Figure 9.  $V_{in} = 115 V_{ac}$  - short circuit

Figure 10.  $V_{in} = 230 V_{ac}$  - short circuit



577

With the circuit used in this evaluation board, when the output current has rapid variation from maximum to zero and the input voltage is low ( < 105  $V_{ac}$ ), the VIPer12A-E loses the supply for about 400-500 ms. The output voltage thereby decreases. After that time the IC turns on again and the output returns to the nominal value. This behavior is not problematic in this kind of application and has not been modified, in order to have a smaller and cheaper solution. If this phenomenon must be avoided, however, it is enough to increase C3 to 100  $\mu F$ .

# 3 Electrical performance

## 3.1 Efficiency

Table 1 and Table 2 show the board efficiency at the two nominal voltages.

Table 1. Efficiency at 115 Vrms

lo [A]	Vo [V]	Po [W]	lin [mA]	Pin [W]	Efficiency
0.1	5.153	0.520	16.9	0.832	62.5%
0.2	5.185	1.036	27.4	1.483	69.9%
0.3	5.217	1.566	38.2	2.235	70.1%
0.4	5.248	2.096	47.6	2.928	71.6%
0.5	5.280	2.638	58.7	3.769	70.0%
0.6	5.310	3.187	68.5	4.530	70.3%

Table 2. Efficiency at 230 Vrms

	•				
lo [A]	Vo [V]	Po [W]	lin [mA]	Pin [W]	Efficiency
0.1	5.158	0.520	12.8	1.033	50.4%
0.2	5.190	1.037	20.1	1.740	59.6%
0.3	5.222	1.568	25.5	2.364	66.3%
0.4	5.254	2.098	32.6	3.193	65.7%
0.5	5.286	2.641	38.4	3.908	67.6%
0.6	5.319	3.192	43.6	4.572	69.8%




Figure 11. Efficiency vs. output current

As indicated in *Table 3*, the no-load consumption is always below 300 mW, and therefore complies with the more restrictive standards (European Code Of Conduct).


Table 3. No-load consumption

Value	90V <sub>ac</sub>	115V <sub>ac</sub>	230V <sub>ac</sub>	264V <sub>ac</sub>
Pin [W]	0.106	0.131	0.239	0.273
V <sub>OUT</sub> [V]	5.12	5.12	5.12	5.12

### 3.2 Output characteristics

*Figure 12* shows the output characteristics (taken with 115  $V_{ac}$  mains input) on PCB pads and at the end of the output cable. Values are very close also at 230  $V_{ac}$ . It is interesting to note that, while in the constant current region, the output voltage can reach zero.

Figure 12. Output characteristics at 115 V<sub>ac</sub> with CDC (cable drop compensation)



5/

The effect of the cable drop compensation is also worthy of note. Table 4 shows the output voltage at various load amounts measured at the output connector, after the output cable. 115  $V_{ac}$  and 230  $V_{ac}$  mains input give very similar results. With the cable drop compensation the output voltage is nearly constant while, without this feature, at maximum load the output voltage goes down to 4.96 V (about -3.1%). The effect of this feature is also clearly visible in the output characteristic (Figure 12), with a flat line while in the constant voltage regulation region.

Table 4. Output voltage at output connector

lout [A]	0	0.1	0.2	0.3	0.4	0.5	0.6
Vout [V] with CDC	5.12	5.13	5.13	5.14	5.14	5.15	5.15
Vout [V] without CDC	5.12	5.09	5.07	5.04	5.01	4.98	4.96

#### Hold-up time 3.3

During power down phase the output voltage undergoes a clean transition without restart trials or glitches. By observing the waveforms it is possible to measure the hold-up time. In Figure 13 and Figure 14 this condition is shown for the two nominal voltages of 115 Vac and 230  $V_{ac}$ . In the worst case, 115  $V_{ac}$ , a hold-up time of about 17.1 ms is measured.

CH1: output voltage (yellow) CH3: rectified input voltage (purple) C1 \ 2.5V Stopped Single Seq 1/At )58.48Hz

Figure 13. Power down at 115 V<sub>ac</sub> - 60 Hz




Figure 14. Power down at 230  $V_{ac}$  - 50 Hz

#### Conducted noise measurements (pre-compliance 4 test)

Figure 15 and Figure 16 show the conducted noise measurements performed at the two nominal voltages with peak detection and considering only the worst phase. The measurements have a good margin with respect to the limits (stated in EN55022 CLASS B specifications).

**\* Agilent** 15:26:10 Jan 31, 2007 115Vac - N Ref 75 dB<sub>P</sub>V #Atten 10 dB #Peak Log 10 dB/ W1 S2 S3 LS A AA


VBW 30 kHz

Figure 15. CE peak measure at 115  $V_{ac}$  and full load



Start 150 kHz

#Res BW 9 kHz



Stop 30 MHz

Sweep 881.3 ms (1515 pts)

AN2448 Thermal measurements

### 5 Thermal measurements

A thermal analysis of the board was performed using an IR camera. The results are shown in *Figure 17* and *Figure 18* for 115  $V_{ac}$  and 230  $V_{ac}$  mains input. Both images refer to full load condition (lout = 600 mA).

 $T_{AMB} = 25$  °C for both figures

Emissivity = 0.9 for all points

Figure 17.  $V_{in} = 115 V_{ac}$  - full load - bottom and top sides




Table 5. Key component temperatures at 115  $V_{ac}$  - 600 mA

Point	Temperature [°C]	Reference
Α	69.2	R2 (clamp)
В	72.3	R1 (clamp)
С	63.0	IC2 (VIPer12A-E)
D	66.3 D4 (output diode)	
E	68.3 TR1 (windings)	
F	64.0 TR1 (ferrite)	
G	66.2	Hot spot on PCB due to bottom side components

17/21

Thermal measurements AN2448

Figure 18.  $V_{in} = 230 V_{ac}$  - full load - bottom and top sides

Table 6. Key component temperatures at 230  $V_{ac}$  - 600 mA

	•	ac
Point	Temperature [°C]	Reference
А	70.4	R2 (clamp)
В	72.7 R1 (clamp)	
С	67.9	IC2 (VIPer12A-E)
D	66.1	D4 (output diode)
E	70.4 TR1 (windings)	
F	66.0	TR1 (ferrite)
G	68.5 Hot spot on PCB due to bottom side compo	

AN2448 BOM

# 6 BOM

Table 7. EVALTSM1052 bill of material

Ref	Description	Size	Manufacturer
C1	Electr.cap. 2.2 μF 400 V 105°C SEK	ø6x11 p2.5	TEAPO/YAGEO
C2	Electr.cap. 4.7 μF 400 V 105°C SEK	ø8x11 p3.5	TEAPO/YAGEO
C3	Electr.cap. 33 μF 50 V 105°C	ø5x11 p2.5	
C6	Electr.cap. 470 μF 16 V 105ºC SEK	ø8x11 p3.5	TEAPO/YAGEO
C4	Chip capacitor 1.5 nF/250 V X7R	0805	
C5	Chip capacitor 330 nF/16 V X7R	0603	
C7	Chip capacitor 22 nF/25 V X7R	0603	
C8	Chip capacitor 4.7 nF/25 V X7R	0603	
C9	Chip capacitor 1 uF/16 V X7R	0603	
C10	Chip capacitor 10 nF/50 V X7R	0603	
C11	Chip capacitor 1.8 nF/50 V X7R	0603	
D1	Single phase bridge S1ZB60	MBS	
D2	Diode UF108G	D041	PANJIT
D3 D5	DIODE 1N4148WS	SOD323	
D4	Diode STPS3L40S	SMC	STMicroelectronics
F1	Fuse res. 10 Ohm ±5% 2 W		
I1	Inductor 1 mH CECL-102K		COILS ELECTR.
IC1	Opto SFH617-A3 X007	SMT	SIEMENS
IC2	I.C. VIPer12AS-E	SO8	STMicroelectronics
IC3	I.C. TSM1052CLT	SOT23-6L	STMicroelectronics
R1	Chip resistor 330 K ±5%	0805	
R2	Chip resistor 680 Ohm ±5%	0805	
R3	Chip resistor 1 K ±5%	0603	
R4	Chip resistor 2.2 Ohm ±5%	0603	
R5	Chip resistor 100 Ohm ±5%	0603	
R6	Chip resistor 330 Ohm ±5%	0603	
R7 R9	Chip resistor 22 K ±1%	0603	
R8	Chip resistor 4.7 K ±5%	0603	
R10	Chip resistor 10 K ±1%	0603	
R11	Chip resistor 0.33 Ohm ±1% 200 ppm	1206	
R12	Chip resistor 2.2 K ±5%	0805	
R13	Chip resistor 220 K ±5%	0603	

**577** 

PCB layout AN2448

Table 7.	EVALTSM1052 bill of material (	(continued)	

Ref	Description	Size	Manufacturer
R14	Chip resistor 22 K ±5%	0603	
R15	Chip resistor 0 Ohm	0603	
TR1	Transformer	EF12.6 LP	

# 7 PCB layout

Figure 19. THT components placing (top side)





Figure 20. SMT components placing (bottom side) and copper tracks



# 8 Revision history

Table 8. Revision history

Date	Revision	Changes
04-Jul-2007	1	First issue

#### Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics: EVALTSM1052