

Cable marker label - WML 7,5 (25X13)R - 0800075

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable marker label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, cable diameter: ≤ 7.5 mm, lettering field size: 25 x 13 mm, Number of individual labels: 2100

Your advantages

- High-quality labeling image created by thermal transfer printing
- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- Quick and easy handling
- Resistant to solvents
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The cable marker labels consist of a labeling field and a transparent protective foil



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 562089
GTIN	4046356562089

Technical data

Dimensions

Length (b)	36.5 mm
Width (a)	25.4 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 110 °C
Recommended storage conditions	23 °C / 50 % relative humidity. Storage in poly bags is recommended prior to processing.

General

Color	white
Base element material	Vinyl film

Cable marker label - WML 7,5 (25X13)R - 0800075

Technical data

General

Type	Label
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2100
Number of individual labels per row	3
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
----------	----------

Cable marker label - WML 7,5 (25X13)R - 0800075

Classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE MH 48542
---------------	--	---	---------------

Accessories

Accessories

Ink ribbon

Cable marker label - WML 7,5 (25X13)R - 0800075

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>