



**1-CONDUCTOR PCB TERMINAL
STRIP 1 SOLDER PIN/POLE IN LINE
PIN SPACING 5 MM / 0.197 IN WITH
PUSH BUTTONS
250-502 TO 250-516**

ITEM-NO. (ITEM-NO.)	250-506
Cross section1 (Cross section / mm²)	0.5 - 1.5
Cross section2 (Cross section / AWG)	20 - 14
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	17.5
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	6
Height (Height / mm)	16.5
Width (Width / mm)	31.5
Depth (Depth / mm)	13
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	6
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1.5 mm
Dimensions (Dimensions)	1.2 -0.1 mm