

PRODUCT DATASHEET C10684_EVA-D

EVA-D

~16° diffused spot beam

TECHNICAL SPECIFICATIONS:

Dimensions	Ø 35.0 mm
Height	16.4 mm
Fastening	glue
ROHS compliant	yes 🛈



MATERIAL SPECIFICATIONS:

Component

EVA-D

Туре	
Single lens	

Material	Colour	Finish
PMMA	clear	

ORDERING INFORMATION:


Component	
C10684_EVA-D	
» Box size:	

Qty in box	MOQ	MPQ	Box weight (kg)
540	90	45	4.0



PRODUCT DATASHE C10684_EVA-D

2/9



See also our general installation guide: www.ledil.com/installation_guide



	. I N	80'
CITIZE LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone	CLU7A2 (LES 4.2mm) 16.0° / 33.0° 92 % 7.5 cd/lm 1 White	
		32, <u>64</u> 32,
CREE (
LED	MC-E	
FWHM / FWTM	16.0°	
Efficiency	92 %	
Peak intensity	6 cd/lm	
LEDs/each optic	1	
Light colour	White	
Required compone	ents.	
		9 4
CREE C LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White	5 5 7 7 7 7 7 7 7 7 7 7
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents:	
ED FWHM / FWTM Efficiency Peak intensity EDs/each optic Light colour Required compone	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents:	57 100 67 120 7 65
ED WHM / FWTM Efficiency Peak intensity EDs/each optic Light colour Required compone CREEE ED	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents:	
ED WHM / FWTM Efficiency Peak intensity EDs/each optic Light colour Required compone CREEE ED WHM / FWTM	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0°	25
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone CREEE LED LED FWHM / FWTM Efficiency	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 %	
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone Required compone ED FWHM / FWTM Efficiency Peak intensity	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm	
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone Required compone Efficiency Peak intensity LEDs/each optic	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm 1	
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone CREEE LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm 1 White	
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone Required compone Efficiency Peak intensity LEDs/each optic	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm 1 White	
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone CREEE LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm 1 White	25
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required compone CREEE ED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	MHB-A/B 19.0° / 40.0° 83 % 5.4 cd/lm 1 White ents: XHP35 HI 22.0° / 46.0° 79 % 3.9 cd/lm 1 White	



CREE 4		
	TM	
LED	XM-L	
FWHM / FWTM	16.0°	
Efficiency	91 %	
LEDs/each optic	1	
Light colour	White	
Required compone		
CREE (r.	
LED	XP-G2	
FWHM / FWTM	16.0° / 30.0°	
Efficiency	87 %	
LEDs/each optic	1	
Light colour	White	
Required compone	nts:	
CREE 4		 90* 90*
LED	™ XT-E	
	14.0°	75'
FWHM / FWTM	%	
Efficiency		60* 60*
Peak intensity	7.5 cd/lm 1	612
LEDs/each optic	White	45 ⁴
Light colour		
Required compone	IIS.	3630
		30° 30° 30°
UMIL	EDS	30°
LED	LUXEON 5050 Round LES	
FWHM / FWTM	18.0° / 35.0°	73
Efficiency	91 %	
Peak intensity	6.4 cd/lm	
LEDs/each optic	1	220
Light colour	White	gge date and a second sec
Required compone		
		450
		\times / \setminus / \times



🥙 LUMIL	.EDS		
LED	LUXEON M/MX		
FWHM / FWTM	21.0°		
Efficiency	90 %		
Peak intensity	4.2 cd/lm		
LEDs/each optic	1		
Light colour	White		
Required compone			
	Since.		
	EDC		
			90° 90°
LED	LUXEON MZ		
FWHM / FWTM	16.0° / 33.0°		
Efficiency	88 %		60° 60°
Peak intensity	7.8 cd/lm		227
LEDs/each optic	1		
Light colour	White		4300 42*
Required compone	ents:		
			6130
			\times \times \times
			30° 200 30°
~~~~~			15° 0° 15°
ØNICHI/			90° 90°
LED	NS9x383		73*
FWHM / FWTM	16.0° / 34.0°		1000
Efficiency	89 %		60° 60°
Peak intensity	6.8 cd/lm		$K \longrightarrow 1 \longrightarrow 7$
LEDs/each optic	1		
Light colour	White		gar es
Required compone	ents:		4000
			4 15° 0° 15°
ØNICHI/	۱		90°
LED	NSMx286M		
FWHM / FWTM	20.0° / 44.0°		3
Efficiency	91 %		
Peak intensity	4.4 cd/lm		60° 60°
LEDs/each optic	1		
Light colour	White		
Required compone			
			229
			$\times$ / $\vee$ $\times$
			30° 30° 30°
			15° 4600 35°



LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required componer	Duris S8 18.0° / 36.0° 84 % 6.2 cd/lm 1	91 91 91
Efficiency Peak intensity LEDs/each optic Light colour	84 % 6.2 cd/lm 1	100
Peak intensity LEDs/each optic Light colour	6.2 cd/lm 1	
LEDs/each optic Light colour	1	
Light colour		
Required componer	White	<i>9</i> ⁴
toquirou componer	nts:	400
		37" 650
SEOUL		( 155) of 154
SEOUL SEMICONDUCTOR	Z8Y15	
FWHM / FWTM	13.0° / 28.0°	
Efficiency	86 %	
Peak intensity	11.5 cd/lm	
LEDs/each optic	1	
Light colour	White	
Required componer		
SEOUL SEMICONDUCTOR		
LED	Z8Y19	
FWHM / FWTM	13.0° / 28.0°	
Efficiency	87 %	
Peak intensity	11 cd/lm	
LEDs/each optic	1	
Light colour	White	
Required componer	nts:	



# PHOTOMETRIC DATA (SIMULATED):


		7
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	LUXEON 5258 17.0° / 30.0° 92 % 8.6 cd/lm 1 White	12, 6, 13, 24, 24, 24, 25, 25, 25, 25, 25, 25, 25, 25, 25, 25
	JS	90 ⁴ 90 ⁴
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	CXM-3 14.0° / 26.0° 95 % 11.7 cd/lm 1 White	31, 13, 13, 13, 13, 13, 13, 13, 13, 13,
	IS	90 ⁶
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	CXM-4 18.0° / 34.0° 95 % 7.5 cd/lm 1 White	20 20 20 20 20 20 20 20 20 20
ED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	NFMW48xA 22.0° / 39.0° 96 % 5.6 cd/lm 1 White	34°



## PHOTOMETRIC DATA (SIMULATED):

OS	R	Α	Μ
Opto Se	mico	ndu	tors

LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components: OSCONIQ P 7070 20.0° / 33.0° 94 % 6.9 cd/lm 1 White





#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd. # 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

#### Local sales and technical support www.ledil.com/ where_to_buy

### **Shipping locations**

Salo, Finland Hong Kong, China

#### Distribution Partners www.ledil.com/

where_to_buy