ASMPH-0603

1.6 x 0.8 x 0.8mm

FEATURES:

- High DC bias current due to trench technology
- Much lower profile than any other series
- Monolithic structure for high reliability
- Excellent solderability and heat resistance
- Magnetically shielded structure to eliminate cross coupling

► **APPLICATIONS**:

(Pb)

ASMPH family is a miniature type of multilayer power inductors constructed using low loss ferite material to support high-speed switching frequencies. The compact size and high efficiency is ideal for DC/DC converter applications in space limited boards.

RoHS/RoHS II Compliant

Switching mode regulators for smart phones and cameras. Buck converters for RFIC, RFPA and Audio Codec modules. Boost converters for flash drivers.

Wireless cards, DVD players and other electronic devices.

ELECTRICAL SPECIFICATIONS:

Operating Temperature: -55°C to +125°C **Component Storage Temperature:** -55°C to +125°C **Package Storage Temperature:** -10°C to +40 °C

Part Number ASMPH-0603- Inductance Code	Inductance	Tolerance	DCR (Typ)	DCR (Max)	SRF Min.	Temperature Rise Current (Max)	Saturation Current (Typ)	Saturation Current (Max)
Units	μH	%	Ω	Ω	MHz	mA	mA	mA
Symbol	L	M=±20% N=±30%	DCR	DCR	SRF	Irms	Isat	Isat
ASMPH-0603-R22	0.22	M, N	0.10	0.13	200	1250	1600	1350
ASMPH-0603-R33	0.33	M, N	0.13	0.17	190	1200	1500	1250
ASMPH-0603-R47	0.47	M, N	0.15	0.19	180	1100	1200	1000
ASMPH-0603-R68	0.68	M, N	0.18	0.23	160	1150	1100	950
ASMPH-0603-1R0	1.0	M, N	0.20	0.25	125	1000	800	650
ASMPH-0603-1R5	1.5	M, N	0.23	0.29	100	900	500	420
ASMPH-0603-2R2	2.2	M, N	0.30	0.38	80	850	300	250
ASMPH-0603-2R7	2.7	M, N	0.34	0.43	90	750	220	180
ASMPH-0603-3R3	3.3	M, N	0.40	0.50	100	700	150	125
ASMPH-0603-4R7	4.7	M, N	0.40	0.50	65	700	80	65

Unless otherwise specified, the standard atmospheric conditions for measurement/test as:

- a. Ambient Temperature: 20±15°C
- b. Relative Humidity: 65±20%
- c. Air Pressure: 86 kPa to 106 kPa

Inductance (L): HP4291B+HP16192A or Equivalent, tested at 1MHz, -20dBm or 50mV. Direct Current Resistance (DCR): Milliohmeter-HP4338B or Equivalent Self-Resonant Frequency (SRF): HP4291B+HP16192A or Equivalent, -20dBm or 50mV.


Irms is the value of DC current as chip surface temperature rose just 40°C against chip initial surface temperature.

Isat is the value of DC current inductance decreased just 30% against initial value.




5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

RoHS/RoHS II Compliant



ASMPH-0603





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 03-28-19

ABRACON IS ISO9001-2015 CERTIFIED


SMD Multilayer Chip Power Inductor

Pb RoHS/RoHS II Compliant

1.6 x 0.8 x 0.8mm

ASMPH-0603

REFLOW PROFILE:



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 03-28-19

ABRACON IS ISO9001-2015 CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

<u>ASMPH-0603-R33M-T</u> <u>ASMPH-0603-1R0M-T</u> <u>ASMPH-0603-R68M-T</u> <u>ASMPH-0603-2R2M-T</u> <u>ASMPH-0603-1R5M-T</u> ASMPH-0603-R47M-T ASMPH-0603-R22M-T