

10 SEGMENT BAR GRAPH ARRAY

Part Number: DC10GWA

Green


Features

- Suitable for level indicators.
- Low current operation.
- Excellent on/off contrast.
- End stackable.
- Mechanically rugged.
- Standard : gray face, white segment.
- RoHS compliant.

Description

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions& Internal Circuit Diagram



1. All dimensions are in millimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.

2. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

2.54(0.1)

DATE: NOV/18/2013 SPEC NO: DSAD1429 **REV NO: V.9A** PAGE: 1 OF 6 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Y.Liu ERP: 1331000017

20

ø1.0-20

Selection Guide

Part No.	Dice	Lens Type	Iv (ucd) [1] @ 10mA		Description
			Min.	Тур.	
DC10GWA	Green (GaP)	White Diffused	5600	12000	10 Segments Bar graph-Display
			*1400	*4000	

- Note:
 1. Luminous intensity/ luminous Flux: +/-15%.
 *Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD [1]	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Green	2.2	2.5	V	I=20mA
lR	Reverse Current	Green		10	uA	V _R =5V

Notes:


- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C


Parameter	Green	Units		
Power dissipation	62.5	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating / Storage Temperature	-40°C To +85°C			
Lead Solder Temperature[2]	260°C For 3-5 Seconds			


- 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. 2mm below package base.


DATE: NOV/18/2013 SPEC NO: DSAD1429 **REV NO: V.9A** PAGE: 2 OF 6 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Y.Liu ERP: 1331000017




Green DC10GWA










SPEC NO: DSAD1429 APPROVED: WYNEC REV NO: V.9A CHECKED: Joe Lee DATE: NOV/18/2013 DRAWN: Y.Liu PAGE: 3 OF 6 ERP: 1331000017



Terms and conditions for the usage of this document

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.

RoHS Compliant

- 2.The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6.All design applications should refer to Kingbright application notes available at http://www.KingbrightUSA.com/ApplicationNotes


 SPEC NO: DSAD1429
 REV NO: V.9A
 DATE: NOV/18/2013
 PAGE: 4 OF 6

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: Y.Liu
 ERP: 1331000017

THROUGH HOLE DISPLAY MOUNTING METHOD

Lead Forming

Do not bend the component leads by hand without proper tools. The leads should be bent by clinching the upper part of the lead firmly such that the bending force is not exerted on the plastic body.




Installation

- 1. The installation process should not apply stress to the lead terminals.
- 2. When inserting for assembly, ensure the terminal pitch matches the substrate board's hole pitch to prevent spreading or pinching the lead terminals.



3. The component shall be placed at least 5mm from edge of PCB to avoid damage caused excessive heat during wave soldering.




PAGE: 5 OF 6

ERP: 1331000017

SPEC NO: DSAD1429 REV NO: V.9A DATE: NOV/18/2013

APPROVED: WYNEC CHECKED: Joe Lee DRAWN: Y.Liu

Recommended Wave Soldering Profiles:



Notes:

- 1.Recommend pre—heat temperature of 105°C or less (as measured with a thermocouple attached to the LED pins) prior to immersion in the solder wave with a maximum solder bath temperature of 260°C
- 2.Peak wave soldering temperature between 245°C \sim 255°C for 3 sec (5 sec max).
- 3.Do not apply stress to the epoxy resin while the temperature is above 85°C.
- 4.Fixtures should not incur stress on the component when mounting and during soldering proc 5.SAC 305 solder alloy is recommended.
- 6.No more than one wave soldering pass.

Soldering General Notes:


- 1. Through—hole displays are incompatible with reflow soldering.
- 2. If components will undergo multiple soldering processes, or other processes where the components may be subjected to intense heat, please check with Kingbright for compatibility.

CLEANING

- 1.Mild "no-clean" fluxes are recommended for use in soldering.
- If cleaning is required, Kingbright recommends to wash components with water only. Do not use harsh organic solvents for cleaning, because they may damage the plastic parts .And the devices should not be washed for more than one minute.

CIRCUIT DESIGN NOTES

- 1.Protective current—limiting resistors may be necessary to operate the Displays.
- 2.LEDs mounted in parallel should each be placed in series with its own current—limiting resistor.



SPEC NO: DSAD1429 APPROVED: WYNEC REV NO: V.9A CHECKED: Joe Lee DATE: NOV/18/2013 DRAWN: Y.Liu PAGE: 6 OF 6 ERP: 1331000017